



Product Description

UVB Broadband TL

Tubular or compact single-ended low-pressure mercury vapour fluorescent lamps

Benefits

- Photo-sensitizing agent - free treatment

Features

- Emit radiation for therapeutic and other applications

Application

- Phototherapy in dermatology (psoriasis, SUP)
- Meteorological testing equipment
- These lamps produce UV-B radiation which is harmful to human skin and eyes. They are therefore only available for medical and industrial applications

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


UVB Broadband TL

Versions



XPPR XUMTLRS G13

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL 20W/12 RS SLV/25	40.5 mm	589.8 mm	596.9 mm	594.5 mm	604 mm
TL 40W/12 RS SLV/25	40.5 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

General Information	
Cap-Base	G13
Light Technical	
Color Designation	Ultra Violet B
Color Code	12
Mechanical and Housing	
Bulb Shape	T38

Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Voltage (Nom)	Power Consumption
928010001230	TL 20W/12 RS SLV/25	0.37 A	59 V	19.3 W

Order Code	Full Product Name	Lamp Current (Nom)	Voltage (Nom)	Power Consumption
928011301230	TL 40W/12 RS SLV/25	0.43 A	101 V	39 W

Approval and Application

Order Code	Full Product Name	Mercury (Hg) Content (Nom)
928010001230	TL 20W/12 RS SLV/25	-

Order Code	Full Product Name	Mercury (Hg) Content (Nom)
928011301230	TL 40W/12 RS SLV/25	5.5 mg

