PHILIPS Lighting

TUV TL Mini - Small diameter lamps for residential applications

TUV TL Mini

TUV TL Mini lamps are slim double-ended UVC (germicidal) lamps used in residential water and air disinfection units. The small 16 mm diameter of the lamp allows for a small system design and design flexibility. TUV TL Mini lamps offer almost constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy.

Benefits

- $\boldsymbol{\cdot}$ Security of effective disinfection over the useful lifetime of the lamp
- High system efficacy because it is not required to over-design the purification system to maintain effectiveness of disinfection
- \cdot Good environmental choice because of lowest amount of mercury

Features

- Short-wave UV radiation with a peak at 253.7 nm (UVC) for disinfection purposes
- Protective inside coating ensures almost constant UV output over the complete lifetime of the lamp
- \cdot Special lamp glass filters out the 185 nm ozone-forming radiation
- $\boldsymbol{\cdot}$ Warning sign on lamp indicates that the lamp radiates UVC

Application

- Deactivation of bacteria, viruses and other micro-organisms
- Residential drinking water units
- Fish pond water units
- In-duct air treatment units
- Stand alone air purifiers


Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.

Versions



Dimensional drawing



Product	D	с
TUV 8W FAM/10X25BOX	16 mm	302.5 mm
TUV 11W FAM/10X25BOX	16 mm	226.3 mm

TUV TL Mini

Approval and application	
Mercury (Hg) Content (Nom)	4.4 mg
General information	
Cap-Base	G5
Useful Life (Nom)	11000 h
Main Application	Disinfection
System Description	na
Light technical	
Color Code	TUV
Color Designation	-
Lumen Depreciation At Useful Lifetime	15 %
Mechanical and housing	
Bulb Shape	Т5

Operating and electrical

Order Code	Full Product Name	Lamp Current (Nom)	Voltage (Nom)	Power (Nom)
299305	TUV 8T5 GERMICIDAL 25PK	0.145 A	56 V	7.1 W
352542	TUV 11W FAM/10X25BOX	0.4 A	34 V	11.5 W

-	

Order Code	Full Product Name	UV-C Radiation	Order Code	Full Product Name	UV-C Radiation
299305	TUV 8T5 GERMICIDAL 25PK	2.4 W	352542	TUV 11W FAM/10X25BOX	2.6 W



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

www.lighting.philips.com 2023, April 7 - data subject to change