



# Actinic BL PL-S/PL-L – compact for design freedom

## Actinic BL PL-S/PL-L

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers.

### Benefits

- Perfectly matches the eye sensitivity of houseflies and in this way attracts more insects
- Safe for use
- Good environmental choice
- Design freedom

### Features

- Emits long-wave UV-A radiation in the 350-400nm range
- UV-B/UV-A ratio less than 0.1 % (UV-B 280-315nm)
- 100% lead-free
- Low mercury content
- Compact lamp format

### Application

- Insect traps, Electronic Fly Killers (EFKs)

# Actinic BL PL-S/PL-L

## Warnings and Safety


- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury. Manage in Accord with Disposal Laws. See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

## Versions




PL-S

## Dimensional drawing



Product	D1 (max)	D (max)	A (max)	B (max)	C (max)
PL-L 18W/10/4P 1CT/25	18 mm	39 mm	194.2 mm	220 mm	226.6 mm
PL-L 36W/10/4P 1CT/25	18 mm	39 mm	384.2 mm	410 mm	416.6 mm



Product	D1 (max)	D (max)	A (max)	B (max)	C (max)
Actinic BL PL-S 9W/10/2P 1CT/6X10BOX	13 mm	28 mm	128.8 mm	144.5 mm	167 mm

## General Information

Main Application

Insect traps

## Operating and Electrical

## Actinic BL PL-S/PL-L

Order Code	Full Product Name	Lamp Current		Power (Rated)
		(Nom)	Voltage (Nom)	(Nom)
157651	PL-S 9W/10/2P Lead Free	0.17 A	60 V	8.6 W

Order Code	Full Product Name	Lamp Current		Power (Rated)
		(Nom)	Voltage (Nom)	(Nom)
130344	PL-L18W/10	0.375 A	58 V	18 W
232934	PL-L 36W/10/4P 1CT/25	0.435 A	106 V	36 W

### General Information

Order Code	Full Product Name	Cap-Base	Life To 50%	Useful Life
			Failures (Nom)	(Nom)
157651	PL-S 9W/10/2P Lead Free	G23	1000 h	2000 h
130344	PL-L18W/10	2G11	15000 h	5000 h

Order Code	Full Product Name	Cap-Base	Life To 50%	Useful Life
			Failures (Nom)	(Nom)
232934	PL-L 36W/10/4P 1CT/25	2G11	11000 h	-

### Light Technical

Order Code	Full Product Name	Color Code	Color Designation
157651	PL-S 9W/10/2P Lead Free	210	Ultra Violet A
130344	PL-L18W/10	10	Ultra Violet A

Order Code	Full Product Name	Color Code	Color Designation
232934	PL-L 36W/10/4P 1CT/25	210	-

### Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
157651	PL-S 9W/10/2P Lead Free	2xT12
130344	PL-L18W/10	2xT16

Order Code	Full Product Name	Bulb Shape
232934	PL-L 36W/10/4P 1CT/25	2xT16

### UV

Order Code	Full Product Name	UV-A Radiation 100Hr (IEC)	UV-B/UV-A (IEC)
157651	PL-S 9W/10/2P Lead Free	1.66 W	0.1 %
130344	PL-L18W/10	3.5 W	-

Order Code	Full Product Name	UV-A Radiation 100Hr (IEC)	UV-B/UV-A (IEC)
232934	PL-L 36W/10/4P 1CT/25	8.5 W	-

### Approval and Application

Order Code	Full Product Name	Mercury (Hg) Content	Mercury (Hg) Content
		(Max)	(Nom)
157651	PL-S 9W/10/2P Lead Free	-	-
130344	PL-L18W/10	-	-

Order Code	Full Product Name	Mercury (Hg) Content	Mercury (Hg) Content
		(Max)	(Nom)
232934	PL-L 36W/10/4P 1CT/25	2.1 mg	2.0 mg

