



Actinic BL TL-D(K) Secura – additional safety and HACCP approval

Actinic BL TL-D(K) Secura

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL-D(K) Secura lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. In addition, they have a special "Secura" sleeve that keeps all glass and components together in the case of accidental breakage. This eliminates the risk of glass splinters showering down on food preparation areas, for example. And that is why it meets the strict HACCP requirements. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice.

Benefits

- Perfectly matches the eye sensitivity of houseflies and in this way attracts more insects
- · Safe for use
- · Good environmental choice
- · No risk of glass particles

Features

- $\boldsymbol{\cdot}$ Emits long-wave UV-A radiation in the 350-400nm range
- · UV-B/UV-A ratio less than 0.1 % (UV-B 280-315nm)
- · 100% lead-free
- · Low mercury content
- · Shatterproof sleeve

Actinic BL TL-D(K) Secura

Application

• Insect traps, Electronic Fly Killers (EFKs)

Warnings and Safety


- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- · Lamp contains mercury.
- · Manage in Accord with Disposal Laws.
- · See: www.lamprecycle.org or 1-800-555-0050

Versions



TL-D Secura

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL-D 15W/10	1-1/8 in	17-1/4 in	17-1/2 in	17-7/16 in	17-13/16 in
Secura 1SL/25					
Actinic BL TL-D 18W/10	1-1/8 in	23-1/4 in	23-1/2 in	23-7/16 in	23-13/16 in
Secura 1SL/25					

Actinic BL TL-D(K) Secura

General information	
Cap-Base	G13
Useful Life (Nom)	9000 h
Main Application	Insect traps
Light technical	
Color Code	10
Color Designation	Actinic
Mechanical and housing	
Bulb Shape	Т8
UV	
UV-B/UV-A (IEC)	0.2 %

Approval and application

Order Code	Full Product Name	Mercury (Hg) Content (Nom)
215186	ACTINIC BL15W/10 SECURA 25PK	5.5 mg

Order Code	Full Product Name	Mercury (Hg) Content (Nom)
258996	Actinic BL TL-D 18W/10 Secura 1SL/25	5.0 mg

Operating and electrical

		Lamp Current	Voltage	Power
Order Code	Full Product Name	(Nom)	(Nom)	(Nom)
215186	ACTINIC BL15W/10	0.335 A	55 V	15 W
	SECURA 25PK			

		Lamp Current	Voltage	Power
Order Code	Full Product Name	(Nom)	(Nom)	(Nom)
258996	Actinic BL TL-D 18W/10	0.36 A	59 V	18 W
	Secura 1SL/25			

General information

Order Code	Full Product Name	Life To 50% Failures (Nom)
215186	ACTINIC BL15W/10 SECURA 25PK	8000 h

Order Code	Full Product Name	Life To 50% Failures (Nom)
258996	Actinic BL TL-D 18W/10 Secura 1SL/25	13000 h

UV

Order Code	Full Product Name	UV-A Radiation 100Hr (IEC)	Order Code
215186	ACTINIC BL15W/10 SECURA 25PK	3.15 W	258996

Order Code	Full Product Name	UV-A Radiation 100Hr (IEC)
258996	Actinic BL TL-D 18W/10 Secura 1SL/25	4.5 W



© 2022 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.