



Energy-efficient lighting for industrial and commercial applications

Greenperform Batten

GreenPerform Batten BN208C Dali is a high quality LED batten that delivers significant energy savings of up to 50% comparing to conventional T8 battens. BN208X incorporates the reliable structure, long lifetime LED lighting, and the global standard ZigBee control system, to achieve an easy-to-use networked solution. In the mean time, it helps to further increase energy saving maximum to 80% with daylight harvest and occupancy sensor.

Benefits

- High energy saving – up to 50% comparing to TL-8 batten
- Comfort light with accurate colour
- Safe and reliable
- Installation Flexibility
- Networking lighting

Features

- System efficacy 117lm/W, 4000/6000lm
- Frosted PC cover, CRI 80
- Lifetime 50Khrs @L70, CB/EMC/CE/ASNZ
- Suit for surface and suspension mounting
- Actilume Wireless 4.1+PIR/DDR sensor

Greenperform Batten

Application

- General Lighting
- Cove Lighting
- Indoor Parking

Warnings and Safety

- The product is IPX0 & as such is not protected against water ingress and as such we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips/Signify cannot guarantee safe failure and product warranty will become void

Accessories



Ordercode 911401567501,
911401567601, 911401567701,
911401567801, 911401568001,
911401568201, 911401568301,
911401831599, 911401831699,
911401831999, 911401832099

Greenperform Batten

Application Conditions

Ambient temperature range	0 to +40 °C
Maximum dimming level	1% (depends on dimmer, ELV)

Approval and Application

Mech. impact protection code	IK03
Ingress protection code	IP20

Controls and Dimming

Dimmable	Yes
----------	-----

Operating and Electrical

Input Voltage	220 to 240 V
---------------	--------------

General Information

CE mark	CE mark
Protection class IEC	Safety class I (I)
Optical cover/lens type	O
Driver included	Yes
ENEC mark	-
Flammability mark	NO
Gear	-
Glow-wire test	650/30
Light source replaceable	No
Number of gear units	1 unit
Optic type	WB
UL mark	No

Initial Performance (IEC Compliant)

Initial chromaticity	-
Init. Colour rendering index	80
Initial LED luminaire efficacy	118 lm/W
Luminous flux tolerance	+/-7.5%

Mechanical and Housing

Colour	White
--------	-------

General Information

Order Code	Full Product Name	Lamp family code
911401831599	BN208X LED40/NW L1200 ACW2 OS ACF EN	LED40S
911401831699	BN208X LED40/CW L1200 ACW2 OS ACF EN	LED40S
911401831999	BN208X LED60/NW L1500 ACW2 OS ACF EN	LED60S
911401832099	BN208X LED60/CW L1500 ACW2 OS ACF EN	LED60S

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Colour Temperature	Initial luminous flux	Initial input power
911401831599	BN208X LED40/NW L1200 ACW2 OS ACF EN	4000 K	4000 lm	34 W
911401831699	BN208X LED40/CW L1200 ACW2 OS ACF EN	6500 K	4000 lm	34 W

Order Code	Full Product Name	Init. Corr. Colour Temperature	Initial luminous flux	Initial input power
911401831999	BN208X LED60/NW L1500 ACW2 OS ACF EN	4000 K	6000 lm	51 W
911401832099	BN208X LED60/CW L1500 ACW2 OS ACF EN	6500 K	6000 lm	51 W

