



Energy-efficient lighting for industrial and commercial applications

GreenPerform Trunking

With Philips GreenPerform Trunking, industry and supermarket owners have an innovative LED solution that intelligently combines high-performance lighting features with maximised energy savings. This solution is designed to boost productivity and enhance the shopping experience without compromising performance and energy-efficiency. Suitable for a wide range of applications, GreenPerform Trunking is safe, reliable and versatile, the perfect direct replacement for conventional fluorescent trunking.

Benefits

- \cdot A system efficacy of 108 lm/w, providing up to 50% energy saving when replacing 2 x 58 w fluorescent trunking. Designed for 70% lumen maintenance over 50,000 hours, ensuring reliable performance over the product lifetime.
- Specially designed plastic caps improve uniformity along the length leading to a more uniform lighting distribution.
- 3 different beam angles available (Double asymmetric/Wide-beam/Opal) enabling you to choose the most optimum solution for different applications.
- An integrated modular design with 3-phase, 5-wire connection ensuring easy and flexible installation, and the possibility of controlling each phase separately.

Features


- · Philips Fortimo LED Line 1R for high efficiency and reliability
- · Advanced optics enable precise and energy-saving beam shapes
- · Requires much less packaging than fluorescent

GreenPerform Trunking

Application

- Supermarkets
- Warehouses
- Production facilities

Versions



LL120X LED35/LED70 L1500

GreenPerform Trunking

Driver failure rate at 5,000 hours	1%
Application Conditions	
Ambient temperature range	-20 to +35 °C
Suitable for random switching	No
Approval and Application	
Mech. impact protection code	IK02
Ingress protection code	IP20
Operating and Electrical	
Input Voltage	220 to 240 V
General Information	
Beam angle of light source	90 x 90 °
CE mark	CE mark
Protection class IEC	Safety class I (I)
Optical cover/lens type	0
Driver included	Yes
ENEC mark	-
Flammability mark	NO
Gear	-
Glow-wire test	650/30
Lamp family code	LED76S
Light source replaceable	No
Number of gear units	1 unit
Optic type	WB
UL mark	No
Initial Performance (IEC Compli	ant)
Init. Colour rendering index	80
Initial LED luminaire efficacy	108.57 lm/W
Initial luminous flux	7600 lm
Luminous flux tolerance	+/-7.5%
Initial input power	70 W
Machanical and Housing	
Mechanical and Housing	White
Colour	White
Over Time Performance (IEC Co	mpliant)
Median useful life L80B50	40000 h
	4000011

Application Conditions

Order Code	Full Product Name	Maximum dimming level
91140158202	1 LL120X LED70 L1500 NW PSU 5	OP ENG -
91140158292	1 LL120X LED70 L1500 CW PSD 7	OP ENG 1% (depends on dimmer, ELV)

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401582021	LL120X LED70 L1500 NW PSU 5 OP ENG	No

Order Code	Full Product Name	Dimmable
911401582921	LL120X LED70 L1500 CW PSD 7 OP ENG	Yes

Initial Performance (IEC Compliant)

GreenPerform Trunking

			Init. Corr. Colour
Order Code	Full Product Name	Initial chromaticity	Temperature
911401582021	LL120X LED70 L1500 NW	(0.38, 0.38) SDCM <5	4000 K
	PSU 5 OP ENG		

			Init. Corr. Colour
Order Code	Full Product Name	Initial chromaticity	Temperature
911401582921	LL120X LED70 L1500 CW	(0.31, 0.32) SDCM <5	6500 K
	PSD 7 OP ENG		



© 2021 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.