



Make roads safer sustainably with GreenVision Xceed

GreenVision Xceed

GreenVision Xceed offers an affordable LED road lighting solution to the customer for both pedestrian and vehicle road applications. It offers 3 housing sizes and a range of beam optics to fully cater to different road configurations and conditions. It is designed to achieve better light uniformity and maximum spacing between poles, while ensuring sufficient light on the road. Its die-cast aluminum housing and Philips LEDGINE LED platform ensures long lifetime and reliability. Best of all, GreenVision Xceed offers up to 50% of energy savings when compared to conventional lamp systems.

Benefits

- Solid die-cast housing design ensures long fixture lifetime
- Excellent thermal management ensures long system lifetime
- World class, approbated quality components (LEDs / Driver / etc.)
- Equipped with Service tag, a QR-based identification system that makes each luminaire uniquely identifiable and provides maintenance, installation and spare part information

Features

- Up to 50% energy savings with full compliance to road lighting safety standards
- Superior W/m² performance delivered through different optics for greater flexibility to fit different road applications
- High quality cool and neutral white light with high

Application

- Pedestrian category roads (P1-P6)
- Vehicle category roads (M1-M6)

GreenVision Xceed

Versions



BRP371 220-240V

BRP371 220-240V

Approval and Application

Mech. impact protection code	IK08
------------------------------	------

Controls and Dimming

Dimmable	No
----------	----

General Information

CE mark	CE mark
Light source color	730 warm white
Optical cover/lens type	Clear glass
Driver included	Yes
UL mark	-

Initial Performance (IEC Compliant)

Init. Color Rendering Index	>70
-----------------------------	-----

Mechanical and Housing

Color	Gray
-------	------

General Information

Order Code	Full Product Name	Service tag
911401673502	BRP371 LED91/WW 90W 220-240V DM MP1	-
911401673802	BRP371 LED73/WW 75W 220-240V DM MP1	-
911401673602	BRP371 LED55/WW 55W 220-240V DM MP1	Yes

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial luminous flux
911401673502	BRP371 LED91/WW 90W 220-240V DM MP1	3000 K	9100 lm



GreenVision Xceed

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial luminous flux
911401673802	BRP371 LED73/WW 75W 220-240V DM MP1	4000 K	7300 lm
911401673602	BRP371 LED55/WW 55W 220-240V DM MP1	4000 K	5500 lm

