



# Enhance the city with a new way of light

## RoadGrace

We now light up roads differently. It's no longer just about functionality as it is also about how road lighting can effortlessly complement new areas, and seamlessly retrofit into existing areas. With the RoadGrace LED luminaire, you can upgrade to an energy efficiency solution, and amazing flexibility with its five optic options, optimised for multiple road and street applications, such as freeways, intersections and crosswalks.

### Benefits

- Easy to install, it has tool-less access and an adjustable mounting spigot design that enables customisation of the lighting set-up to achieve the desired effect.
- Comes with five optic options, optimised for various road and street applications.

### Features

- Designed to withstand extreme temperatures with superior thermal management (-40 to 50C Ta )
- Top-class LED that ensures reliability and a long 50,000-hour lifetime. Cities save on maintenance costs and safeguard the community's safety, sustainably.
- Adjustable spigot +/- 15 degrees

### Application

- Road
- Street
- Motorway
- Freeways

## Versions



### BRP711

#### Approval and Application

Mech. impact protection code	IK08
------------------------------	------

#### Controls and Dimming

Dimmable	No
----------	----

#### General Information

CE mark	CE mark
Light source colour	740 neutral white
Optical cover/lens type	PC-MLO
Driver included	Yes
Light source replaceable	No
Number of gear units	1 unit
UL mark	No

#### Initial Performance (IEC Compliant)

Init. Corr. Colour Temperature	4000 K
Init. Colour Rendering Index	>70

#### Light Technical

Standard tilt angle side entry	15°
Standard tilt angle posttop	5°

#### Mechanical and Housing

Colour	Grey
--------	------

#### Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial luminous flux
911401810898	BRP711 LED67/NW 56W DWP3	6720 lm
911401810998	BRP711 LED88/NW 73W DWP3	8760 lm

