



# TubeLine LED unit – Optimised comfort with a linear LED solution

## TubeLine

Fluorescent linear lighting has traditionally been the preferred choice for customers demanding a high level of visual comfort. With excellent lighting uniformity on the road and walls, perfect visual guidance and high colour recognition, linear lighting offers the driver superior lighting quality and safety as well as high system redundancy compared to point-source lighting solutions. With TubeLine, the same lighting quality can be achieved but with the advantages of LED technology.

TubeLine is a state-of-the-art LED tunnel luminaire which offers all the benefits of linear lighting. With the latest LED technology, optimised dimensions and attractive pricing, linear lighting has never been more achievable within the constraints of limited budgets.

### Benefits

### Features

### Application

### Specifications

Type	BGP360
Light source	Integral LED-module
Power	21-108 W (21/44/72/82/108 W system power)
Luminous flux	3,000 up to 14,400 lm (3,000/6,000/10,000/11,400/14,400 lm)
Luminaire efficacy	> 120 lm/W (129/124/126/125/120 lm/W)

Correlated Colour	NW (4,000 K)
Temperature	Optional CW (5,700 K)
Colour Rendering Index	Minimal 70

# TubeLine

<b>Lumen maintenance at median useful life* 100,000 h</b>	L95
<b>Performance Ambient Temperature Tq</b>	+25 °C
<b>Operating temperature range</b>	-30 to +45 °C
<b>Driver</b>	Separate (non-self ballasted LED-module)
<b>Options</b>	Flying lead length Flying lead cable type Through-wiring Cable-gland metal Connector type
<b>Optic</b>	DTS, DTS-NB, DTS-WB, DTA, DTA-NB, DTA-WB
<b>Optical element</b>	Lenses
<b>Optical cover</b>	Glass flat
<b>Material</b>	Housing: extruded aluminium with diecasted endcaps and glass cover Extruded aluminium profiles: AlMg Si 0.5 anodised 25 µm Endcaps: diecaster aluminium, LM-6 powder-coated 65 µm Glass cover: 5 mm, thermally toughened

<b>Colour</b>	Extruded aluminium: natural Die-cast aluminium end-caps
<b>Connection</b>	Flying lead with plug fitted
<b>Maintenance</b>	NOT openable on site
<b>Installation</b>	Can be mounted with various mounting brackets: Standard, Ceiling and Cable tray-mounting brackets. A trunking solution is available: trunking profiles and cabling/connectivity solution. No integrated driver, a separate driver unit needs to be connected to power the LED unit. Operating temperature: -30 to +40 °C Recommended mounting height: > 4 m Mounting orientation: horizontal lengthwise in the tunnel
<b>Cable gland</b>	M12
<b>Accessories</b>	Mounting brackets: Standard, Ceiling and Cable tray-mounting brackets. Trunking profiles (at 2/4/6 m length) and cabling/connectivity solution. Special driver units to power the TubeLine locally and units for remote power supply.
<b>Remarks</b>	All accessories need to be ordered separately.

## Versions



TubeLine BGP360 tunnel luminaire

## Product details

TubeLine\_BGP360-DP01.tif



TubeLine\_BGP360-DP02.tif



# TubeLine

## Product details


TubeLine\_BGP360-DP03.tif



TubeLine\_BGP360-DP04.tif




TubeLine\_BGP360-DP05.tif



TubeLine\_BGP360-DP06.tif



TubeLine\_BGP360-DP07.tif



TubeLine\_BGP360-DP08.tif



TubeLine\_BGP360\_ZGP360-DP09.tif



## Accessories



TubeLine Acc.

Ordercode 10112100



TubeLine Acc.

Ordercode 10720800



TubeLine Acc.

Ordercode 10719200

## Approval and Application

Mech. impact protection code	IK08
Surge Protection (Common/Differential)	-

## General Information

Luminaire light beam spread	150°
CE mark	CE mark
Light source colour	740 neutral white
Optical cover/lens type	FG
Driver included	No
Flammability mark	NO
Gear	-
Gland material	Cable gland plastic
Light source replaceable	No
Number of gear units	1 unit
Optic type	Distribution tunnel symmetrical
Product Family Code	BGP360
UL mark	No

## Initial Performance (IEC Compliant)

Init. Corr. Colour Temperature	4000 K
Init. Colour Rendering Index	≥80

## Light Technical

Standard tilt angle side entry	-
Standard tilt angle posttop	-
Upward light output ratio	0

## Mechanical and Housing

Colour	Aluminium
--------	-----------

## Controls and Dimming

Order Code	Full Product Name	Dimmable
09429400	BGP360 LED30/740 DTS CFW C250WM GP	no
09430000	BGP360 LED60/740 DTS CFW C250WM GP	No
09432400	BGP360 LED120/740 DTS CFW C250WM GP	No
09433100	BGP360 LED159/740 DTS CFW C250WM GP	No

## Operating and Electrical

Order Code	Full Product Name	Driver current
09429400	BGP360 LED30/740 DTS CFW C250WM GP	310 mA
09430000	BGP360 LED60/740 DTS CFW C250WM GP	289 mA

Order Code	Full Product Name	Driver current
09432400	BGP360 LED120/740 DTS CFW C250WM GP	550 mA
09433100	BGP360 LED159/740 DTS CFW C250WM GP	700 mA

## General Information

Order Code	Full Product Name	Lamp family code	Number of light sources
09429400	BGP360 LED30/740 DTS CFW C250WM GP	LED30	24
09430000	BGP360 LED60/740 DTS CFW C250WM GP	LED60	48

Order Code	Full Product Name	Lamp family code	Number of light sources
09432400	BGP360 LED120/740 DTS CFW C250WM GP	LED120	48
09433100	BGP360 LED159/740 DTS CFW C250WM GP	LED159	48

## Initial Performance (IEC Compliant)

## TubeLine

Order Code	Full Product Name	Initial luminous flux
09429400	BGP360 LED30/740 DTS CFW C250WM GP	2700 lm
09430000	BGP360 LED60/740 DTS CFW C250WM GP	5400 lm

Order Code	Full Product Name	Initial luminous flux
09432400	BGP360 LED120/740 DTS CFW C250WM GP	10680 lm
09433100	BGP360 LED159/740 DTS CFW C250WM GP	14240 lm

