



Philips Cleanroom: a uniform, reliable, value-for-money solution

Cleanroom LED CR250B

In applications where hygiene is crucially important, such as hospitals and food production facilities, customers want proven IP65- and IP54-rated luminaires that are safe to use and are an economical investment. This family of fixtures represents an affordable solution: the Philips LED engine delivers reliable, high-quality light, and the flexible mounting possibilities mean that this family can be used in a wide range of applications. The fixtures are also compliant with all relevant standards (CE, EMC, RoHS).

Benefits

- Value-for-money investment
- Low maintenance due to the long lifetime of the luminaire
- Meets light-level requirements for main applications

Features

- Uniform surface of light
- IP65 (glass cover) and IP54 (PMMA cover) versions
- Light output 3,500 to 5,500 lm
- Works with different ceiling types
- Class II

Application

- Food production facilities and kitchens
- Hospitals and other healthcare facilities
- Clean production areas

Cleanroom LED CR250B

Versions







Cleanroom LED-CR150B W60L60



Cleanroom LED-CR250B W30L120

Dimensional drawing



Product details



Cleanroom_LED-
CR250B_W60L60-DP01



Cleanroom_LED-
CR250B_W60L60-DP02

Cleanroom LED CR250B

Product details



Cleanroom_LED-
CR150B_W30L120_PSU-DP04



Cleanroom_LED-
CR150B_W30L120_PSD-DP05



Cleanroom_LED-CR150B-
PSU_W30L120_PSU-DP06



Cleanroom_LED-
CR150B_W30L120_PSD-DP07



Cleanroom_LED-CR250B_PSU-
DP08



Cleanroom_LED-
CR150B_W30L120_CR150Z_SMB-
DP11



Cleanroom_LED-
CR150B_W60L60_CR150Z_SMB-
DP12



Cleanroom_LED-
CR250B_W30L120_CR250Z_SMB-
DP13

Cleanroom LED CR250B

Product details



Cleanroom_LED-
CR250B_W60L60_CR250Z_SMB-
DP14

General Information

CE mark	Yes
Driver included	Yes
ENEC mark	-
Flammability mark	For mounting on easily flammable surfaces
Light source replaceable	Yes
Number of gear units	Unit

Light Technical

Correlated Colour Temperature	4000 K
Colour rendering index (CRI)	>80
Number of light sources	2
Optic type	-

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz

Mechanical and Housing

Housing Colour	White
----------------	-------

Approval and Application

Protection class IEC	Safety class II
----------------------	-----------------

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-5%
-------------------------	-------

Application Conditions

Suitable for random switching	Yes
-------------------------------	-----

General Information

Order Code	Full Product Name	Glow-wire test	Lamp family code
07291200	CR150B LED35S/840 PSU W60L60 IP54	Temperature 650 °C, duration 30 s	GRN35
07292900	CR150B LED35S/840 PSD W60L60 IP54	Temperature 650 °C, duration 30 s	GRN35
07293600	CR150B LED35S/840 PSU W30L120 IP54	Temperature 650 °C, duration 30 s	GRN35
07294300	CR150B LED35S/840 PSD W30L120 IP54	Temperature 650 °C, duration 30 s	GRN35
07284400	CR250B LED35S/840 PSD W60L60 IP65	Temperature 850 °C, duration 30 s	GRN35
07285100	CR250B LED55S/840 PSU W60L60 IP65	Temperature 850 °C, duration 30 s	GRN55
07286800	CR250B LED55S/840 PSD W60L60 IP65	Temperature 850 °C, duration 30 s	GRN55
07287500	CR250B LED35S/840 PSU W30L120 IP65	Temperature 850 °C, duration 30 s	GRN35
07288200	CR250B LED35S/840 PSD W30L120 IP65	Temperature 850 °C, duration 30 s	GRN35
07289900	CR250B LED55S/840 PSU W30L120 IP65	Temperature 850 °C, duration 30 s	GRN55
07290500	CR250B LED55S/840 PSD W30L120 IP65	Temperature 850 °C, duration 30 s	GRN55

Light Technical

Cleanroom LED CR250B

Order Code	Full Product Name	Optical cover type	Luminous efficacy (rated)	Luminous
			(nom.)	Flux
07291200	CR150B LED35S/840 PSU W60L60 IP54	Polymethyl methacrylate bowl/ cover	88 lm/W	3,500 lm
07292900	CR150B LED35S/840 PSD W60L60 IP54	Polymethyl methacrylate bowl/ cover	88 lm/W	3,500 lm
07293600	CR150B LED35S/840 PSU W30L120 IP54	Polymethyl methacrylate bowl/ cover	88 lm/W	3,500 lm
07294300	CR150B LED35S/840 PSD W30L120 IP54	Polymethyl methacrylate bowl/ cover	88 lm/W	3,500 lm
07284400	CR250B LED35S/840 PSD W60L60 IP65	Clear glass with diffuser foil	88 lm/W	3,500 lm
07285100	CR250B LED55S/840 PSU W60L60 IP65	Clear glass with diffuser foil	87 lm/W	5,500 lm

Order Code	Full Product Name	Optical cover type	Luminous efficacy (rated)	Luminous
			(nom.)	Flux
07286800	CR250B LED55S/840 PSD W60L60 IP65	Clear glass with diffuser foil	87 lm/W	5,500 lm
07287500	CR250B LED35S/840 PSU W30L120 IP65	Clear glass with diffuser foil	88 lm/W	3,500 lm
07288200	CR250B LED35S/840 PSD W30L120 IP65	Clear glass with diffuser foil	88 lm/W	3,500 lm
07289900	CR250B LED55S/840 PSU W30L120 IP65	Clear glass with diffuser foil	87 lm/W	5,500 lm
07290500	CR250B LED55S/840 PSD W30L120 IP65	Clear glass with diffuser foil	87 lm/W	5,500 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
07291200	CR150B LED35S/840 PSU W60L60 IP54	40 W
07292900	CR150B LED35S/840 PSD W60L60 IP54	40 W
07293600	CR150B LED35S/840 PSU W30L120 IP54	40 W
07294300	CR150B LED35S/840 PSD W30L120 IP54	40 W
07284400	CR250B LED35S/840 PSD W60L60 IP65	40 W
07285100	CR250B LED55S/840 PSU W60L60 IP65	63 W

Order Code	Full Product Name	Power Consumption
07286800	CR250B LED55S/840 PSD W60L60 IP65	63 W
07287500	CR250B LED35S/840 PSU W30L120 IP65	40 W
07288200	CR250B LED35S/840 PSD W30L120 IP65	40 W
07289900	CR250B LED55S/840 PSU W30L120 IP65	63 W
07290500	CR250B LED55S/840 PSD W30L120 IP65	63 W

Temperature

Order Code	Full Product Name	Ambient temperature range
07291200	CR150B LED35S/840 PSU W60L60 IP54	0 to +40 °C
07292900	CR150B LED35S/840 PSD W60L60 IP54	0 to +40 °C
07293600	CR150B LED35S/840 PSU W30L120 IP54	0 to +40 °C
07294300	CR150B LED35S/840 PSD W30L120 IP54	0 to +40 °C
07284400	CR250B LED35S/840 PSD W60L60 IP65	-20 to +40 °C
07285100	CR250B LED55S/840 PSU W60L60 IP65	-20 to +40 °C

Order Code	Full Product Name	Ambient temperature range
07286800	CR250B LED55S/840 PSD W60L60 IP65	-20 to +40 °C
07287500	CR250B LED35S/840 PSU W30L120 IP65	-20 to +40 °C
07288200	CR250B LED35S/840 PSD W30L120 IP65	-20 to +40 °C
07289900	CR250B LED55S/840 PSU W30L120 IP65	-20 to +40 °C
07290500	CR250B LED55S/840 PSD W30L120 IP65	-20 to +40 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
07291200	CR150B LED35S/840 PSU W60L60 IP54	No
07292900	CR150B LED35S/840 PSD W60L60 IP54	Yes
07293600	CR150B LED35S/840 PSU W30L120 IP54	No
07294300	CR150B LED35S/840 PSD W30L120 IP54	Yes
07284400	CR250B LED35S/840 PSD W60L60 IP65	Yes
07285100	CR250B LED55S/840 PSU W60L60 IP65	No

Order Code	Full Product Name	Dimmable
07286800	CR250B LED55S/840 PSD W60L60 IP65	Yes
07287500	CR250B LED35S/840 PSU W30L120 IP65	No
07288200	CR250B LED35S/840 PSD W30L120 IP65	Yes
07289900	CR250B LED55S/840 PSU W30L120 IP65	No
07290500	CR250B LED55S/840 PSD W30L120 IP65	Yes

Approval and Application

Cleanroom LED CR250B

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
07291200	CR150B LED35S/840 PSU W60L60 IP54	IK03	IP54
07292900	CR150B LED35S/840 PSD W60L60 IP54	IK03	IP54
07293600	CR150B LED35S/840 PSU W30L120 IP54	IK03	IP54
07294300	CR150B LED35S/840 PSD W30L120 IP54	IK03	IP54
07284400	CR250B LED35S/840 PSD W60L60 IP65	IK07	IP65
07285100	CR250B LED55S/840 PSU W60L60 IP65	IK07	IP65

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
07286800	CR250B LED55S/840 PSD W60L60 IP65	IK07	IP65
07287500	CR250B LED35S/840 PSU W30L120 IP65	IK07	IP65
07288200	CR250B LED35S/840 PSD W30L120 IP65	IK07	IP65
07289900	CR250B LED55S/840 PSU W30L120 IP65	IK07	IP65
07290500	CR250B LED55S/840 PSD W30L120 IP65	IK07	IP65

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
07291200	CR150B LED35S/840 PSU W60L60 IP54	(0.38, 0.38) SDCM <4
07292900	CR150B LED35S/840 PSD W60L60 IP54	(0.38, 0.38) SDCM <4
07293600	CR150B LED35S/840 PSU W30L120 IP54	(0.38, 0.38) SDCM <4
07294300	CR150B LED35S/840 PSD W30L120 IP54	(0.38, 0.38) SDCM <4
07284400	CR250B LED35S/840 PSD W60L60 IP65	(0.38, 0.38) SDCM <4
07285100	CR250B LED55S/840 PSU W60L60 IP65	(0.38, 0.38) SDCM <3

Order Code	Full Product Name	Initial chromaticity
07286800	CR250B LED55S/840 PSD W60L60 IP65	(0.38, 0.38) SDCM <3
07287500	CR250B LED35S/840 PSU W30L120 IP65	(0.38, 0.38) SDCM <4
07288200	CR250B LED35S/840 PSD W30L120 IP65	(0.38, 0.38) SDCM <4
07289900	CR250B LED55S/840 PSU W30L120 IP65	(0.38, 0.38) SDCM <3
07290500	CR250B LED55S/840 PSD W30L120 IP65	(0.38, 0.38) SDCM <3

Application Conditions

Order Code	Full Product Name	Maximum dim level
07291200	CR150B LED35S/840 PSU W60L60 IP54	-
07292900	CR150B LED35S/840 PSD W60L60 IP54	1%
07293600	CR150B LED35S/840 PSU W30L120 IP54	-
07294300	CR150B LED35S/840 PSD W30L120 IP54	1%
07284400	CR250B LED35S/840 PSD W60L60 IP65	1%
07285100	CR250B LED55S/840 PSU W60L60 IP65	-

Order Code	Full Product Name	Maximum dim level
07286800	CR250B LED55S/840 PSD W60L60 IP65	1%
07287500	CR250B LED35S/840 PSU W30L120 IP65	-
07288200	CR250B LED35S/840 PSD W30L120 IP65	1%
07289900	CR250B LED55S/840 PSU W30L120 IP65	-
07290500	CR250B LED55S/840 PSD W30L120 IP65	1%

