# **PHILIPS** Lighting



# Pentura Mini LED – ultra-slim batten

# Pentura Mini LED

Pentura Mini LED is an extremely slim batten that offers the energy-saving benefits of LED technology, coupled with excellent lighting performance – bright, uniform light with good color rendering.Pentura Mini LED is very easy to install, even where space is limited, e.g. under shelves in shops, and over worktops and workstations in the home and home office. Thanks to its integrated driver and through-wiring, installation time is reduced to a minimum. Power cable, mounting clips and connection accessories are also supplied. Translucent end-caps eliminate black spots between the products, enabling consumers to create a continuous light-line.

#### Benefits

- Ultra-slim LED batten
- Energy-saving and long life benefits of LED technology
- $\cdot$  Easy to install; complete kit of accessories supplied

#### Features

- Minimalistic, unobtrusive design
- $\boldsymbol{\cdot}$  Integrated driver and through wiring
- $\cdot$  Polycarbonate housing
- Choice of 3000 and 4000 K color temperature
- Available in 300, 600, 900 and 1200 mm lengths
- $\cdot$  Non-trunkable version with on/off switch available

#### Application

- $\cdot$  Cove lighting
- $\cdot$  Under-cabinet lighting
- $\cdot$  Under-shelf lighting
- $\cdot$  Under-counter lighting

#### Specifications

Туре	BN132C (trunkable version)	Dimming	No
	BN133C (stand-alone version)	Material	Housing: extruded polycarbonate, white
Light source	Non-replaceable LED module		Diffuser: polycarbonate
Power	4 to 14 W (depending on type)		Endcaps: polycarbonate, translucent
Beam angle	Wide beam (120º)		Clips: steel
Luminous flux	350 to 1250 lm (depending on type)	Color	White
Correlated Color	3000 or 4000 K	Connection	Connector with flying wires (included)
Temperature		Installation	BN132C:
Color Rendering Index	> 80		Individual or in line; clicking the luminaire into pre-screwed
Lumen maintenance at	L65		ceiling brackets
median useful life*			Through-wiring possible (included)
50000 h			BN133C:
Control gear failure rate	<b>2</b> 7.5%		Individual, fly-wire from back of housing, of/off switch
at median useful life		Accessories	BN132C:
50000 h			Mounting clips, electrical connector with flying wires (150 mm)
Performance Ambient	+25 °C		and through-wiring cable (160 mm) included in the box
Temperature Tq			BN133C:
Operating temperature	0 to +35 °C		Mounting clips, included in the box
range			BN132Z:
Driver	Built-in		CCPA through-wiring cable (600 mm), to be ordered separately
Mains voltage	220-240 V / 50-60 Hz		

#### Versions





Pentura Mini LED BN132C batten

Pentura Mini LED BN133C batten

#### **Product details**



End-caps with integrated connector parts

Luminaires mounted in line

#### **Product details**



Side view, male connector part



Pentura Mini LED BN132C, length 900 mm





Mounting accessories included in the box

Fly-wire connection

Pentura Mini LED BN133C, length 600 mm



Accessories

Flexible coupling piece, 600 mm



Ordercode 910503910166

Application Conditions	
Ambient temperature range	0 to +35 °C
Suitable for random switching	No
Approval and Application	
Mech. impact protection code	IK02
Ingress protection code	IP40
Controls and Dimming	
Dimmable	No
Operating and Electrical	
Input Voltage	220-240 V
General Information	
Beam angle of light source	- °
CE mark	CE mark
Protection class IEC	Safety class II
Driver included	Yes
ENEC mark	-
Flammability mark	-
Gear	-
Glow-wire test	Temperature 650
	°C, duration 30 s
Lamp family code	LED-MP
Light source replaceable	No
Number of gear units	1 unit
Number of light sources	1 pc
Optic type	-
Initial Performance (IEC Compliant	
Init. Color Rendering Index	≥80
Luminous flux tolerance	+/-10%

#### Initial Performance (IEC Compliant) (1/2)

			Init. Corr. Color	Initial LED Iuminaire	Initial
	Full Day doubt Name	to March all and the second second			
Order Code	Full Product Name	Initial chromaticy	Temperature	efficacy	luminous flux
910503910156	BN132C LED12S/840	(0.39, 0.38)	4000 K	89 lm/W	1250 lm
	PSU L1200	SDCM<5			
910503910157	BN132C LED12S/830	(0.44, 0.41)	3000 K	89 lm/W	1250 lm
	PSU L1200	SDCM<5			
910503910158	BN132C LED9S/840	(0.39, 0.38)	4000 K	95 lm/W	950 lm
	PSU L900	SDCM<5			
910503910159	BN132C LED9S/830	(0.44, 0.41)	3000 K	95 lm/W	950 lm
	PSU L900	SDCM<5			
910503910160	BN132C LED6S/840	(0.39, 0.38)	4000 K	93 lm/W	650 lm
	PSU L600	SDCM<5			
910503910161	BN132C LED6S/830	(0.44, 0.41)	3000 K	93 lm/W	650 lm
	PSU L600	SDCM<5			
910503910162	BN132C LED3S/840	(0.39, 0.38)	4000 K	88 lm/W	350 lm
	PSU L300	SDCM<5			
910503910163	BN132C LED3S/830	(0.44, 0.41)	3000 K	88 lm/W	350 lm
	PSU L300	SDCM<5			
910503910164	BN133C LED6S/840	(0.39, 0.38)	4000 K	93 lm/W	650 lm
	PSU L600	SDCM<5			
910503910165	BN133C LED6S/830	(0.44, 0.41)	3000 K	93 lm/W	650 lm
	PSU L600	SDCM<5			

#### Initial Performance (IEC Compliant) (2/2)

Order Code	Full Product Name	Initial input power
910503910156	BN132C LED12S/840 PSU L1200	14 W
910503910157	BN132C LED12S/830 PSU L1200	14 W
910503910158	BN132C LED9S/840 PSU L900	10 W
910503910159	BN132C LED9S/830 PSU L900	10 W
910503910160	BN132C LED6S/840 PSU L600	7 W

Order Code	Full Product Name	Initial input power
910503910161	BN132C LED6S/830 PSU L600	7 W
910503910162	BN132C LED3S/840 PSU L300	4 W
910503910163	BN132C LED3S/830 PSU L300	4 W
910503910164	BN133C LED6S/840 PSU L600	7 W
910503910165	BN133C LED6S/830 PSU L600	7 W

#### Mechanical and Housing

Order Code	Full Product Name	Color
910503910156	BN132C LED12S/840 PSU L1200	White
910503910157	BN132C LED12S/830 PSU L1200	White
910503910158	BN132C LED9S/840 PSU L900	White
910503910159	BN132C LED9S/830 PSU L900	White
910503910160	BN132C LED6S/840 PSU L600	White

Order Code	Full Product Name	Color
910503910161	BN132C LED6S/830 PSU L600	White
910503910162	BN132C LED3S/840 PSU L300	white
910503910163	BN132C LED3S/830 PSU L300	White
910503910164	BN133C LED6S/840 PSU L600	White
910503910165	BN133C LED6S/830 PSU L600	White



© 2020 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

www.lighting.philips.com 2020, November 25 - data subject to change