



CitySoul gen2 LED – a versatile identity

CitySoul gen2 LED Large

CitySoul gen2 LED is one of the most versatile and inspirational urban street lighting families designed by Philips to date. This highly efficient range delivers excellent lighting levels whilst also providing the right ambiance for all urban application areas, from the outskirts of the city right through to the city center. By evolving the modularity of the CitySoul family and adding new innovations like the Lyre and the Accent bracket, Philips has made this range the ideal toolbox for every urban context. The design is flatter, completely round, and the transitions with the spigot and bracket entirely flush, thereby giving your cityscape a coherent, elegant and discreet identity. Designed around its LED engine, CitySoul gen2 LED is highly efficient and easy to maintain. It comes in two sizes and is suitable for side-entry, post-top, catenary and suspended mounting.

Benefits

- An integrated UrbanStyling lighting toolbox designed for many different urban applications
- Luminaires, brackets and poles are designed as one integrated concept to ensure coherence
- Future-proof thanks to excellent lighting performance and product quality

Features

- A broad range of elegant, dedicated and complete sets, including poles and brackets, a tiltable option, double post-top and catenary versions
- Various features to deliver the most efficient and comfortable lighting level
- Compatible with all Philips' standard and advanced lighting controls
- Easy maintenance on-site
- Compatible with existing CitySoul pole and bracket range Flip, Morph, Jump, Sweep

CitySoul gen2 LED Large

Application

- City centers
- Parks and plazas
- Roads and streets
- Commercial districts

Specifications

Type	BPP531 (post top version)
	BRP531 (side entry version)
	BSP531 (catenary or suspended version)
	BVP531 (dedicated for Right Curve bracket)
	BGP531 (MBA CD; dedicated for Graphic and East bracket)
Light source	Integral LED-module
Power	GreenLine (GRN): 38-138 W depending on configuration
Luminous flux (system)	4250-13,000 lm (3000 K)
	4600-14,800 lm (4000 K)
Luminaire efficacy (system)	Up to 110 lm/W
Correlated Color	3000 K, warm white
Temperature	4000 K, neutral white
Color Rendering Index	≥ 70, neutral white
	≥ 80, warm white

Maintenance of lumen output - L80B10	100,000 hours
Operating temperature range	-20 to +35 °C
Driver	Built-in (self ballasted LED-module)
Mains voltage	210-240 V / 50-60 Hz
Inrush current	80 A / 150 µs (75 W driver)
	108 A / 140 µs (150 W driver)
Dimming	DynaDimmer
	LumiStep
	CLO
Controls system input	DALI
	StarSense RF
	LightWave (GPRS)

Specifications

Options	Photocell: Minicell, 35, 55, 70 lux
Optic	Distribution medium (DM), wide (DW), wet road (DK), asymmetrical (A), symmetrical (S)
Optical cover	Hard glass, tempered
	Glass plate, frosted (optional)
	IK10 glass, tempered (optional)
Material	Housing: high-pressure die-cast aluminum, coated
	Gasket: silicone rubber, heat resistant
	Optics: plastic (PMMA)
	Cover: glass, thermally hardened
Color	Housing: Philips ultra-dark grey (close to RAL 7022, fine textured color)
	Frame: satin silver grey (close to RAL 9006)
	Other RAL and AKZO Futura colors available on request
Connection	Screw connection block
	Wieland push in connector possible (optional)
Maintenance	From below by opening the housing with 1 screws (Torx T20) Same screws to access the luminaire, driver and LED-board

Installation	BPP531: post-top mounting: Ø 60-76 mm
	BRP531: side-entry mounting: Ø 42-60 mm
	BSP531: catenary or suspended mounting with dedicated bracket
	Recommended mounting height: up to 14 m
	Adjustable tilt angle: possible with specific MBA or 76PA mounting spigot
Cable gland	Max SCx
	- BRP/BPP531: 0.014 m ²
	- 2 x BGP531 + JRP532: 0.033 m ²
	- BGP531 + MBA SJ (tiltable side-entry bracket): 0.017 m ²
Accessories	JRP533 (lyre bracket)
	JRP534 (accent spigot)
	JRP532 (double post top spigot)
	JGP530 (east bracket)
	JRP531 (graphic bracket)
	JSP532 (right curve bracket)
	YHB530 (lyre dedicated pole)
Remarks	Lyre bracket version only available for CitySoul gen2 LED Mini family (BPP532)
	Pre-cabled possible for:
	- Wall mounted / suspended or catenary (C2K, 1.65 m cable)
	- Other configurations (C8K, 8 m cable, C10K, 10 m cable, C14K, 14 m cable)

CitySoul gen2 LED Large

Versions



Product details



CitySoul gen2 side-entry version-
top view



CitySoul gen2 with Right Curve
bracket



CitySoul gen2 with East bracket-
side view



CitySoul gen2 with East bracket-
top view



CitySoul gen2 with East bracket-
below view



CitySoul gen2 with Graphic
bracket- side view

CitySoul gen2 LED Large

Product details



CitySoul gen2 with Graphic bracket- top view



CitySoul gen2 with Graphic bracket- below view



CitySoul gen2 with Right Curve bracket- side view



CitySoul gen2 with Right Curve bracket- top view



CitySoul gen2 with Right Curve bracket- below view



CitySoul gen2 with Accent spigot mounted on Ocean Straight pole



CitySoul gen2 with adjustable spigot on Ocean Curved pole



CitySoul gen2 post-top version- side view

CitySoul gen2 LED Large

Product details

CitySoul gen2 post-top version-
top view



CitySoul gen2 double post-top
version- side view



Spigot ensures flush transition
between double post-top
luminaire and mast



Approval and Application

Mech. impact protection code	IK08
Surge Protection (Common/Differential)	Luminaire surge protection level up to 6 kV differential mode and 8 kV common mode

General Information

Luminaire light beam spread	180°
CE mark	CE mark
Coating	-
Optical cover/lens type	FG
Driver included	Yes
Flammability mark	NO
Light source replaceable	Yes
Number of gear units	1 unit

Light Technical

Standard tilt angle side entry	0°
Standard tilt angle posttop	0°
Upward light output ratio	0.03

Mechanical and Housing

Colour	Gray
--------	------

Application Conditions

Order Code	Full Product Name	Maximum dim level
61330600	BPP531 GRN85-/740 I DM FG CO GR D9	20%
61346700	BPP531 GRN125-/740 I DM FG CO GR D9	20%
61352800	BPP531 GRN60-/830 II DM FG AL GR	Not applicable
61362700	BPP531 GRN160-/830 II DM FG AL GR T35	Not applicable
61334400	BRP531 GRN145-/740 II DM FG CO GR 60S	Not applicable
61340500	BRP531 GRN106-/740 I DM FG CO GR D9 60S	20%
61342900	BRP531 GRN145-/740 I DM FG CO GR D9 T35	20%
61344300	BRP531 GRN185-/740 I DM FG CO GR D9 60S	10%
61350400	BRP531 GRN60-/830 II DM FG AL GR T35 60S	Not applicable
61367200	BRP531 GRN95-/740 I DM FG CO GR CLO T35	Not applicable

Controls and Dimming

CitySoul gen2 LED Large

Order Code	Full Product Name	Dimmable
61330600	BPP531 GRN85-/740 I DM FG CO GR D9	Yes
61346700	BPP531 GRN125-/740 I DM FG CO GR D9	Yes
61352800	BPP531 GRN60-/830 II DM FG AL GR	No
61362700	BPP531 GRN160-/830 II DW FG AL GR T35	No
61334400	BRP531 GRN145-/740 II DM FG CO GR 60S	No

Order Code	Full Product Name	Dimmable
61340500	BRP531 GRN106-/740 I DM FG CO GR D9 60S	Yes
61342900	BRP531 GRN145-/740 I DM FG CO GR D9 T35	Yes
61344300	BRP531 GRN185-/740 I DM FG CO GR D9 60S	Yes
61350400	BRP531 GRN60-/830 II DM FG AL GR T35 60S	No
61367200	BRP531 GRN95-/740 I DM FG CO GR CLO T35	No

General Information (1/2)

Order Code	Full Product Name	Parts colour	Light		Lamp family code
			source colour	Glow-wire test	
61330600	BPP531 GRN85-/740 I DM FG CO GR D9	Cover painted	740 neutral white	650/30	GRN85
61346700	BPP531 GRN125-/740 I DM FG CO GR D9	Cover painted	740 neutral white	650/30	GRN125
61352800	BPP531 GRN60-/830 II DM FG AL GR	All parts colored	830 warm white	650/30	GRN60
61362700	BPP531 GRN160-/830 II DW FG AL GR T35	All parts colored	830 warm white	650/30	GRN160
61334400	BRP531 GRN145-/740 II DM FG CO GR 60S	Cover painted	740 neutral white	650/30	GRN145

Order Code	Full Product Name	Parts colour	Light		Lamp family code
			source colour	Glow-wire test	
61340500	BRP531 GRN106-/740 I DM FG CO GR D9 60S	Cover painted	740 neutral white	650/30	GRN106
61342900	BRP531 GRN145-/740 I DM FG CO GR D9 T35	Cover painted	740 neutral white	650/30	GRN145
61344300	BRP531 GRN185-/740 I DM FG CO GR D9 60S	Cover painted	740 neutral white	650/30	GRN185
61350400	BRP531 GRN60-/830 II DM FG AL GR T35 60S	All parts colored	830 warm white	650/30	GRN60
61367200	BRP531 GRN95-/740 I DM FG CO GR CLO T35	Cover painted	740 neutral white	-	GRN95

General Information (2/2)

Order Code	Full Product Name	Number of		Product Family Code
		light sources	Optic type	
61330600	BPP531 GRN85-/740 I DM FG CO GR D9	40	Distribution medium	BPP531
61346700	BPP531 GRN125-/740 I DM FG CO GR D9	64	Distribution medium	BPP531
61352800	BPP531 GRN60-/830 II DM FG AL GR	40	Distribution medium	BPP531
61362700	BPP531 GRN160-/830 II DW FG AL GR T35	64	Distribution wide	BPP531
61334400	BRP531 GRN145-/740 II DM FG CO GR 60S	64	Distribution medium	BRP531

Order Code	Full Product Name	Number of		Product Family Code
		light sources	Optic type	
61340500	BRP531 GRN106-/740 I DM FG CO GR D9 60S	64	Distribution medium	BRP531
61342900	BRP531 GRN145-/740 I DM FG CO GR D9 T35	64	Distribution medium	BRP531
61344300	BRP531 GRN185-/740 I DM FG CO GR D9 60S	64	Distribution medium	BRP531
61350400	BRP531 GRN60-/830 II DM FG AL GR T35 60S	40	Distribution medium	BRP531
61367200	BRP531 GRN95-/740 I DM FG CO GR CLO T35	1	Distribution medium	BRP531

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Colour Temperature	Init. Colour	
			Rendering Index	Initial luminous flux
61330600	BPP531 GRN85-/740 I DM FG CO GR D9	4000 K	>70	7057 lm
61346700	BPP531 GRN125-/740 I DM FG CO GR D9	4000 K	>70	10292 lm
61352800	BPP531 GRN60-/830 II DM FG AL GR	3000 K	>80	4942 lm
61362700	BPP531 GRN160-/830 II DW FG AL GR T35	3000 K	>80	12779 lm

Order Code	Full Product Name	Init. Corr. Colour Temperature	Init. Colour	
			Rendering Index	Initial luminous flux
61334400	BRP531 GRN145-/740 II DM FG CO GR 60S	4000 K	>70	11882 lm
61340500	BRP531 GRN106-/740 I DM FG CO GR D9 60S	4000 K	>70	10697 lm
61342900	BRP531 GRN145-/740 I DM FG CO GR D9 T35	4000 K	>70	11882 lm
61344300	BRP531 GRN185-/740 I DM FG CO GR D9 60S	4000 K	>70	14995 lm

CitySoul gen2 LED Large

Order Code	Full Product Name	Init. Corr. Colour Temperature	Init. Colour Rendering Index	Initial luminous flux
61350400	BRP531 GRN60-/830 II DM FG AL GR T35 60S	3000 K	>80	4942 lm

Order Code	Full Product Name	Init. Corr. Colour Temperature	Init. Colour Rendering Index	Initial luminous flux
61367200	BRP531 GRN95-/740 I DM FG CO GR CLO T35	4000 K	>70	7863 lm

