



Philips LuxSpace Mini, recessed – high efficiency, visual comfort and a stylish design

LuxSpace Mini, recessed

Customers are looking to optimise all their resources, and that means not just their running costs (energy, etc.) but also user costs where they see much a bigger impact on return. Therefore, LuxSpace is designed to provide the perfect combination of efficiency, visual comfort and design, without compromising on lighting performance (colour rendering and light distribution). It offers a wide choice of options for creating the desired ambience to support user comfort, whatever the application.

Benefits

- Best-in-class efficacy with up to 150 lm/W
- Creates a gentle, natural light, ensuring visual comfort
- Perfect ceiling integration with narrow rim or rimless version for plaster ceilings
- Improved glare control with office compliancy
- Provides uniform lighting thanks to wide light distribution

LuxSpace Mini, recessed


Features

- Choice of four optics: high-gloss, faceted, matt and white
- Heights: deep (up to UGR 19), low (up to UGR 22)
- Rim colours: high-gloss metalised, white (RAL9003), grey (RAL9006), black (RAL9004) as standard
- Rimless version available
- Light colour: CRI80 3000K ,4000K and CRI90 2700, 3000K and 4000K
- Compliant for central emergency lighting with DC
- Multiple additional options: PG (Protection Glass front face) and PGO (IP54 Protection Glass Opal front face), 3 Hours emergency, through-wiring, Eca and B2ca class cable(Halogen free) and connector options

Application

- Offices
- Retail
- Hospitals and care centres
- Hospitality

Dimensional drawing



LuxSpace Mini, recessed

General Information	
CE mark	Yes
Driver included	Yes
ENEC mark	ENEC mark
Number of gear units	Unit
Light Technical	
Correlated Colour Temperature	4000 K
Optical cover type	-
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Mechanical and Housing	
Housing Colour	White
Approval and Application	
Protection class IEC	Safety class II
Mech. impact protection code	IK02
Ingress protection code	IP20
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

General Information (1/2)

Order Code	Full Product Name	Flammability mark	Glow-wire test	Lamp family code	Light source replaceable
97049900	DN561B LED12S/840 PSU-E C WH	For mounting on normally flammable surfaces	Temperature 850 °C, duration 5 s	-	No
97055000	DN561B LED12S/840 DIA-VLC-E C WH	For mounting on normally flammable surfaces	Temperature 850 °C, duration 5 s	-	No
58580500	DN561B LED12S/840UE PSU-E C WH	-	Temperature 650 °C, duration 30 s	12S	Yes
97045100	DN560B LED12S/840 PSU-E C WH	For mounting on normally flammable surfaces	Temperature 850 °C, duration 5 s	-	No
97051200	DN560B LED12S/840 PSU-E C ELP3 WH	For mounting on normally flammable surfaces	Temperature 850 °C, duration 5 s	-	No
97053600	DN560B LED12S/840 DIA-VLC-E C WH	For mounting on normally flammable surfaces	Temperature 850 °C, duration 5 s	-	No
97057400	DN560B LED20S/840 PSU-E C WH	For mounting on normally flammable surfaces	Temperature 850 °C, duration 5 s	-	No
58579900	DN560B LED12S/840UE PSU-E C WH	-	Temperature 650 °C, duration 30 s	12S	Yes

General Information (2/2)

Order Code	Full Product Name	Product family code
97049900	DN561B LED12S/840 PSU-E C WH	DN561B
97055000	DN561B LED12S/840 DIA-VLC-E C WH	DN561B
58580500	DN561B LED12S/840UE PSU-E C WH	DN561B
97045100	DN560B LED12S/840 PSU-E C WH	DN560B

Order Code	Full Product Name	Product family code
97051200	DN560B LED12S/840 PSU-E C ELP3 WH	DN560B
97053600	DN560B LED12S/840 DIA-VLC-E C WH	DN560B
97057400	DN560B LED20S/840 PSU-E C WH	DN560B
58579900	DN560B LED12S/840UE PSU-E C WH	DN560B

Light Technical (1/2)

Order Code	Full Product Name	Colour rendering index (CRI)	Luminous efficacy (rated) (nom.)	Luminous Flux	Optic type
97049900	DN561B LED12S/840 PSU-E C WH	>80	138 lm/W	1,350 lm	-
97055000	DN561B LED12S/840 DIA-VLC-E C WH	>80	138 lm/W	1,350 lm	-
58580500	DN561B LED12S/840UE PSU-E C WH	80	150 lm/W	1,200 lm	High-gloss mirror
97045100	DN560B LED12S/840 PSU-E C WH	>80	138 lm/W	1,350 lm	-

Order Code	Full Product Name	Colour rendering index (CRI)	Luminous efficacy (rated) (nom.)	Luminous Flux	Optic type
97051200	DN560B LED12S/840 PSU-E C ELP3 WH	>80	105 lm/W	1,350 lm	-
97053600	DN560B LED12S/840 DIA-VLC-E C WH	>80	138 lm/W	1,350 lm	-
97057400	DN560B LED20S/840 PSU-E C WH	>80	134 lm/W	2,200 lm	-
58579900	DN560B LED12S/840UE PSU-E C WH	80	150 lm/W	1,200 lm	High-gloss mirror

LuxSpace Mini, recessed

Light Technical (2/2)

Order Code	Full Product Name	Upwards light output ratio
97049900	DN561B LED12S/840 PSU-E C WH	-
97055000	DN561B LED12S/840 DIA-VLC-E C WH	-
58580500	DN561B LED12S/840UE PSU-E C WH	0
97045100	DN560B LED12S/840 PSU-E C WH	-

Order Code	Full Product Name	Upwards light output ratio
97051200	DN560B LED12S/840 PSU-E C ELP3 WH	-
97053600	DN560B LED12S/840 DIA-VLC-E C WH	-
97057400	DN560B LED20S/840 PSU-E C WH	-
58579900	DN560B LED12S/840UE PSU-E C WH	0

Operating and Electrical

Order Code	Full Product Name	Power Consumption
97049900	DN561B LED12S/840 PSU-E C WH	9.8 W
97055000	DN561B LED12S/840 DIA-VLC-E C WH	9.8 W
58580500	DN561B LED12S/840UE PSU-E C WH	8.2 W
97045100	DN560B LED12S/840 PSU-E C WH	9.8 W

Order Code	Full Product Name	Power Consumption
97051200	DN560B LED12S/840 PSU-E C ELP3 WH	12.8 W
97053600	DN560B LED12S/840 DIA-VLC-E C WH	9.8 W
97057400	DN560B LED20S/840 PSU-E C WH	16.4 W
58579900	DN560B LED12S/840UE PSU-E C WH	8.2 W

Temperature

Order Code	Full Product Name	Ambient temperature range
97049900	DN561B LED12S/840 PSU-E C WH	+10 to +25 °C
97055000	DN561B LED12S/840 DIA-VLC-E C WH	+10 to +25 °C
58580500	DN561B LED12S/840UE PSU-E C WH	+10 to +35 °C
97045100	DN560B LED12S/840 PSU-E C WH	+10 to +25 °C

Order Code	Full Product Name	Ambient temperature range
97051200	DN560B LED12S/840 PSU-E C ELP3 WH	+10 to +25 °C
97053600	DN560B LED12S/840 DIA-VLC-E C WH	+10 to +25 °C
97057400	DN560B LED20S/840 PSU-E C WH	+10 to +25 °C
58579900	DN560B LED12S/840UE PSU-E C WH	+10 to +35 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
97049900	DN561B LED12S/840 PSU-E C WH	No
97055000	DN561B LED12S/840 DIA-VLC-E C WH	Yes
58580500	DN561B LED12S/840UE PSU-E C WH	No
97045100	DN560B LED12S/840 PSU-E C WH	No

Order Code	Full Product Name	Dimmable
97051200	DN560B LED12S/840 PSU-E C ELP3 WH	No
97053600	DN560B LED12S/840 DIA-VLC-E C WH	Yes
97057400	DN560B LED20S/840 PSU-E C WH	No
58579900	DN560B LED12S/840UE PSU-E C WH	No

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
97049900	DN561B LED12S/840 PSU-E C WH	(0.38, 0.38) SDCM <2
97055000	DN561B LED12S/840 DIA-VLC-E C WH	(0.38, 0.38) SDCM <2
58580500	DN561B LED12S/840UE PSU-E C WH	-
97045100	DN560B LED12S/840 PSU-E C WH	(0.38, 0.38) SDCM <2

Order Code	Full Product Name	Initial chromaticity
97051200	DN560B LED12S/840 PSU-E C ELP3 WH	(0.38, 0.38) SDCM <2
97053600	DN560B LED12S/840 DIA-VLC-E C WH	(0.38, 0.38) SDCM <2
97057400	DN560B LED20S/840 PSU-E C WH	(0.38, 0.38) SDCM <2
58579900	DN560B LED12S/840UE PSU-E C WH	-

Application Conditions

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
97049900	DN561B LED12S/840 PSU-E C WH	-	Yes
97055000	DN561B LED12S/840 DIA-VLC-E C WH	1%	Yes
58580500	DN561B LED12S/840UE PSU-E C WH	Not applicable	No
97045100	DN560B LED12S/840 PSU-E C WH	-	Yes
97051200	DN560B LED12S/840 PSU-E C ELP3 WH	-	Yes

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
97053600	DN560B LED12S/840 DIA-VLC-E C WH	1%	Yes
97057400	DN560B LED20S/840 PSU-E C WH	-	Yes
58579900	DN560B LED12S/840UE PSU-E C WH	Not applicable	No

LuxSpace Mini, recessed

