



Simple, robust magnetic ballast

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

The HID Basic Semi-Parallel ballast is an impregnated (HID standard) electromagnetic copper/iron ballast for use with an external ignitor for HID lamps.

Benefits

- Limited volume of ballast coil; also lightweight
- Simple installation and cabling

Features

- Orthocyclic winding process
- Ballasts equipped with screw terminal blocks as standard
- Earthing-while-mounting facility (HID Standard ballasts)
- Low watt losses

Application

- For use with SON and HPI (PLUS) lamps in road, public, area and industry lighting
- For use with MHN/CDM lamps in shop, lobby and city beautification applications
- HID-Basic ballasts should be restricted to built-in situations where relative humidity is limited.

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

Versions



Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 100L 300I	6.2 mm	51.5 mm	122.0 mm	107 mm	57.1 mm
BSN 400L 300I TS	6.2 mm	82 mm	165.0 mm	150 mm	96.5 mm
BSN 250L 302I	6.3 mm	64.5 mm	150.0 mm	129.0 mm	72.5 mm
BSN 250L 427I TS	6.2 mm	64.5 mm	150.0 mm	135 mm	75.5 mm

Operating and Electrical

Input Frequency	50 Hz
-----------------	-------

Operating and Electrical

Order Code	Full Product Name	Input Voltage
913710100859	BSN 250L 427I TS	230 V (default) or 240 V
913710102850	BSN 250L 302I	230 V

Order Code	Full Product Name	Input Voltage
913710103750	BSN 100L 300I	220 V
913710109542	BSN 400L 300I TS	220 V

System characteristics

Order Code	Full Product Name	Rated Ballast-Lamp Power
913710100859	BSN 250L 427I TS	250 W
913710102850	BSN 250L 302I	250 W

Order Code	Full Product Name	Rated Ballast-Lamp Power
913710103750	BSN 100L 300I	100 W
913710109542	BSN 400L 300I TS	400 W

HID-Basic Semi-Parallel ballasts for SON/CDM/MH lamps

