



RCS750 3-circuit square track system – flexible and multifunctional

3-circuit Square RCS750

The RCS750 3-circuit square track system is made up of a solid aluminium track available in lengths of 1, 2, 3 and 4 m with four electrical conductors. Any given configuration can be created easily: horizontal or vertical, mounted on or in the ceiling, on the wall or on free-standing panels. The system can also be used as a floating structure. All luminaires have a separate power supply and can be switched selectively. They can be moved easily to change the lighting and presentation. In this way, a multifunctional track system can be created for accent lighting as well as for suspending advertising and decorative material. A range of adaptors, power supply connections and mounting accessories is also available.

Benefits

- Flexible 3-circuit track system for the professional user, allowing any required configuration to be created relatively easily
- All luminaires have separate power switching so they can easily be moved, for example to create changing atmospheres in shop windows or interiors
- Can be applied as a 'floating' structure using the suspension tubes and clamps provided

Features

- Can be used with all Philips LED 3C track spots
- Available in lengths of 1, 2, 3 and 4 m
- Available in three finishes – white, black, aluminum
- Range of adaptors, power supply connections and mounting accessories available

3-circuit Square RCS750

Application

- Retail
- Indoor architectural lighting

Versions



ZRS750 EPSR BK (XTS11-2+41-2)



ZRS750 EPSL BK (XTS12-2+41-2)



ZRS750 CPS WH (XTS14-3)



ZRS750 EP BK (XTS41-2)



ZRS750 EP WH (XTS41-3)





RCS750 track, black



ZRS750 ICP BK (XTS21-2)

Dimensional drawing




3-circuit Square RCS750

Dimensional drawing



Product details



General Information

3-circuit Square RCS750

Order Code	Full Product Name	Accessory		
		color	Glow-wire test	Glow-wire test
910502558518	ZRS750 EPSR BK (XTS11-2+41-2)	Black	-	-
910502558418	ZRS750 EPSL BK (XTS12-2+41-2)	Black	-	-
910500187615	ZRS750 CPS WH (XTS14-3)	White	-	-
910502558618	ZRS750 EP BK (XTS41-2)	Black	-	-
910500187715	ZRS750 EP WH (XTS41-3)	White	-	-

Order Code	Full Product Name	Accessory		
		color	Glow-wire test	Glow-wire test
910930013218	RCS750 3C L1000 BK (XTS4100-2)	Black	Temperature 850 °C, duration 5 s	Temperature 850 °C, duration 5 s
910930013318	RCS750 3C L2000 BK (XTS4200-2)	Black	Temperature 850 °C, duration 5 s	Temperature 850 °C, duration 5 s
910502558718	ZRS750 ICP BK (XTS21-2)	Black	-	-

Operating and Electrical

Order Code	Full Product Name	Input Voltage	Input Voltage
910502558518	ZRS750 EPSR BK (XTS11-2+41-2)	250 V	250 V
910502558418	ZRS750 EPSL BK (XTS12-2+41-2)	250 V	250 V
910500187615	ZRS750 CPS WH (XTS14-3)	250 V	250 V
910502558618	ZRS750 EP BK (XTS41-2)	-	-

Order Code	Full Product Name	Input Voltage	Input Voltage
910500187715	ZRS750 EP WH (XTS41-3)	-	-
910930013218	RCS750 3C L1000 BK (XTS4100-2)	-	-
910930013318	RCS750 3C L2000 BK (XTS4200-2)	-	-
910502558718	ZRS750 ICP BK (XTS21-2)	250 V	250 V

Approval and Application

Order Code	Full Product Name	Protection class IEC	Protection class IEC	Ingress protection	Ingress protection
				code	code
910502558518	ZRS750 EPSR BK (XTS11-2+41-2)	-	-	-	-
910502558418	ZRS750 EPSL BK (XTS12-2+41-2)	-	-	-	-
910500187615	ZRS750 CPS WH (XTS14-3)	-	-	-	-
910502558618	ZRS750 EP BK (XTS41-2)	-	-	-	-

Order Code	Full Product Name	Protection class IEC	Protection class IEC	Ingress protection	Ingress protection
				code	code
910500187715	ZRS750 EP WH (XTS41-3)	-	-	-	-
910930013218	RCS750 3C L1000 BK (XTS4100-2)	Safety class I	Safety class I	IP30	IP30
910930013318	RCS750 3C L2000 BK (XTS4200-2)	Safety class I	Safety class I	IP30	IP30
910502558718	ZRS750 ICP BK (XTS21-2)	-	-	-	-

