# **PHILIPS** Lighting



# GreenSpace Accent – The best recessed accent retrofit solution

# **GreenSpace Accent Elbow**

Lighting is one of the key assets that can help retailers and building operators achieve their cost targets. Until now, many have been reluctant to switch from CDM to LED technology because the efficiency, initial investment, installation process, light level and/or quality of light of new LED solutions were not on par with their CDM existing solutions. This is no longer the case, thanks to GreenSpace Accent. Now, retailers and building operators can make the switch and enjoy the benefits of Philips PerfectAccent light quality as well as significant energy savings compared to their existing CDM installation - all for a reasonable initial investment. And GreenSpace Accent's regular cut-out makes retrofit installation quick and easy. For food and fashion retailers, GreenSpace Accent elbow is also available with special light recipes to further enhance the store ambiance and to show the produce and goods on offer in the very best light: Fresh Food Champagne is the perfect LED solution for displaying fruit, vegetables, cheese, bread and pastries in a warm lighting ambiance; Fresh Food Meat creates the best light setting for meat enhancement in a cool natural ambiance; CrispWhite is the clear choice for fashion retailers to make colors appear rich and intense while keeping whites bright.

# Benefits

- $\cdot$  Hassle-free replacement of CDM recessed luminaires
- $\cdot$  Short payback compared with CDM luminaires due to high system efficacy
- High-quality accent lighting thanks to PerfectAccent reflector's light signature

# **GreenSpace Accent Elbow**

# Features

- High efficacy
- Philips PerfectAccent quality of light
- CDM retrofit recessed luminaire; easy to install
- Clean, robust design

## Application

- $\cdot$  Retail stores, especially food and fashion stores
- Public spaces such as shopping malls, train stations, airports, etc.

# Warnings and Safety

- $\cdot$  During maintenance, the product must be switched off and cooled down
- The product must be installed out of arm's reach. Manipulating the product when hot is only possible with an insulated glove

# **Dimensional drawing**



# **Product details**



IPDP\_RS340Bi\_0001-Detail photo



IPDP\_RS340Bi\_0007-Detail photo

IPDP\_RS340Bi\_0009-Detail photo



IPDP\_RS340Bi\_0015-Detail photo

# **GreenSpace Accent Elbow**

# Product details



#### **General Information** CE mark Yes Driver included Yes ENEC mark ENEC mark Flammability mark For mounting on normally flammable surfaces Glow-wire test Temperature 650 °C, duration 30 s Light source replaceable No Number of gear units 1 unit Product family code RS342B **Light Technical** Beam angle of light source 120 degree(s) Wide beam Optic type **Operating and Electrical** Input Voltage 220 to 240 V Line Frequency 50 to 60 Hz **Controls and Dimming** Dimmable No Mechanical and Housing Housing Color White **Approval and Application** Protection class IEC Safety class II Mech. impact protection code IK02 Ingress protection code IP20 Initial Performance (IEC Compliant) Luminous flux tolerance +/-10% **Application Conditions** Maximum dim level Not applicable Suitable for random switching Yes

#### IPDP\_RS340Bi\_0017-Detail photo

### Light Technical

		Correlated Color	Color		
		Temperature	rendering	Luminous Efficacy	
Order Code	Full Product Name	(Nom)	index (CRI)	(rated) (Nom)	Luminous Flux
97782500	RS342B 19S/FMT PSU-E	3000 K	>90	86 lm/W	1,900 lm
	WB CP WH				
97792400	RS342B 27S/PW930	3000 K	≥90	121 lm/W	2,850 lm
	PSU-E WB CP WH				
97796200	RS342B 39S/840 PSU-E	4000 K	≥80	142 lm/W	4,000 lm
	WB CP WH				

# GreenSpace Accent Elbow

# **Operating and Electrical**

Order Code	Full Product Name	Power Consumption
97782500	RS342B 19S/FMT PSU-E WB CP WH	22 W
97792400	RS342B 27S/PW930 PSU-E WB CP WH	26 W

Order Code	Full Product Name	Power Consumption
97796200	RS342B 39S/840 PSU-E WB CP WH	28 W

#### Temperature

Order Code	Full Product Name	Ambient temperature range
97782500	RS342B 19S/FMT PSU-E WB CP WH	+10 to +25 °C
97792400	RS342B 27S/PW930 PSU-E WB CP WH	+10 to +35 °C

Order Code	Full Product Name	Ambient temperature range
97796200	RS342B 39S/840 PSU-E WB CP WH	+10 to +25 °C

# Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
97782500	RS342B 19S/FMT PSU-E WB CP WH	(0.406, 0.350) SDCM<3
97792400	RS342B 27S/PW930 PSU-E WB CP WH	(0.422, 0.386) SDCM <2

Order Code	Full Product Name	Initial chromaticity
97796200	RS342B 39S/840 PSU-E WB CP WH	(0.382, 0.380) SDCM <3



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.