

Electronic Transformers for low-voltage LED application

LED Transformer for LED strip

Constant voltage LED transformer for 24VDC LED application, compatible with Philips and other LED strip and offer 24VDC interface to LED application

Benefits

- Total system solution from Philips for LED strip application
- No need earth connection
- High power factor

Features


- LED strip dedicated transformer
- Long lifetime
- Class II installation (2 wiring installation only)
- Independant housing
- EMC compliant to EN 55015

Application


- Hotels and restaurants
- Retail and shopping malls
- Decorative applications

LED Transformer for LED strip

Versions



Dimensional drawing



Product	A1	A2	B1	B2	C1
LED Transformer 60W 24VDC	180 mm	170 mm	52 mm	42.0 mm	30 mm

Product	A1	A2	B1	B2	C1
LED Transformer 120W 24VDC	300 mm	290 mm	40 mm	29 mm	30 mm

Operating and Electrical

Input Frequency	50 to 60 Hz
Input Voltage	220 to 240 V

General Information

Lamp Type	LV Halogen
-----------	------------

General Information

Order Code	Full Product Name	Number Of Products On MCB (16A Type B) (Max)
72909000	LED Transformer 60W 24VDC	13

Order Code	Full Product Name	Number Of Products On MCB (16A Type B) (Max)
10202000	LED Transformer 120W 24VDC	12

LED Transformer for LED strip

System characteristics

Order Code	Full Product Name	Rated Ballast-Lamp Power	Order Code	Full Product Name	Rated Ballast-Lamp Power
72909000	LED Transformer 60W 24VDC	60 W	10202000	LED Transformer 120W 24VDC	120 W

