



Ledinaire Panel - Simply great LED

Ledinaire Panel

The Ledinaire range contains a selection of popular off-the-shelf LED luminaires that comes with the high Philips quality levels at a competitive price. Reliable, energy efficient and affordable – just what you need.

Benefits

- Philips quality and reliability
- Energy saving
- Diffuse comfortable light

Features

- Accessoires for plaster, surface mounted and suspension available
- Modern, unobtrusive design

Application

- General lighting

Specifications

Type	RC065B
Ceiling type	Exposed T-bar ceiling
Module size	600 x 600 mm
Light source	Non-replaceable LED module
Power	42 W
Beam angle	114°
Luminous flux	3200 lm
Correlated Color	4000 K (Neutral white)
Temperature	
Color Rendering Index	> 80

Lumen maintenance at	L70
median useful life*	
50000 h	
Control gear failure rate	7.5%
at median useful life	
50000 h	
Performance Ambient	+25 °C
Temperature Tq	
Operating temperature	+10 to +40 °C
range	
Driver	Separate

Ledinaire Panel

Mains voltage	220-240 V / 50-60 Hz
Dimming	Not dimmable
Material	Painted steel
Color	White (RAL9016)
Optical cover	Polystyrene diffuser
Connection	Push-in connector with pull relief

Maintenance	No internal cleaning required
Installation	Individual, lay-in in exposed ceiling grids Through-wiring not possible Installation without removing lamp and cover
Accessories	Accessories for suspension, plaster ceiling and surface-mounting

Versions



RC065B - LED Module, system
flux 3200 lm

Product details

Ledinaire_Panel-
RC065B_W60L60-DP.tif



Ledinaire_Panel-
RC065_W60L60_OC-DPP.TIF



Ledinaire Panel

Product details

Ledinaire_Panel-
RC066_W62L62_OC-DPP.TIF



Ledinaire Panel

Application Conditions

Ambient temperature range	+10 to +35 °C
Suitable for random switching	No

Approval and Application

Mech. impact protection code	IK02
Ingress protection code	IP20

Controls and Dimming

Dimmable	No
----------	----

Operating and Electrical

Input Voltage	220/240 V
---------------	-----------

General Information

Beam angle of light source	120 °
CE mark	CE mark
Protection class IEC	Safety class II
Driver included	Yes
ENEC mark	-
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Light source replaceable	No
Number of gear units	1 unit
Service tag	Yes

Initial Performance (IEC Compliant)

Initial chromaticity	(0.38, 0.38) SDCM <5
Init. Corr. Color Temperature	4000 K
Init. Color Rendering Index	80
Initial LED luminaire efficacy	90 lm/W
Initial luminous flux	3400 lm
Luminous flux tolerance	+/-10%
Initial input power	38 W

Mechanical and Housing

Color	White
Width	- mm

General Information

Order Code	Full Product Name	Optic type
912401483175	RC065B LED34S/840 PSU W60L60 OC	Beam angle 70°
912401483176	RC066B LED34S/840 PSU W62L62 OC	Beam angle 70°
912401483243	RC065B LED34S/840 PSU W60L60 NOC 1PK	Beam angle 110°
912401483244	RC065B LED34S/840 PSU W60L60 OC 1PK	Beam angle 70°
912401483245	RC065B LED34S/840 PSU W60L60 NOC	Beam angle 110°

Mechanical and Housing

Order Code	Full Product Name	Diameter
912401483175	RC065B LED34S/840 PSU W60L60 OC	-
912401483176	RC066B LED34S/840 PSU W62L62 OC	-
912401483243	RC065B LED34S/840 PSU W60L60 NOC 1PK	-

Order Code	Full Product Name	Diameter
912401483244	RC065B LED34S/840 PSU W60L60 OC 1PK	-
912401483245	RC065B LED34S/840 PSU W60L60 NOC	-

Ledinaire Panel

