



Philips CityCharm: combining visual comfort and performance

CityCharm Cone

The Philips CityCharm range is designed for use in urban areas where comfortable lighting, ambience, and design play an important role. It offers three iconic, timeless designs: CityCharm cordoba (BDS490), CityCharm cone (BDS491), and CityCharm fluid (BDS492) along with a range of decorative and practical accessories. This enables you to create a lighting solution that carries the signature of your municipality, both by day and by night. Whether you specify cordoba, cone or fluid LED lights, CityCharm provides high visual comfort while maintaining excellent performance. It offers a choice of two innovative Philips Lighting technologies: GentleBeam, which maximizes visual comfort, or ClearGuide (cordoba or cone), which optimizes vertical illumination and visual guidance. To personalize your CityCharm lighting solution further, decorative accessories for this range make it possible to define the volume of the bowl and change its appearance. A variety of dedicated brackets and masts are also available to enable you to reshape your residential areas and city centers in the most elegant way imaginable.

Benefits

- Elegant, iconic range enhanced by dedicated poles and brackets to create distinctive styles
- Comfortable lighting with GentleBeam or ClearGuide technologies
- Multiple geometries for visual comfort in all urban spaces
- Excellent lighting performance, high-quality finishing
- Future-ready with Zhaga-D4i system ready (SR) top socket to connect with Interact controls
- Service tag for easy installation and maintenance

CityCharm Cone

Features

- Choice of luminaire shapes, color effects, poles and brackets
- Diffusing tools for visual comfort, colored inserts to enhance ambiance
- Wide range of lumen outputs and optics for maximum efficiency at all lighting levels
- Choice of color temperatures and color rendering for different ambiances: 2200K, 2700K, 3000K and 4000K
- Efficacy up to 144 lm/W
- Cordoba and fluid versions available with ULR < 1%
- Lifetime up to 100,000 hours @L96 B10
- 5-year standard warranty (option to extend up to 10 years)

Application

- Residential
- Footpaths and cycle lanes
- Parks and boulevards

Versions



OPPR BDS490i 0009

Dimensional drawing

Product details



CityCharm_Cordoba_Cone-
BDS490_BDS491_DGR-DP02.tif



CityCharm_Cone-BDS491_DGR-
DP03.tif

General Information	
CE mark	Yes
Driver included	Yes
Flammability mark	-
Light source replaceable	Yes
Number of gear units	1 unit
Product family code	BDS491
Light Technical	
Luminaire light beam spread	360°
Optical cover type	Polycarbonate bowl/cover
Standard tilt angle side entry	0°
Standard tilt angle posttop	0°
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Housing Color	Gray
Approval and Application	
Mech. impact protection code	IK10
Ingress protection code	IP66
Application Conditions	
Maximum dim level	Not applicable

General Information

Order Code	Full Product Name	Gear	Glow-wire test	Lamp family code	Service tag
910505017426	BDS491 CG25-/740 II S GR D11 76	EB	Temperature 650 °C, duration 5 s	CG25	-
910505017431	BDS491 CG25-/740 II A GR H07RN-PX1.5 60	EB	Temperature 650 °C, duration 5 s	CG25	-
910505017432	BDS491 CG25-/730 II S GR 60	EB	Temperature 650 °C, duration 5 s	CG25	-
912300024687	BDS491 LED70-/830 I S GRB GR 60	-	-	LED70	Yes
912300024693	BDS491 LED30-/830 II DM GRB GR 60	-	-	LED30	Yes
912300024719	BDS491 LED20/722 PSU II DM GRB GR H07 60	-	-	LED20	Yes
912300024684	BDS491 LED100-/740 I DM GRB DF-S GR CLO	-	-	LED100	Yes
912300024685	BDS491 LED10-/740 I DM GRB DF-S GR CLO S	-	-	LED10	Yes
912300024721	BDS491 LED40/730 PSU I DW DF-S GR H07 60	-	-	LED40	Yes

Light Technical (1/2)

Order Code	Full Product Name	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Flux
910505017426	BDS491 CG25-/740 II S GR D11 76	neutral white	4000 K	≥70	2,140 lm

Order Code	Full Product Name	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Flux
910505017431	BDS491 CG25-/740 II A GR H07RN-PX1.5 60	neutral white	4000 K	≥70	2,140 lm

Order Code	Full Product Name	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Flux
910505017432	BDS491	730	3000 K	≥70	2,117 lm
	CG25-/730 II S GR	warm			
	60	white			
912300024687	BDS491	830	3000 K	80	5,670 lm
	LED70-/830 I S	warm			
	GRB GR 60	white			
912300024693	BDS491	830	3000 K	80	2,400 lm
	LED30-/830 II DM	warm			
	GRB GR 60	white			
912300024719	BDS491	722 warm	2200 K	70	1,600 lm
	LED20/722 PSU II	white			

Order Code	Full Product Name	Light source color	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Flux
	DM GRB GR H07				
	60				
912300024684	BDS491	740	4000 K	70	7,600 lm
	LED100-/740 I	neutral			
	DM GRB DF-S GR CLO	white			
912300024685	BDS491	740	4000 K	70	800 lm
	LED10-/740 I DM	neutral			
	GRB DF-S GR CLO S	white			
912300024721	BDS491	730	3000 K	70	3,200 lm
	LED40/730 PSU I	warm			
	DW DF-S GR H07	white			
	60				

Light Technical (2/2)

Order Code	Full Product Name	Number of light sources	Optic type outdoor	Upward light output ratio
910505017426	BDS491 CG25-/740 II S GR D11 76	15	Symmetrical	0.03
910505017431	BDS491 CG25-/740 II A GR H07RN-PX1.5 60	15	Asymmetrical	0.03
910505017432	BDS491 CG25-/730 II S GR 60	15	Symmetrical	0.03
912300024687	BDS491 LED70-/830 I S GRB GR 60	-	Symmetrical	0.0136
912300024693	BDS491 LED30-/830 II DM GRB GR 60	-	Distribution medium	0.03

Order Code	Full Product Name	Number of light sources	Optic type outdoor	Upward light output ratio
912300024719	BDS491 LED20/722 PSU II DM GRB GR H07 60	-	Distribution medium	0.0261
912300024684	BDS491 LED100-/740 I DM GRB DF-S GR CLO	-	Distribution medium	0.0351
912300024685	BDS491 LED10-/740 I DM GRB DF-S GR CLO S	-	Distribution medium	0.0307
912300024721	BDS491 LED40/730 PSU I DW DF-S GR H07 60	-	Distribution wide	0.0322

Operating and Electrical

Order Code	Full Product Name	Power Consumption
910505017426	BDS491 CG25-/740 II S GR D11 76	20 W
910505017431	BDS491 CG25-/740 II A GR H07RN-PX1.5 60	20 W
910505017432	BDS491 CG25-/730 II S GR 60	22 W
912300024687	BDS491 LED70-/830 I S GRB GR 60	53 W
912300024693	BDS491 LED30-/830 II DM GRB GR 60	23.5 W

Order Code	Full Product Name	Power Consumption
912300024719	BDS491 LED20/722 PSU II DM GRB GR H07 60	17.2 W
912300024684	BDS491 LED100-/740 I DM GRB DF-S GR CLO	58 W
912300024685	BDS491 LED10-/740 I DM GRB DF-S GR CLO S	6.8 W
912300024721	BDS491 LED40/730 PSU I DW DF-S GR H07 60	26.5 W

Approval and Application

Order Code	Full Product Name	Surge Protection (Common/Differential)
910505017426	BDS491 CG25-/740 II S GR D11 76	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Surge Protection (Common/Differential)
910505017431	BDS491 CG25-/740 II A GR H07RN-PX1.5 60	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Surge Protection (Common/ Differential)
910505017432	BDS491 CG25-/730 II S GR 60	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
912300024687	BDS491 LED70-/830 I S GRB GR 60	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
912300024693	BDS491 LED30-/830 II DM GRB GR 60	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
912300024719	BDS491 LED20/722 PSU II DM GRB GR H07 60	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Surge Protection (Common/ Differential)
912300024684	BDS491 LED100-/740 I DM GRB DF-S GR CLO	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
912300024685	BDS491 LED10-/740 I DM GRB DF-S GR CLO S	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
912300024721	BDS491 LED40/730 PSU I DW DF-S GR H07 60	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Driver failure rate at 5000 h
910505017426	BDS491 CG25-/740 II S GR D11 76	0.05 %
910505017431	BDS491 CG25-/740 II A GR H07RN-PX1.5 60	0.05 %
910505017432	BDS491 CG25-/730 II S GR 60	0.05 %
912300024687	BDS491 LED70-/830 I S GRB GR 60	-
912300024693	BDS491 LED30-/830 II DM GRB GR 60	-

Order Code	Full Product Name	Driver failure rate at 5000 h
912300024719	BDS491 LED20/722 PSU II DM GRB GR H07 60	-
912300024684	BDS491 LED100-/740 I DM GRB DF-S GR CLO	-
912300024685	BDS491 LED10-/740 I DM GRB DF-S GR CLO S	-
912300024721	BDS491 LED40/730 PSU I DW DF-S GR H07 60	-

