



Classic LEDbulbs lamps for decorative lighting

Classic filament LEDbulbs

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Benefits

- Around 90% energy saving
- Very long lifetime that reduces the need for replacement
- Easy replacement of classic conventional lamps

Features


- Heritage design with classic shape
- Designed to be seen, they look good on and off
- Perfect fit and high quality finishing
- High color rendering (CRI > 80) for vivid colors
- Environmentally friendly: contains no mercury or other hazardous substances

Application

- Perfect for decorative installations
- Domestic applications
- Hospitality: restaurants and hotels


Classic filament LEDbulbs

Versions



Dimensional drawing

D



Product	D	C
LEDClassic 7.5-70W A60 E27 WW CL D APR	60 mm	112 mm
LEDClassic 4-50W A60 E27 WW CL ND APR	60 mm	104 mm
LEDClas 7.5-60W A60 E27 2000K GOLD APR	60 mm	112 mm

Product	D	C
LEDClassic 7-60W G120 E27 2000K GOLD APR	125 mm	188 mm

Classic filament LEDbulbs

Operating and Electrical	
Input Frequency	50 to 60 Hz
Voltage (Nom)	220-240 V
Starting Time (Nom)	0.5 s
General Information	
Cap-Base	E27
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20,000X
Light Technical	
Colour Rendering Index (Nom)	80
Llmf At End Of Nominal Lifetime (Nom)	70 %
Temperature	
T-Case Maximum (Nom)	70 °C

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Energy Efficiency Label (EEL)
929001228008	LEDClassic 7.5-70W A60 E27 WW CL D APR	8 kWh	A+
929001228108	LEDClä 7.5-60W A60 E27 2000K GOLD APR	8 kWh	A+
929001229108	LEDClassic 7-60W G120 E27 2000K GOLD APR	7 kWh	A+
929001237108	LEDClassic 4-50W A60 E27 WW CL ND APR	4 kWh	A++

Controls and Dimming

Order Code	Full Product Name	Dimmable
929001228008	LEDClassic 7.5-70W A60 E27 WW CL D APR	Yes
929001228108	LEDClä 7.5-60W A60 E27 2000K GOLD APR	Yes

Order Code	Full Product Name	Dimmable
929001229108	LEDClassic 7-60W G120 E27 2000K GOLD APR	Yes
929001237108	LEDClassic 4-50W A60 E27 WW CL ND APR	No

Operating and Electrical

Order Code	Full Product Name	Wattage Equivalent	Power (Rated) (Nom)
929001228008	LEDClassic 7.5-70W A60 E27 WW CL D APR	70 W	7.5 W
929001228108	LEDClä 7.5-60W A60 E27 2000K GOLD APR	60 W	7.5 W

Order Code	Full Product Name	Wattage Equivalent	Power (Rated) (Nom)
929001229108	LEDClassic 7-60W G120 E27 2000K GOLD APR	60 W	7 W
929001237108	LEDClassic 4-50W A60 E27 WW CL ND APR	50 W	4 W

Light Technical

Order Code	Full Product Name	Correlated Colour		
		Colour Code	Temperature (Nom)	Luminous Flux (Nom)
929001228008	LEDClassic 7.5-70W A60 E27 WW CL D APR	827	2700 K	806 lm
929001228108	LEDClä 7.5-60W A60 E27 2000K GOLD APR	820	2000 K	600 lm

Order Code	Full Product Name	Correlated Colour		
		Colour Code	Temperature (Nom)	Luminous Flux (Nom)
929001229108	LEDClassic 7-60W G120 E27 2000K GOLD APR	820	2000 K	630 lm
929001237108	LEDClassic 4-50W A60 E27 WW CL ND APR	827	2700 K	470 lm

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929001228008	LEDClassic 7.5-70W A60 E27 WW CL D APR	Clear	A60
929001228108	LEDClä 7.5-60W A60 E27 2000K GOLD APR	Gold Clear	A60
929001229108	LEDClassic 7-60W G120 E27 2000K GOLD APR	Gold Clear	G120
929001237108	LEDClassic 4-50W A60 E27 WW CL ND APR	Clear	A60

Classic filament LEDbulbs

