



Créez une ambiance chaleureuse et accueillante avec un éclairage de qualité supérieure

MASTER LEDspot ExpertColor MV

Le spot MASTER LEDspot MV ExpertColor crée une ambiance chaleureuse et confortable dans les établissements hôteliers, les habitations et les restaurants. Une telle atmosphère est due à un éclairage de qualité supérieure présentant un spectre lumineux personnalisé, une valeur IRC élevée et une fonction de gradation en profondeur. Résultat ? Un magnifique éclairage esthétique. De plus, la conception innovante de la lentille sans bord s'adapte à la plupart des décors intérieurs, grâce à son aspect propre et soigné. Vous pouvez également tirer parti de la gamme complète ExpertColor, qui comprend également les lampes LEDspot LV et LEDspot PAR.

Avantages

- Crée une ambiance chaleureuse et confortable
- La décoration intérieure, les meubles et les tissus sont sublimes
- Solution de rénovation simple pour une meilleure efficacité énergétique et une durabilité accrue

MASTER LEDspot ExpertColor MV

Fonctions

- Un spectre de couleurs personnalisé imite la couleur de la lumière halogène
- Conception sans bords avec superbe lentille avec prismes à angle droit
- Perception des couleurs inégalée IRC97, R9>85
- Gradation en douceur et profondeur
- Interchangeables avec des lampes halogènes GU10 à tension secteur


Application

- Hôtellerie : chambres d'hôtel, couloirs, hall d'accueil, réception, restaurants, bars, cafés
- Habitat : salle de séjour, chambres, hall d'entrée
- Commerces : halls d'exposition, vitrines, boutiques, vestiaires

Versions



Schéma dimensionnel



Product	D	C
MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 927 36D	50 mm	54 mm
MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 930 36D	50 mm	54 mm
MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 940 36D	50 mm	54 mm
MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 25D	50 mm	54 mm
MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 930 25D	50 mm	54 mm
MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 36D	50 mm	54 mm
MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 940 25D	50 mm	54 mm
MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 930 36D	50 mm	54 mm
MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 940 36D	50 mm	54 mm

MASTER LEDspot ExpertColor MV

Normes et recommandations

Classe énergétique A+

Gestion et gradation

Intensité réglable Oui

Caractéristiques électriques

Fréquence d'entrée 50 à 60 Hz

Tension (nom.) 220-240 V

Heure de démarrage (nom.) 0,5 s

Caractéristiques générales

Culot GU10

Durée de vie nominale (nom.) 40000 h

Cycle d'allumage 50000X

Photométries et Colorimétries

Indice de rendu des couleurs (nom.) 97

LLMF à la fin de la durée de vie nominale (nom.) 70 %

Matériaux et finitions

Forme de l'ampoule PAR16

Températures

Température maximale du boîtier (nom.) 80 °C

Normes et recommandations

Order Code	Full Product Name	Consommation d'énergie kWh/1 000 h
70755500	MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 927 36D	4 kWh
70757900	MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 930 36D	4 kWh
70759300	MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 940 36D	4 kWh
70761600	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 25D	6 kWh
70763000	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 930 25D	6 kWh
70765400	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 940 25D	6 kWh
70767800	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 36D	6 kWh
70769200	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 930 36D	6 kWh
70771500	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 940 36D	6 kWh

Caractéristiques électriques

Order Code	Full Product Name	Puissance équivalente	Puissance (valeur nominale)
70755500	MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 927 36D	35 W	3.9 W
70757900	MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 930 36D	35 W	3.9 W
70759300	MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 940 36D	35 W	3.9 W
70761600	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 25D	50 W	5.5 W
70763000	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 930 25D	50 W	5.5 W

Order Code	Full Product Name	Puissance équivalente	Puissance (valeur nominale)
70765400	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 940 25D	50 W	5.5 W
70767800	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 36D	50 W	5.5 W
70769200	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 930 36D	50 W	5.5 W
70771500	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 940 36D	50 W	5.5 W

Photométries et Colorimétries (1/2)

Order Code	Full Product Name	Angle d'émission du faisceau (nom.)	Code couleur	Température de couleur proximale (nom.)	Flux lumineux (nom.)
70755500	MASTER LED ExpertColor LED	36 °	927	2700 K	265 lm


MASTER LEDspot ExpertColor MV

Order Code	Full Product Name	Angle d'émission du faisceau (nom.)	Code couleur	Température de couleur proximale (nom.)	Flux lumineux (nom.)
	ExpertColor 3.9-35W GU10 927 36D				
70757900	MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 930 36D	36 °	930	3000 K	280 lm
70759300	MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 940 36D	36 °	940	4000 K	300 lm
70761600	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 25D	25 °	927	2700 K	355 lm
70763000	MASTER LED ExpertColor LED ExpertColor	25 °	930	3000 K	375 lm





Order Code	Full Product Name	Angle d'émission du faisceau (nom.)	Code couleur	Température de couleur proximale (nom.)	Flux lumineux (nom.)
	5.5-50W GU10 930 25D				
70765400	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 940 25D	25 °	940	4000 K	400 lm
70767800	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 36D	36 °	927	2700 K	355 lm
70769200	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 930 36D	36 °	930	3000 K	375 lm
70771500	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 940 36D	36 °	940	4000 K	400 lm

Photométries et Colorimétries (2/2)



Order Code	Full Product Name	Flux lumineux (nominal) (nom.)	Intensité lumineuse (nom.)
70755500	MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 927 36D	265 lm	540 cd
70757900	MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 930 36D	280 lm	560 cd
70759300	MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 940 36D	300 lm	600 cd
70761600	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 25D	355 lm	1000 cd
70763000	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 930 25D	375 lm	1000 cd
70765400	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 940 25D	400 lm	1050 cd
70767800	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 36D	355 lm	800 cd
70769200	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 930 36D	375 lm	800 cd
70771500	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 940 36D	400 lm	800 cd




MASTER LEDspot ExpertColor MV




MASTER LEDspot ExpertColor MV




Accent Diagrams




**MASTER LEDspot ExpertColor MV 35W GU10
927 36D**




**MASTER LEDspot ExpertColor MV 35W GU10
930 36D**




**MASTER LEDspot ExpertColor MV 35W GU10
940 36D**




**MASTER LEDspot ExpertColor MV 50W GU10
927 25D**



**MASTER LEDspot ExpertColor MV 50W GU10
930 25D**




**MASTER LEDspot ExpertColor MV 50W GU10
940 25D**



**MASTER LEDspot ExpertColor MV 50W GU10
927 36D**




**MASTER LEDspot ExpertColor MV 50W GU10
930 36D**



**MASTER LEDspot ExpertColor MV 50W GU10
940 36D**


MASTER LEDspot ExpertColor MV

Beam Diagrams




MASTER LEDspot ExpertColor MV 35W GU10
927 36D


MASTER LEDspot ExpertColor MV 35W GU10
930 36D



MASTER LEDspot ExpertColor MV 35W GU10
940 36D




MASTER LEDspot ExpertColor MV 50W GU10
927 25D




MASTER LEDspot ExpertColor MV 50W GU10
930 25D




MASTER LEDspot ExpertColor MV 50W GU10
940 25D



MASTER LEDspot ExpertColor MV 50W GU10
927 36D



MASTER LEDspot ExpertColor MV 50W GU10
930 36D



MASTER LEDspot ExpertColor MV 50W GU10
940 36D

MASTER LEDspot ExpertColor MV

