



Create a warm, welcoming ambience with superior quality lighting

MASTER LEDspot ExpertColor LV

MASTER LEDspot LV ExpertColor creates a warm and comfortable ambience for hospitality venues, homes and restaurants. It creates such an ambience with superior lighting that has a customized spectrum, high CRI, and deep dimming feature. The result? A beautiful lighting experience. What's more, the innovative, trimless lens design will suit almost any interior decor with its clean and neat look. In addition, you can take advantage of the full ExpertColor family, which also includes LEDspot MV and LEDspot Par lamps.

Benefits

- · Create warm and comfortable ambience
- · Interior decor, furnishings and fabrics look great
- · Hassle-free retrofit solution for greater energy efficiency and sustainability

Features


- \cdot Customized color spectrum replicates halogen light color
- · Trimless design with beautiful V-groove lens
- · Best-in-class color realization CRI97, R9<gt/>85
- $\boldsymbol{\cdot}$ Deep and smooth dimming with broad transformer compatibility
- Retrofit with low-voltage MR16 halogen lamps with GU5.3 socket

MASTER LEDspot ExpertColor LV

Application

- Hospitality: hotel guest room, corridors, lobby, reception area, restaurants, bars, cafes
- · Home: living room, bedrooms, hall way
- · Retail: exhibitions, display cabinets, shops, dressing rooms

Dimensional drawing




Product	D	С
MAS LED MR16 ExpertColor 6.7-50W 927 24D	50.5 mm	46 mm
MAS LED MR16 ExpertColor 6.7-50W 927 36D	50.5 mm	46 mm


General Information	
Cap-Base	GU5.3
Switching Cycle	50,000
Nominal lifetime	40,000 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	97
Color Code	927
LLMF At End Of Nominal Lifetime	70 %
(Nom)	
Luminous Flux	450 lm
Operating and Electrical	
Input Frequency	- Hz
Line Frequency	- Hz
Power Consumption	6.7 W
Starting Time (Nom)	0.5 s
Wattage Equivalent	50 W
Temperature	
T-Case Maximum (Nom)	92 ℃
Controls and Dimming	
Dimmable	Only with specific
	dimmers
Mechanical and Housing	
Bulb Shape	MR16

Light Technical


Order Code	Full Product Name	Beam Angle (Nom)	Luminous Intensity (Nom)
929003077008	MAS LED MR16 ExpertColor 6.7-50W 927 24D	24 degree(s)	2,200 cd
929003077308	MAS LED MR16 ExpertColor 6.7-50W 927 36D	36 degree(s)	1,350 cd


MASTER LEDspot ExpertColor LV






Accent Diagrams






Accent Diagram - MAS LED MR16 ExpertColor 6.7-50W 927 36D Accent Diagram - MAS LED MR16 ExpertColor 6.7-50W 927 24D

Beam Diagrams





Beam diagram - MAS LED MR16 ExpertColor 6.7-50W 927 24D Beam diagram - MAS LED MR16 ExpertColor 6.7-50W 927 36D



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.