



# The new generation of energy-saving LED PLL tube lighting

## CorePro LED PLL

Philips CorePro LED PLL is the ideal uplampping solution for downlights & luminaires in a wide range of general lighting applications. It integrates a LED light source into a traditional fluorescent form factor to offer superb energy savings over a lifetime that's twice as long as fluorescent alternatives.

### Benefits

- Reduced operational cost thanks to a lower energy consumption than conventional PLL lamps, as well as lower maintenance cost thanks to a two to three times longer lifetime than conventional lamps
- Simple lamp-for-lamp replacement, re-using the existing fixture without major modifications, using a similar PLL form factor
- The fastest and easiest way to upgrade existing luminaires to LED technology

### Features

- High quality of light, no flickering or stroboscopic effects
- Instant 100% light
- Choice of 3,000 K, 4,000 K & 6,500 K

### Application



- Hospitality
- Retail
- Office (stairways, corridors)
- Industrial areas

# CorePro LED PLL

## Versions



## Dimensional drawing



Product	D	D1	A1	A2	A3
CorePro LED PLL HF 24W 865 4P 2G11	37.6 mm	17 mm	453 mm	528.5 mm	535.1 mm
CorePro LED PLL HF 24W 830 4P 2G11	37.6 mm	17 mm	453 mm	528.5 mm	535.1 mm
CorePro LED PLL HF 24W 840 4P 2G11	37.6 mm	17 mm	453 mm	528.5 mm	535.1 mm

Product	D1	D2	A1	A2	A3
CorePro LED PLL HF 16.5W 840 4P 2G11	43.6 mm	23.4 mm	329.5 mm	405 mm	411.6 mm
CorePro LED PLL HF 16.5W 830 4P 2G11	43.6 mm	23.4 mm	329.5 mm	405 mm	411.6 mm

# CorePro LED PLL

## Approval and Application

Energy Efficiency Label (EEL)	A+
<b>Controls and Dimming</b>	
Dimmable	No
<b>Operating and Electrical</b>	
Voltage (Nom)	53-77 V
Starting Time (Nom)	0.5 s
<b>General Information</b>	
Cap-Base	2G11
Nominal Lifetime (Nom)	30000 h
Switching Cycle	50,000X
<b>Light Technical</b>	
Beam Angle (Nom)	160 °
Colour Rendering Index (Nom)	83
Llmf At End Of Nominal Lifetime (Nom)	70 %
<b>Mechanical and Housing</b>	
Bulb Shape	Tube, single-ended
<b>Temperature</b>	
T-Ambient (Max)	45 °C
T-Ambient (Min)	-20 °C
T-Case Maximum (Nom)	70 °C
T-Storage (Min)	-40 °C

## Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
73966200	CorePro LED PLL HF 16.5W 830 4P 2G11	20 kWh
73974700	CorePro LED PLL HF 16.5W 840 4P 2G11	20 kWh
82839700	CorePro LED PLL HF 24W 830 4P 2G11	29 kWh
82841000	CorePro LED PLL HF 24W 840 4P 2G11	29 kWh
82843400	CorePro LED PLL HF 24W 865 4P 2G11	29 kWh

## Operating and Electrical

Order Code	Full Product Name	Input Frequency	Power (Rated) (Nom)
73966200	CorePro LED PLL HF 16.5W 830 4P 2G11	39000-71000 Hz	16.5 W
73974700	CorePro LED PLL HF 16.5W 840 4P 2G11	39000-71000 Hz	16.5 W
82839700	CorePro LED PLL HF 24W 830 4P 2G11	20000-70000 Hz	24 W

Order Code	Full Product Name	Input Frequency	Power (Rated) (Nom)
82841000	CorePro LED PLL HF 24W 840 4P 2G11	20000-70000 Hz	24 W
82843400	CorePro LED PLL HF 24W 865 4P 2G11	20000-70000 Hz	24 W

## Light Technical

Order Code	Full Product Name	Correlated Colour		
		Colour Code	Temperature (Nom)	Luminous Flux (Nom)
73966200	CorePro LED PLL HF 16.5W 830 4P 2G11	830	3000 K	2000 lm
73974700	CorePro LED PLL HF 16.5W 840 4P 2G11	841	4000 K	2100 lm
82839700	CorePro LED PLL HF 24W 830 4P 2G11	830	3000 K	3200 lm

Order Code	Full Product Name	Correlated Colour		
		Colour Code	Temperature (Nom)	Luminous Flux (Nom)
82841000	CorePro LED PLL HF 24W 840 4P 2G11	841	4000 K	3400 lm
82843400	CorePro LED PLL HF 24W 865 4P 2G11	865	6500 K	3400 lm

# CorePro LED PLL

## Temperature

Order Code	Full Product Name	T-Storage (Max)
73966200	CorePro LED PLL HF 16.5W 830 4P 2G11	60 °C
73974700	CorePro LED PLL HF 16.5W 840 4P 2G11	60 °C
82839700	CorePro LED PLL HF 24W 830 4P 2G11	65 °C
82841000	CorePro LED PLL HF 24W 840 4P 2G11	65 °C
82843400	CorePro LED PLL HF 24W 865 4P 2G11	65 °C

