



A flexible and affordable retail toolbox

GreenSpace Accent Pendant

Thanks to the GreenSpace Accent family, retailers and building operators can now easily make the switch from CDM to LED and enjoy the benefits of Philips PerfectAccent light quality as well as significant energy savings – all for a reasonable initial investment. GreenSpace Accent Pendant can be installed on a regular 3C adaptor or onto a ceiling mount with track interface for quick and easy installation. The cable can be cut to length to perfectly match the installation height of the luminaire. For fashion and food retailers, GreenSpace Accent Pendant is available with special light flavors and LED recipes to show the clothes and fresh food produce on offer in the very best light. Check out our Fashion and Food catalogue pages to discover more about CrispWhite, PremiumWhite, Fresh Food Meat and Fresh Food Champagne.

Benefits

- Clean and robust design
- Full retail application coverage
- Lighting flexibility beyond CDM

Features

- Driver integrated in a compact housing
- High quality of light enabled by the Philips PerfectAccent reflectors
- Light flavors for fashion and LED recipes for food included
- Cable can be cut to length, and can be installed on track or ceiling

Application

- Food retail
- Fashion retail
- Hospitality

GreenSpace Accent Pendant

Specifications

Aiming possibilities from the horizontal	to °
Aiming possibilities from the vertical	to °
Ambient Temperature	+10 to +40 °C
Beam angle lightsource	120 °
Beam spread luminaire	24°, 30°, 34°, 38°
Main color of the Luminaire	Black, silver, white
Connection	Flying leads/wires (Flying leads/wires)
Dimming	No, yes
Driver	Power supply unit (Power supply unit) Power supply unit with DALI interface (Power supply unit with DALI interface)
Initial correlated color temperature	2200, 2700, 3000, 4000 K
Initial input power	14.4, 16.6, 22.5, 23.5, 25.5, 27, 30, 32.5, 41 W
Initial LED luminaire efficacy	66.66666666666667, 70.37037037037037, 83.07692307692308, 84.44444444444444, 90, 95.1219512195122, 102.40963855421685, 105.88235294117646, 110.63829787234043, 114.58333333333333, 114.8936170212766, 118.05555555555556, 119.14893617021276, 125 lm/W
Initial luminous flux	1650, 1700, 1800, 1900, 2600, 2700, 2800, 3900 lm

Input frequency	50 to 60 Hz
Input voltage	220 to 240 V
Inrush current (A)	18.6, 20.4 A
Light source color	-, 827 warm white, 830 warm white, 840 neutral white, crisp white, fresh meat, premium white with CRI ≥90, rosé
Light source replaceable	No
Material	Bracket:
Material	Gear box:
Material	Housing: aluminum
Material	Reflector: polycarbonate aluminum coated
Median Useful Life	70000 h
L70B50	
Median Useful Life	50000 h
L80B50	
Median Useful Life	25000 h
L90B50	
Optic	Medium beam, very wide beam, wide beam
Optical cover	Polycarbonate
Tilt angle housing	Standard tilt angle posttop: Standard tilt angle side entry:
Type	PT320C PT320T
Warranty period	5 years

Versions



GSA Pendant Track Mounted



GSA Pendant Track Mounted



GSA Pendant Ceiling Mounted

GreenSpace Accent Pendant

Product details



GreenSpace_Accent_Pendant-PT320T_C-1DPP.tif



GreenSpace_Accent_Pendant-PT320T_C-2DPP.tif



GreenSpace_Accent_Pendant PT320T_BBS-DPP.TIF



GreenSpace_Accent_Pendant PT320T-DPP.TIF



GreenSpace_Accent_Pendant PT320T_RPS-DPP.TIF



GreenSpace_Accent_Pendant PT320T_BCS-DPP.TIF



GreenSpace_Accent_Pendant PT320T_SOS-DPP.TIF



GreenSpace_Accent_Pendant-PT320C-DPP.tif

GreenSpace Accent Pendant

Application Conditions

Ambient temperature range	+10 to +40 °C
Suitable for random switching	Yes

Approval and Application

Mech. impact protection code	IK02
Ingress protection code	IP20

Operating and Electrical

Input Voltage	220 to 240 V
---------------	--------------

General Information

CE mark	CE mark
Protection class IEC	Safety class I
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 5 s
Light source replaceable	No
Number of gear units	1 unit
Service tag	Yes

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Application Conditions

Order Code	Full Product Name	Maximum dim level
910500465122	PT320T LED17S/827 PSU MB WH	-
910500465124	PT320C LED17S/840 PSU MB WH	-
910500465130	PT320T LED27S/830 PSD-VLC MB WH	1%
910500465273	PT320T LED19S/ROSE PSD-VLC WB WH	-
910500465702	PT320T LED27S/PC930 PSU MB WH	-
910500465703	PT320T LED39S/PC930 PSU MB WH	-
910500465123	PT320T LED17S/830 PSU MB BK	-
910500465125	PT320C LED17S/PW930 PSU WB BK	-
910500465128	PT320T LED19S/FMT PSD-VLC VWB BK	1%
910500465129	PT320T LED27S/827 PSD-VLC MB BK	1%
910500465131	PT320T LED27S/840 PSD-VLC MB BK	1%
910500465274	PT320T LED27S/ROSE PSU WB BK	-
910500465126	PT320C LED17S/CRW PSU WB SI	-
910500465132	PT320T LED27S/PW930 PSD-VLC WB SI	1%

Controls and Dimming

Order Code	Full Product Name	Dimmable
910500465122	PT320T LED17S/827 PSU MB WH	No
910500465124	PT320C LED17S/840 PSU MB WH	No
910500465130	PT320T LED27S/830 PSD-VLC MB WH	Yes
910500465273	PT320T LED19S/ROSE PSD-VLC WB WH	Yes
910500465702	PT320T LED27S/PC930 PSU MB WH	No
910500465703	PT320T LED39S/PC930 PSU MB WH	No
910500465123	PT320T LED17S/830 PSU MB BK	No

Order Code	Full Product Name	Dimmable
910500465125	PT320C LED17S/PW930 PSU WB BK	No
910500465128	PT320T LED19S/FMT PSD-VLC VWB BK	Yes
910500465129	PT320T LED27S/827 PSD-VLC MB BK	Yes
910500465131	PT320T LED27S/840 PSD-VLC MB BK	Yes
910500465274	PT320T LED27S/ROSE PSU WB BK	No
910500465126	PT320C LED17S/CRW PSU WB SI	No
910500465132	PT320T LED27S/PW930 PSD-VLC WB SI	Yes

General Information (1/2)

Order Code	Full Product Name	Beam angle of light			
		source	Cap-Base	Optical cover/lens type	Gear
910500465122	PT320T LED17S/827 PSU MB WH	120 °	-	Polymethyl methacrylate bowl/cover	-
910500465124	PT320C LED17S/840 PSU MB WH	120 °	-	Polymethyl methacrylate bowl/cover	-

Order Code	Full Product Name	Beam angle of light			
		source	Cap-Base	Optical cover/lens type	Gear
910500465130	PT320T LED27S/830 PSD-VLC MB WH	120 °	-	Polymethyl methacrylate bowl/cover	-
910500465273	PT320T LED19S/ROSE PSD-VLC WB WH	-	-	-	-

GreenSpace Accent Pendant

Order Code	Full Product Name	Beam angle of light source	Cap-Base	Optical cover/lens type	Gear
910500465702	PT320T LED27S/ PC930 PSU MB WH	120 °	-	Polymethyl methacrylate bowl/cover	-
910500465703	PT320T LED39S/ PC930 PSU MB WH	120 °	-	Polymethyl methacrylate bowl/cover	-
910500465123	PT320T LED17S/830 PSU MB BK	120 °	-	Polymethyl methacrylate bowl/cover	-
910500465125	PT320C LED17S/ PW930 PSU WB BK	120 °	-	Polymethyl methacrylate bowl/cover	-
910500465128	PT320T LED19S/FMT PSD-VLC VWB BK	120 °	-	Polymethyl methacrylate bowl/cover	-

Order Code	Full Product Name	Beam angle of light source	Cap-Base	Optical cover/lens type	Gear
910500465129	PT320T LED27S/827 PSD-VLC MB BK	120 °	-	Polymethyl methacrylate bowl/cover	-
910500465131	PT320T LED27S/840 PSD-VLC MB BK	120 °	-	Polymethyl methacrylate bowl/cover	-
910500465274	PT320T LED27S/ ROSE PSU WB BK	-	-	-	-
910500465126	PT320C LED17S/CRW PSU WB SI	120 °	-	Polymethyl methacrylate bowl/cover	-
910500465132	PT320T LED27S/ PW930 PSD-VLC WB SI	120 °	-	Polymethyl methacrylate bowl/cover	-

General Information (2/2)

Order Code	Full Product Name	Optic type	Product Family Code
910500465122	PT320T LED17S/827 PSU MB WH	Medium beam	PT320T
910500465124	PT320C LED17S/840 PSU MB WH	Medium beam	PT320C
910500465130	PT320T LED27S/830 PSD-VLC MB WH	Medium beam	PT320T
910500465273	PT320T LED19S/ROSE PSD-VLC WB WH	Wide beam	PT320T
910500465702	PT320T LED27S/PC930 PSU MB WH	Wide beam	PT320T
910500465703	PT320T LED39S/PC930 PSU MB WH	Wide beam	PT320T
910500465123	PT320T LED17S/830 PSU MB BK	Medium beam	PT320T
910500465125	PT320C LED17S/PW930 PSU WB BK	Wide beam	PT320C

Order Code	Full Product Name	Optic type	Product Family Code
910500465128	PT320T LED19S/FMT PSD-VLC VWB BK	Very wide beam	PT320T
910500465129	PT320T LED27S/827 PSD-VLC MB BK	Medium beam	PT320T
910500465131	PT320T LED27S/840 PSD-VLC MB BK	Medium beam	PT320T
910500465274	PT320T LED27S/ROSE PSU WB BK	Wide beam	PT320T
910500465126	PT320C LED17S/CRW PSU WB SI	Wide beam	PT320C
910500465132	PT320T LED27S/PW930 PSD-VLC WB SI	Wide beam	PT320T

Initial Performance (IEC Compliant) (1/2)

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy
910500465122	PT320T LED17S/ 827 PSU MB WH	(0.46, 0.41) SDCM<3	2700 K	≥80	114.58333333333333 lm/W
910500465124	PT320C LED17S/ 840 PSU MB WH	(0.38, 0.38) SDCM<3	4000 K	≥80	125 lm/W
910500465130	PT320T LED27S/ 830 PSD-	(0.43, 0.40) SDCM<3	3000 K	≥80	114.8936170212766 lm/W

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy
	VLC MB WH				
910500465273	PT320T LED19S/ ROSE PSD- VLC WB WH	(0.45, 0.38) SDCM <3	2200 K	≥80	84.44444444444444 lm/W
910500465702	PT320T LED27S/ PC930 PSU MB WH	(0.42, 0.39) SDCM<3	3000 K	≥90	90 lm/W

GreenSpace Accent Pendant

Order Code	Full Product		Init. Corr.	Init. Color	
	Name	Initial chromaticity	Color Temperature	Rendering Index	Initial LED luminaire efficacy
910500465703	PT320T LED39S/PC930 PSU MB WH	(0.42, 0.39)	3000 K	≥90	95.1219512195122 lm/W
910500465123	PT320T LED17S/830 PSU MB BK	(0.43, 0.40)	3000 K	≥80	118.05555555555556 lm/W
910500465125	PT320C LED17S/PW930 PSU WB BK	(0.42, 0.39)	3000 K	≥90	102.40963855421685 lm/W
910500465128	PT320T LED19S/FMT PSD-VLC VWB BK	(0.40, 0.33)	3000 K	≥85	70.37037037037037 lm/W
910500465129	PT320T LED27S/827 PSD-	(0.46, 0.41)	2700 K	≥80	110.63829787234043 lm/W

Order Code	Full Product		Init. Corr.	Init. Color	
	Name	Initial chromaticity	Color Temperature	Rendering Index	Initial LED luminaire efficacy
	VLC MB BK				
910500465131	PT320T LED27S/840 PSD-VLC MB BK	(0.38, 0.38)	4000 K	≥80	119.14893617021276 lm/W
910500465274	PT320T LED27S/ROSE PSU WB BK	(0.45, 0.38)	2200 K	≥80	83.07692307692308 lm/W
910500465126	PT320C LED17S/CRW PSU WB SI	(0.43, 0.40)	3000 K	≥95	66.66666666666667 lm/W
910500465132	PT320T LED27S/PW930 PSD-VLC MB SI	(0.42, 0.39)	3000 K	≥90	105.88235294117646 lm/W

Initial Performance (IEC Compliant) (2/2)

Order Code	Full Product Name	Initial luminous flux	Initial input power
910500465122	PT320T LED17S/827 PSU MB WH	1650 lm	14.4 W
910500465124	PT320C LED17S/840 PSU MB WH	1800 lm	14.4 W
910500465130	PT320T LED27S/830 PSD-VLC MB WH	2700 lm	23.5 W
910500465273	PT320T LED19S/ROSE PSD-VLC WB WH	1900 lm	22.5 W
910500465702	PT320T LED27S/PC930 PSU MB WH	2700 lm	30 W
910500465703	PT320T LED39S/PC930 PSU MB WH	3900 lm	41 W
910500465123	PT320T LED17S/830 PSU MB BK	1700 lm	14.4 W
910500465125	PT320C LED17S/PW930 PSU WB BK	1700 lm	16.6 W

Order Code	Full Product Name	Initial luminous flux	Initial input power
910500465128	PT320T LED19S/FMT PSD-VLC VWB BK	1900 lm	27 W
910500465129	PT320T LED27S/827 PSD-VLC MB BK	2600 lm	23.5 W
910500465131	PT320T LED27S/840 PSD-VLC MB BK	2800 lm	23.5 W
910500465274	PT320T LED27S/ROSE PSU WB BK	2700 lm	32.5 W
910500465126	PT320C LED17S/CRW PSU WB SI	1700 lm	25.5 W
910500465132	PT320T LED27S/PW930 PSD-VLC WB SI	2700 lm	25.5 W

Mechanical and Housing

Order Code	Full Product Name	Color
910500465122	PT320T LED17S/827 PSU MB WH	White
910500465124	PT320C LED17S/840 PSU MB WH	White
910500465130	PT320T LED27S/830 PSD-VLC MB WH	White

Order Code	Full Product Name	Color
910500465273	PT320T LED19S/ROSE PSD-VLC WB WH	White
910500465702	PT320T LED27S/PC930 PSU MB WH	White
910500465703	PT320T LED39S/PC930 PSU MB WH	White

GreenSpace Accent Pendant

Order Code	Full Product Name	Color	Order Code	Full Product Name	Color
910500465123	PT320T LED17S/830 PSU MB BK	Black	910500465131	PT320T LED27S/840 PSD-VLC MB BK	Black
910500465125	PT320C LED17S/PW930 PSU WB BK	Black	910500465274	PT320T LED27S/ROSE PSU WB BK	Black
910500465128	PT320T LED19S/FMT PSD-VLC VWB BK	Black	910500465126	PT320C LED17S/CRW PSU WB SI	Silver
910500465129	PT320T LED27S/827 PSD-VLC MB BK	Black	910500465132	PT320T LED27S/PW930 PSD-VLC WB SI	Silver

