



# Coreline Bollard

## Coreline Bollard

Coreline Bollard is a professional bollard that will guide people at night time and will integrate very well in most urban landscape thanks to its discreet design.

### Benefits

- Comfortable light
- Easy to install
- Saves energy compared to conventional lamps

### Features

- 1000lm system output
- 1m height
- IP65 / IK10
- Available in Warm White and Neutral White
- Available with symmetric and asymmetric optic
- Ground section anchor accessory

### Application

- Open spaces: Parks, squares, playgrounds
- Foot and cycle paths
- Car parks

### Specifications

Ambient Temperature	-40 to +50 °C
Main colour of the luminaire	Dark gray
Driver	Power supply unit (PSU)
Initial correlated colour temperature	3000 K, 4000 K
Initial input power	12 W, 13 W
Initial LED luminaire efficacy	80, 85 lm/W

Initial luminous flux	1000 lm
Input frequency	50 or 60 Hz
Input voltage	220-240 V
Light source colour	Neutral white, warm white
Light source replaceable	No
Optic	Asymmetrical, symmetrical
Optical cover	Polycarbonate

# Coreline Bollard

## Versions



LED Module 1000 lm

Approval and application	
Mech. impact protection code	IK10
Surge protection (common/differential)	6/8 kV
Controls and dimming	
Dimmable	No
General information	
CE mark	CE mark
Optical cover/lens type	O
Driver included	Yes
Flammability mark	NO
Lamp family code	LED10
Light source replaceable	No
Number of gear units	1 unit
Number of light sources	1
Initial performance (IEC compliant)	
Init. Colour rendering index	>80
Initial luminous flux	1000 lm
Light technical	
Standard tilt angle side entry	-
Standard tilt angle post-top	-
Upward light output ratio	50
Mechanical and housing	
Colour	Dark gray

## General information

Order Code	Full Product Name	Luminaire light	Light source	Optic type
		beam spread	colour	
38375600	BCP155 LED100/WW PSU 220-240V A 7043	135°	Warm white	Asymmetrical
38376300	BCP155 LED100/NW PSU 220-240V A 7043	135°	Neutral white	Asymmetrical
38377000	BCP155 LED100/WW PSU 220-240V S 7043	360°	Warm white	Symmetrical
38378700	BCP155 LED100/NW PSU 220-240V S 7043	360°	Neutral white	Symmetrical

## Initial performance (IEC compliant)

Order Code	Full Product Name	Init. Corr. Colour Temperature
38375600	BCP155 LED100/WW PSU 220-240V A 7043	3000 K
38376300	BCP155 LED100/NW PSU 220-240V A 7043	4000 K

Order Code	Full Product Name	Init. Corr. Colour Temperature
38377000	BCP155 LED100/WW PSU 220-240V S 7043	3000 K
38378700	BCP155 LED100/NW PSU 220-240V S 7043	4000 K

