



Coreline Bollard

Coreline Bollard

Coreline Bollard is a professional bollard that will guide people at night time and will integrate very well in most urban landscape thanks to its discreet design.

Benefits

- Comfortable light
- Easy to install
- Saves energy compared to conventional lamps

Features

- 1000lm system output
- 1m height
- IP65 / IK10
- Available in Warm White and Neutral White
- Available with symmetric and asymmetric optic
- Ground section anchor accessory

Application

- Open spaces: Parks, squares, playgrounds
- Foot and cycle paths
- Parking lots

Specifications

Ambient Temperature	-40 to +50 °C
Main color of the Luminaire	Dark gray
Driver	Power supply unit (Power supply unit)
Initial correlated color temperature	3000, 4000 K
Initial input power	12, 13 W
Initial LED luminaire efficacy	80, 85 lm/W

Initial luminous flux	1000 lm
Input frequency	50 or 60 Hz
Input voltage	220-240 V
Light source color	Neutral white, warm white
Light source replaceable	No
Optic	Asymmetrical, symmetrical
Optical cover	Polycarbonate

Coreline Bollard

Versions



LED Module 1000 lm

Accessories



Ordercode 912401483113

Approval and Application

Mech. impact protection code	IK10
Surge Protection (Common/Differential)	6/8 kV

Controls and Dimming

Dimmable	No
----------	----

General Information

CE mark	CE mark
Optical cover/lens type	Opal
Driver included	Yes
Flammability mark	-
Lamp family code	LED10
Light source replaceable	No
Number of gear units	1 unit
Number of light sources	1 pc

Initial Performance (IEC Compliant)

Init. Color Rendering Index	>80
Initial luminous flux	1000 lm

Light Technical

Standard tilt angle side entry	-
Standard tilt angle posttop	-
Upward light output ratio	50

Mechanical and Housing

Color	Dark gray
-------	-----------

General Information

Order Code	Full Product Name	Luminaire light		
		beam spread	Light source color	Optic type
912401483109	BCP155 LED100/WW PSU 220-240V A 7043	135°	Warm white	Asymmetrical
912401483110	BCP155 LED100/NW PSU 220-240V A 7043	135°	Neutral white	Asymmetrical
912401483111	BCP155 LED100/WW PSU 220-240V S 7043	360°	Warm white	Symmetrical
912401483112	BCP155 LED100/NW PSU 220-240V S 7043	360°	Neutral white	Symmetrical

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Color Temperature
912401483109	BCP155 LED100/WW PSU 220-240V A 7043	3000 K
912401483110	BCP155 LED100/NW PSU 220-240V A 7043	4000 K

Order Code	Full Product Name	Init. Corr. Color Temperature
912401483111	BCP155 LED100/WW PSU 220-240V S 7043	3000 K
912401483112	BCP155 LED100/NW PSU 220-240V S 7043	4000 K

