



Greenperform Cleanroom Teardrop G2, provide you a safe, reliable, comfortable cleanroom lighting experience.

Greenperform Cleanroom Teardrop G2

Greenperform Cleanroom Teardrop G2 is an optimized cleanroom lighting fixture. With its slim, compact and smooth housing design, Teardrop G2 maximally avoids dust attached in cleanroom application, and can meet the classification 10 ~1000. CR388C series products also provide excellent lighting quality, substantial energy saving and reliable quality of maintenance free. Both white and yellow lighting solutions are available, Teardrop G2 is your excellent option for both new projects and retrofit projects.

Benefits

- · Compact, slim, robust housing, avoid the dust attaching
- · soft, unifom lighting output, low flicking, friendly to human eyes
- long lifetime, low energy consumption, delivers energy saving and set you free from product maintenance
- · Easy installation, saving your labor cost

Greenperform Cleanroom Teardrop G2


Features


- IP40, IK03, dural extrusion housing, cleanroom classification 10 1000
- · CRI>80, SDCM<5, anti UV Polycarbonate optical diffuser
- 50K hours lifetime @ L70B50
- Surface& ceiling installation, track kits available for T-bar installation

Application

- · Integrated circuit (VLS) manufacturing
- Fine mechanical components, aviation instruments, hydraulic parts
- · Critical optical devices, optical discs
- Beverage, Aseptic filling (juice, custards)
- · Food, Pharmaceutical industry
- \cdot Semiconductor manufacturing/ assembly
- etc.

Dimensional drawing





Product details



CR388C Detail Photo

Greenperform Cleanroom Teardrop G2

General Information			
Driver included	Yes		
ENEC mark	-		
Flammability mark	-		
Glow-wire test	Temperature 750		
	°C, duration 5 s		
Light source replaceable	No		
Number of gear units	1 unit		
Light Technical			
Optical cover type	Polycarbonate		
Optic type	Symmetrical		
Operating and Electrical			
Input Voltage	220 to 240 V		
Line Frequency	50 to 60 Hz		
Temperature			
Ambient temperature range	0 to +35 °C		
Mechanical and Housing			
Housing Color	White		
Approval and Application			
Protection class IEC	Safety class I		
Mech. impact protection code	IK03		
Ingress protection code	IP40		
Initial Performance (IEC Compliant)			
Initial chromaticity	SDCM<5		
Luminous flux tolerance	+/-10%		

General Information

Order Code	Full Product Name	CE mark
911401516941	CR388C LED20 Amber L120 PSU	-
911401519141	CR388C LED20 Amber L120 PSU EN	CE mark
911401516441	CR388C LED20 CW L120 PSU	-
911401516541	CR388C LED40 NW L120 PSU	-
911401516641	CR388C LED40 CW L120 PSU	-
911401516741	CR388C LED40 NW L120 PSD	-
911401519041	CR388C LED40 CW L120 PSU EN	CE mark

Light Technical (1/2)

		Beam	Correlated		
		angle of	Color	Color	Luminous
	Full Product	light	Temperature	rendering	Efficacy
Order Code	Name	source	(Nom)	index (CRI)	(rated) (Nom)
911401516941	CR388C	-	-	-	105 lm/W
	LED20 Amber				
	L120 PSU				
911401519141	CR388C	- degree(s)	-	-	105 lm/W
	LED20 Amber				
	L120 PSU EN				
911401516441	CR388C	-	6500 K	>80	125 lm/W
	LED20 CW				
	L120 PSU				
911401516541	CR388C	-	4000 K	>80	120 lm/W
	LED40 NW				
	L120 PSU				

	Full Product	Beam angle of light	Color Temperature	Color rendering	Luminous Efficacy
Order Code	Name	source	(Nom)	index (CRI)	(rated) (Nom)
911401516641	CR388C LED40 CW	-	6500 K	>80	120 lm/W
	L120 PSU				
911401516741	CR388C	-	4000 K	>80	190 lm/W
	LED40 NW				
	L120 PSD				
911401519041	CR388C	- degree(s)	6500 K	>80	120 lm/W
	LED40 CW				
	L120 PSU EN				

Light Technical (2/2)

Greenperform Cleanroom Teardrop G2

Order Code	Full Product Name	Luminous Flux
911401516941	CR388C LED20 Amber L120 PSU	2,200 lm
911401519141	CR388C LED20 Amber L120 PSU EN	2,200 lm
911401516441	CR388C LED20 CW L120 PSU	2,000 lm
911401516541	CR388C LED40 NW L120 PSU	3,900 lm

Order Code	Full Product Name	Luminous Flux
911401516641	CR388C LED40 CW L120 PSU	3,900 lm
911401516741	CR388C LED40 NW L120 PSD	4,500 lm
911401519041	CR388C LED40 CW L120 PSU EN	3,900 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401516941	CR388C LED20 Amber L120 PSU	21 W
911401519141	CR388C LED20 Amber L120 PSU EN	21 W
911401516441	CR388C LED20 CW L120 PSU	16 W
911401516541	CR388C LED40 NW L120 PSU	32 W

Order Code	Full Product Name	Power Consumption
911401516641	CR388C LED40 CW L120 PSU	32 W
911401516741	CR388C LED40 NW L120 PSD	39 W
911401519041	CR388C LED40 CW L120 PSU EN	32 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401516941	CR388C LED20 Amber L120 PSU	No
911401519141	CR388C LED20 Amber L120 PSU EN	No
911401516441	CR388C LED20 CW L120 PSU	No
911401516541	CR388C LED40 NW L120 PSU	No

Order Code	Full Product Name	Dimmable
911401516641	CR388C LED40 CW L120 PSU	No
911401516741	CR388C LED40 NW L120 PSD	Yes
911401519041	CR388C LED40 CW L120 PSU EN	No

Over Time Performance (IEC Compliant)

		Median useful life	Median useful life
Order Code	Full Product Name	L80B50	L90B50
911401516941	CR388C LED20 Amber L120 PSU	45,000 hour(s)	40,000 hour(s)
911401519141		45,000 hour(s)	40,000 hour(s)
	EN		
911401516441	CR388C LED20 CW L120 PSU	45,000 hour(s)	40,000 hour(s)

		Median useful life	Median useful life
Order Code	Full Product Name	L80B50	L90B50
911401516541	CR388C LED40 NW L120 PSU	-	-
911401516641	CR388C LED40 CW L120 PSU	45,000 hour(s)	40,000 hour(s)
911401516741	CR388C LED40 NW L120 PSD	45,000 hour(s)	40,000 hour(s)
911401519041	CR388C LED40 CW L120 PSU EN	45,000 hour(s)	40,000 hour(s)

Application Conditions

Order Code	Full Product Name	Maximum dim level
911401516941	CR388C LED20 Amber L120 PSU	Not applicable
911401519141	CR388C LED20 Amber L120 PSU EN	Not applicable
911401516441	CR388C LED20 CW L120 PSU	Not applicable
911401516541	CR388C LED40 NW L120 PSU	Not applicable

Order Code	Full Product Name	Maximum dim level
911401516641	CR388C LED40 CW L120 PSU	Not applicable
911401516741	CR388C LED40 NW L120 PSD	1%
911401519041	CR388C LED40 CW L120 PSU EN	Not applicable



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.