



The most cost-effective outdoor spot light with better efficient and performance

UniPoint

Our UniPoint is designed to produce both general and accent lighting while concealing the body of the device, allowing only the light to be exposed. This design can be used to change the surroundings by adding subtle or dramatic contrasting effects. It also includes exclusive features such as energy efficiency, chromatic quality and miniaturisation. We guarantee extreme reliability and high level of resistance to adverse weather conditions and vandalism

Benefits

- In stylish and very compact design
- Price point versus PHILIPS standards
- Effortless and flexible installation
- Customising for you

Features

- High quality LED
- Different choice of light source and beam angles
- Die-cast aluminium housing + dark grey sand coating to ensure anticorrosion
- Structural waterproof technology
- IP66
- IK06
- Quality and reliability in line with all regulations

Application

- Buildings
- Statues
- Columns
- Pillars
- Eaves

Versions



Approval and Application	
Mech. impact protection code	IK06
Controls and Dimming	
Dimmable	No
General Information	
CE mark	CE mark
Optical cover/lens type	GB
Driver included	No
Light source replaceable	No
Initial Performance (IEC Compliant)	
Init. Colour Rendering Index	>75
Light Technical	
Standard tilt angle side entry	-
Standard tilt angle posttop	-
Mechanical and Housing	
Colour	Dark Grey

General Information

Order Code	Full Product Name	Luminaire light		
		beam spread	Light source colour	Optic type
911401711442	BGP312 1LED 2700K NB GG	10°	827 warm white	Narrow beam angle 10°
911401711452	BGP312 1LED 2700K MB GG	25°	827 warm white	Medium beam angle 25°
911401711462	BGP312 1LED 2700K WB GG	40°	827 warm white	Wide beam angle 42°
911401711472	BGP312 1LED 3000K NB GG	10°	830 warm white	Narrow beam angle 10°
911401711482	BGP312 1LED 3000K MB GG	25°	830 warm white	Medium beam angle 25°
911401711492	BGP312 1LED 3000K WB GG	40°	830 warm white	Wide beam angle 42°
911401711502	BGP312 1LED 4000K NB GG	10°	840 neutral white	Narrow beam angle 10°
911401711512	BGP312 1LED 4000K MB GG	25°	840 neutral white	Medium beam angle 25°
911401711522	BGP312 1LED 4000K WB GG	40°	840 neutral white	Wide beam angle 42°
911401711532	BGP312 3LED 2700K NB GG	10°	827 warm white	Narrow beam angle 10°
911401711542	BGP312 3LED 2700K MB GG	25°	827 warm white	Medium beam angle 25°
911401711552	BGP312 3LED 2700K WB GG	40°	827 warm white	Wide beam angle 42°
911401711562	BGP312 3LED 3000K NB GG	10°	830 warm white	Narrow beam angle 10°
911401711572	BGP312 3LED 3000K MB GG	25°	830 warm white	Medium beam angle 25°
911401711582	BGP312 3LED 3000K WB GG	40°	830 warm white	Wide beam angle 42°
911401711592	BGP312 3LED 4000K NB GG	10°	840 neutral white	Narrow beam angle 10°
911401711602	BGP312 3LED 4000K MB GG	25°	840 neutral white	Medium beam angle 25°
911401711612	BGP312 3LED 4000K WB GG	40°	840 neutral white	Wide beam angle 42°
911401711622	BGP312 5LED 2700K NB GG	10°	827 warm white	Narrow beam angle 10°
911401711632	BGP312 5LED 2700K MB GG	25°	827 warm white	Medium beam angle 25°
911401711642	BGP312 5LED 2700K WB GG	40°	827 warm white	Wide beam angle 42°
911401711652	BGP312 5LED 3000K NB GG	10°	830 warm white	Narrow beam angle 10°
911401711662	BGP312 5LED 3000K MB GG	25°	830 warm white	Medium beam angle 25°
911401711672	BGP312 5LED 3000K WB GG	40°	830 warm white	Wide beam angle 42°
911401711682	BGP312 5LED 4000K NB GG	10°	840 neutral white	Narrow beam angle 10°
911401711692	BGP312 5LED 4000K MB GG	25°	840 neutral white	Medium beam angle 25°
911401711702	BGP312 5LED 4000K WB GG	40°	840 neutral white	Wide beam angle 42°

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Colour Temperature	Initial luminous flux
911401711442	BGP312 1LED 2700K NB GG	2700 K	120 lm
911401711452	BGP312 1LED 2700K MB GG	2700 K	120 lm
911401711462	BGP312 1LED 2700K WB GG	2700 K	120 lm
911401711472	BGP312 1LED 3000K NB GG	3000 K	120 lm
911401711482	BGP312 1LED 3000K MB GG	3000 K	120 lm
911401711492	BGP312 1LED 3000K WB GG	3000 K	120 lm
911401711502	BGP312 1LED 4000K NB GG	4000 K	120 lm
911401711512	BGP312 1LED 4000K MB GG	4000 K	120 lm
911401711522	BGP312 1LED 4000K WB GG	4000 K	120 lm
911401711532	BGP312 3LED 2700K NB GG	2700 K	330 lm
911401711542	BGP312 3LED 2700K MB GG	2700 K	330 lm
911401711552	BGP312 3LED 2700K WB GG	2700 K	330 lm
911401711562	BGP312 3LED 3000K NB GG	3000 K	330 lm
911401711572	BGP312 3LED 3000K MB GG	3000 K	330 lm

Order Code	Full Product Name	Init. Corr. Colour Temperature	Initial luminous flux
911401711582	BGP312 3LED 3000K WB GG	3000 K	330 lm
911401711592	BGP312 3LED 4000K NB GG	4000 K	330 lm
911401711602	BGP312 3LED 4000K MB GG	4000 K	330 lm
911401711612	BGP312 3LED 4000K WB GG	4000 K	330 lm
911401711622	BGP312 5LED 2700K NB GG	2700 K	595 lm
911401711632	BGP312 5LED 2700K MB GG	2700 K	595 lm
911401711642	BGP312 5LED 2700K WB GG	2700 K	595 lm
911401711652	BGP312 5LED 3000K NB GG	3000 K	595 lm
911401711662	BGP312 5LED 3000K MB GG	3000 K	595 lm
911401711672	BGP312 5LED 3000K WB GG	3000 K	595 lm
911401711682	BGP312 5LED 4000K NB GG	4000 K	595 lm
911401711692	BGP312 5LED 4000K MB GG	4000 K	595 lm
911401711702	BGP312 5LED 4000K WB GG	4000 K	595 lm

