



The most cost-effective outdoor spot light with better efficient and performance

UniPoint

Our UniPoint is designed to produce both general and accent lighting while concealing the body of the device, allowing only the light to be exposed. This design can be used to change the surroundings by adding subtle or dramatic contrasting effects. It also includes exclusive features such as energy efficiency, chromatic quality and miniaturization. We guarantee extreme reliability and high level of resistance to adverse weather conditions and vandalism

Benefits

- In stylish and very compact design
- Price point versus PHILIPS standards
- Effortless and flexible installation
- Customizing for you

Features

- High quality LED
- Different choice of light source and beam angles
- Die-cast aluminum housing + dark grey sand coating to ensure anticorrosion
- Structural waterproof technology
- IP66
- IK06
- Quality and reliability in line with all regulations

Application

- Buildings
- Statues
- Columns
- Pillars
- Eaves

Versions



Unipoint BGP312 3LED

Approval and Application

Mech. impact protection code	IK06
------------------------------	------

Controls and Dimming

Dimmable	No
----------	----

General Information

CE mark	CE mark
Light source color	830 warm white
Optical cover/lens type	GB
Driver included	No
Light source replaceable	No

Initial Performance (IEC Compliant)

Init. Corr. Color Temperature	3000 K
Init. Color Rendering Index	>75
Initial luminous flux	330 lm

Light Technical

Standard tilt angle side entry	-
Standard tilt angle posttop	-

Mechanical and Housing

Color	Dark gray
-------	-----------

General Information

Order Code	Full Product Name	Luminaire light beam spread	Optic type
911401711562	BGP312 3LED 3000K NB GG	10°	Narrow beam angle 10°
911401711582	BGP312 3LED 3000K WB GG	40°	Wide beam angle 42°

