PHILIPS

Lighting



# LED wall washer lighting fixture- Generation 3

## UNIstrip G3

UNI strip G3 is a LED wall washer lighting fixture designed for architectural lighting applications. UNIstrip G3 offers reliable quality and outstanding performance.

### Benefits

- Low investment cost
- Long term outdoor applications with robust design
- Powerful output with good light quality to ensure the final lighting effect

### Features

- White Mono with CCT 2700K/3000K/4000K
- Reliable waterproof with protective vents, IP66
- Various beam angle options: 15º x55º and 45º
- High efficacy optical and electrical design, up to 100lm/W (4000K)

### Application

- Building facade
- Bridge
- Municipal infrastructure

# UNIstrip G3

## Versions



BCP280 G3

| Approval and Application | |
|---|---|
| Mech. impact protection code | IK06 |
| **General Information** | |
| CE mark | CE mark |
| Optical cover/lens type | ACC |
| Driver included | No |
| Flammability mark | F |
| Light source replaceable | No |
| Number of gear units | 1 unit |
| **Initial Performance (IEC Compliant)** | |
| Init. Colour Rendering Index | 80 |
| **Light Technical** | |
| Standard tilt angle side entry | - |
| Standard tilt angle posttop | - |
| **Mechanical and Housing** | |
| Colour | Aluminum and black |

## Application Conditions

| Order Code | Full Product Name | Maximum dim level |
|---|---|---|
| 911401622104 | BCP280 G3 5LEDHP/2700 L300 24V W DMX | 0% (digital) |
| 911401622204 | BCP280 G3 5LEDHP/4000 L300 24V W DMX | 0% (digital) |
| 911401622304 | BCP280 G3 5LEDHP/2700 L300 24V A DMX | 0% (digital) |
| 911401622404 | BCP280 G3 20LEDHP/3000 L1200 24V W DMX | 0% (digital) |
| 911401622504 | BCP280 G3 5LEDHP/4000 L300 24V W | Not applicable |
| 911401622604 | BCP280 G3 20LEDHP/2700 L1200 24V W DMX | 0% (digital) |
| 911401622704 | BCP280 G3 5LEDHP/2700 L300 24V W | Not applicable |
| 911401622804 | BCP280 G3 20LEDHP/3000 L1200 24V A DMX | 0% (digital) |
| 911401622904 | BCP280 G3 20LEDHP/2700 L1200 24V A | Not applicable |
| 911401623104 | BCP280 G3 20LEDHP/2700 L1200 24V W | Not applicable |
| 911401623204 | BCP280 G3 20LEDHP/2700 L1200 24V A DMX | 0% (digital) |
| 911401623304 | BCP280 G3 20LEDHP/4000 L1200 24V A DMX | 0% (digital) |
| 911401623504 | BCP280 G3 5LEDHP/3000 L300 24V A | Not applicable |
| 911401623604 | BCP280 G3 20LEDHP/3000 L1200 24V W | Not applicable |
| 911401623704 | BCP280 G3 5LEDHP/3000 L300 24V W | Not applicable |
| 911401623804 | BCP280 G3 20LEDHP/4000 L1200 24V W DMX | 0% (digital) |
| 911401623904 | BCP280 G3 5LEDHP/3000 L300 24V A DMX | 0% (digital) |
| 911401624004 | BCP280 G3 5LEDHP/2700 L300 24V A | Not applicable |
| 911401624104 | BCP280 G3 20LEDHP/3000 L1200 24V A | Not applicable |
| 911401624204 | BCP280 G3 5LEDHP/4000 L300 24V A DMX | 0% (digital) |
| 911401624304 | BCP280 G3 5LEDHP/3000 L300 24V W DMX | 0% (digital) |

## Controls and Dimming

| Order Code | Full Product Name | Dimmable |
|---|---|---|
| 911401622104 | BCP280 G3 5LEDHP/2700 L300 24V W DMX | Yes |
| 911401622204 | BCP280 G3 5LEDHP/4000 L300 24V W DMX | Yes |
| 911401622304 | BCP280 G3 5LEDHP/2700 L300 24V A DMX | Yes |
| 911401622404 | BCP280 G3 20LEDHP/3000 L1200 24V W DMX | Yes |
| 911401622504 | BCP280 G3 5LEDHP/4000 L300 24V W | No |
| 911401622604 | BCP280 G3 20LEDHP/2700 L1200 24V W DMX | Yes |
| 911401622704 | BCP280 G3 5LEDHP/2700 L300 24V W | No |
| 911401622804 | BCP280 G3 20LEDHP/3000 L1200 24V A DMX | Yes |
| 911401622904 | BCP280 G3 20LEDHP/2700 L1200 24V A | No |
| 911401623104 | BCP280 G3 20LEDHP/2700 L1200 24V W | No |
| 911401623204 | BCP280 G3 20LEDHP/2700 L1200 24V A DMX | Yes |

| Order Code | Full Product Name | Dimmable |
|---|---|---|
| 911401623304 | BCP280 G3 20LEDHP/4000 L1200 24V A DMX | Yes |
| 911401623504 | BCP280 G3 5LEDHP/3000 L300 24V A | No |
| 911401623604 | BCP280 G3 20LEDHP/3000 L1200 24V W | No |
| 911401623704 | BCP280 G3 5LEDHP/3000 L300 24V W | No |
| 911401623804 | BCP280 G3 20LEDHP/4000 L1200 24V W DMX | Yes |
| 911401623904 | BCP280 G3 5LEDHP/3000 L300 24V A DMX | Yes |
| 911401624004 | BCP280 G3 5LEDHP/2700 L300 24V A | No |
| 911401624104 | BCP280 G3 20LEDHP/3000 L1200 24V A | No |
| 911401624204 | BCP280 G3 5LEDHP/4000 L300 24V A DMX | Yes |
| 911401624304 | BCP280 G3 5LEDHP/3000 L300 24V W DMX | Yes |

## General Information

| Order Code | Full Product Name | Light source colour | Optic type |
|---|---|---|---|
| 911401622104 | BCP280 G3 5LEDHP/2700 L300 24V W DMX | Warm white | Wide beam angle 45° |
| 911401622204 | BCP280 G3 5LEDHP/4000 L300 24V W DMX | Neutral white | Wide beam angle 45° |
| 911401622304 | BCP280 G3 5LEDHP/2700 L300 24V A DMX | Warm white | - |
| 911401622404 | BCP280 G3 20LEDHP/3000 L1200 24V W DMX | Warm white | Wide beam angle 45° |
| 911401622504 | BCP280 G3 5LEDHP/4000 L300 24V W | Neutral white | Wide beam angle 45° |
| 911401622604 | BCP280 G3 20LEDHP/2700 L1200 24V W DMX | Warm white | Wide beam angle 45° |
| 911401622704 | BCP280 G3 5LEDHP/2700 L300 24V W | Warm white | Wide beam angle 45° |
| 911401622804 | BCP280 G3 20LEDHP/3000 L1200 24V A DMX | Warm white | - |
| 911401622904 | BCP280 G3 20LEDHP/2700 L1200 24V A | Warm white | - |
| 911401623104 | BCP280 G3 20LEDHP/2700 L1200 24V W | Warm white | Wide beam angle 45° |
| 911401623204 | BCP280 G3 20LEDHP/2700 L1200 24V A DMX | Warm white | - |
| 911401623304 | BCP280 G3 20LEDHP/4000 L1200 24V A DMX | Neutral white | - |
| 911401623504 | BCP280 G3 5LEDHP/3000 L300 24V A | Warm white | - |
| 911401623604 | BCP280 G3 20LEDHP/3000 L1200 24V W | Warm white | Wide beam angle 45° |
| 911401623704 | BCP280 G3 5LEDHP/3000 L300 24V W | Warm white | Wide beam angle 45° |
| 911401623804 | BCP280 G3 20LEDHP/4000 L1200 24V W DMX | Neutral white | Wide beam angle 45° |
| 911401623904 | BCP280 G3 5LEDHP/3000 L300 24V A DMX | Warm white | - |
| 911401624004 | BCP280 G3 5LEDHP/2700 L300 24V A | Warm white | - |
| 911401624104 | BCP280 G3 20LEDHP/3000 L1200 24V A | Warm white | - |
| 911401624204 | BCP280 G3 5LEDHP/4000 L300 24V A DMX | Neutral white | - |
| 911401624304 | BCP280 G3 5LEDHP/3000 L300 24V W DMX | Warm white | Wide beam angle 45° |

## Initial Performance (IEC Compliant)

| Order Code | Full Product Name | Init. Corr. Colour Temperature | Initial luminous flux |
|---|---|---|---|
| 911401622104 | BCP280 G3 5LEDHP/2700 L300 24V W DMX | 2700 K | 780 lm |
| 911401622204 | BCP280 G3 5LEDHP/4000 L300 24V W DMX | 4000 K | 1000 lm |
| 911401622304 | BCP280 G3 5LEDHP/2700 L300 24V A DMX | 2700 K | 780 lm |
| 911401622404 | BCP280 G3 20LEDHP/3000 L1200 24V W DMX | 3000 K | 3560 lm |
| 911401622504 | BCP280 G3 5LEDHP/4000 L300 24V W | 4000 K | 1000 lm |
| 911401622604 | BCP280 G3 20LEDHP/2700 L1200 24V W DMX | 2700 K | 3120 lm |
| 911401622704 | BCP280 G3 5LEDHP/2700 L300 24V W | 2700 K | 780 lm |
| 911401622804 | BCP280 G3 20LEDHP/3000 L1200 24V A DMX | 3000 K | 3560 lm |
| 911401622904 | BCP280 G3 20LEDHP/2700 L1200 24V A | 2700 K | 3120 lm |
| 911401623104 | BCP280 G3 20LEDHP/2700 L1200 24V W | 2700 K | 3120 lm |
| 911401623204 | BCP280 G3 20LEDHP/2700 L1200 24V A DMX | 2700 K | 3120 lm |
| 911401623304 | BCP280 G3 20LEDHP/4000 L1200 24V A DMX | 4000 K | 4000 lm |
| 911401623504 | BCP280 G3 5LEDHP/3000 L300 24V A | 3000 K | 890 lm |
| 911401623604 | BCP280 G3 20LEDHP/3000 L1200 24V W | 3000 K | 3560 lm |
| 911401623704 | BCP280 G3 5LEDHP/3000 L300 24V W | 3000 K | 890 lm |
| 911401623804 | BCP280 G3 20LEDHP/4000 L1200 24V W DMX | 4000 K | 4000 lm |
| 911401623904 | BCP280 G3 5LEDHP/3000 L300 24V A DMX | 3000 K | 890 lm |
| 911401624004 | BCP280 G3 5LEDHP/2700 L300 24V A | 2700 K | 780 lm |
| 911401624104 | BCP280 G3 20LEDHP/3000 L1200 24V A | 3000 K | 3560 lm |
| 911401624204 | BCP280 G3 5LEDHP/4000 L300 24V A DMX | 4000 K | 1000 lm |
| 911401624304 | BCP280 G3 5LEDHP/3000 L300 24V W DMX | 3000 K | 890 lm |




© 2020 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.