



Miniaturized downlight with leading optical performance and great diversity

LuxSpace G4

LuxSpace Gen4 is the a new LED downlight range combining light comfort and leading performance with luxury looking

Benefits

- Visual comfort
- Multiple options for various applications
- Smart lighting

Features

- Miniaturized form factor
- High optical efficiency
- Great product diversity
- Tunable white

Application

- Office
- shopping mall
- hotel
- retail

Specifications

Mounting type	Recessed
Operating Temperature range	-20 to +40 °C
Light Source	LED module
Mains Voltage	220-240V AC / 50-60Hz
Dimming	PSU: non-dimmable PSD: Dimmable via Dali protocol WIA: Wireless control POE: Power over Ethernet
Control system input	DALI / POE /WIA
Material	Housing: die-cast aluminum
Main color of the luminaire	Black & White
Lumen maintenance at median useful life	L70 50.000h
Flicker / Pst / SVM	<4%
Luminous flux	740lm, 1000lm, 1500lm, 2000lm, 2600lm, 3400lm, 4300lm @840
Power consumption	6.6-39.7W



Luminaire efficacy	97-127 lm/W @840
Correlated color temperature - CCT	3000K, 4000K, Tunable White
Color Rendering index - CRI	80, 90
Beam angle	32°-36° 56°-63°
Reflector material	Plastic, Aluminum coated
Optic	AL coating Office compliant UGR<19 (OC)
Mechanical impact protection	IK02, IK03
Ingress protection	IP20 / IP54 (front side)
Light source replaceable	No
Driver replaceable	Yes
Overall diameter	D100,D125,D150,D200
UGR	19
Installation	recessed Fixation by means of spring fasteners

Versions








Recessed downlight DN588B D100 D125

Dimensional drawing



Dimensional drawing



General Information	
CE mark	CE mark
Driver included	Yes
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Light source replaceable	No
Number of gear units	1 unit
Light Technical	
Optical cover type	Reflector
Color rendering index (CRI)	>80
Optic type	Facetted reflector with beam angle 60°
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Temperature	
Ambient temperature range	-20 to +40 °C
Mechanical and Housing	
Housing Color	White and black
Approval and Application	
Mech. impact protection code	IK03
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Driver failure rate at 5000 h	1 %
Median useful life L80B50	50,000 hour(s)
Median useful life L90B50	21,000 hour(s)

Light Technical

		Correlated Color		
		Temperature	Luminous Efficacy	
Order Code	Full Product Name	(Nom)	(rated) (Nom)	Luminous Flux
911401549541	DN588B LED6/830 PSU C D125 WH WB WP GM	3000 K	103 lm/W	680 lm
911401549641	DN588B LED6/840 PSU C D125 WH WB WP GM	4000 K	108 lm/W	710 lm
911401547841	DN589B LED10/840 PSU C D150 WH WB GM	4000 K	125 lm/W	1,050 lm
911401548041	DN590B LED15/840 PSU C D150 WH WB GM	4000 K	185 lm/W	1,550 lm
911401548141	DN591B LED20/830 PSU C D200 WH WB GM	3000 K	113 lm/W	2,030 lm
911401548241	DN591B LED20/840 PSU C D200 WH WB GM	4000 K	119 lm/W	2,150 lm
911401548341	DN593B LED30/830 PSU C D200 WH WB GM	3000 K	102 lm/W	3,300 lm
911401548441	DN593B LED30/840 PSU C D200 WH WB GM	4000 K	105 lm/W	3,400 lm
911401548541	DN594B LED40/830 PSU C D200 WH WB GM	3000 K	103 lm/W	4,100 lm
911401548641	DN594B LED40/840 PSU C D200 WH WB GM	4000 K	108 lm/W	4,300 lm
911401548941	DN589B LED10/840 PSD C D150 WH WB GM	4000 K	125 lm/W	1,050 lm
911401549141	DN591B LED20/830 PSD C D200 WH WB GM	3000 K	105 lm/W	2,030 lm
911401549241	DN591B LED20/840 PSD C D200 WH WB GM	4000 K	111 lm/W	2,150 lm
911401549441	DN594B LED40/840 PSD C D200 WH WB GM	4000 K	108 lm/W	4,300 lm
911401549741	DN589B LED10/830 PSU C D150 WH WB WP GM	3000 K	112 lm/W	940 lm
911401549841	DN589B LED10/840 PSU C D150 WH WB WP GM	4000 K	119 lm/W	1,000 lm
911401550041	DN590B LED15/840 PSU C D150 WH WB WP GM	4000 K	109 lm/W	1,470 lm
911401550241	DN591B LED20/840 PSU C D200 WH WB WP GM	4000 K	113 lm/W	2,040 lm
911401550341	DN593B LED30/840 PSU C D200 WH WB WP GM	4000 K	99 lm/W	3,230 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
911401549541	DN588B LED6/830 PSU C D125 WH WB WP GM	6.6 W	911401548341	DN593B LED30/830 PSU C D200 WH WB GM	32.5 W
911401549641	DN588B LED6/840 PSU C D125 WH WB WP GM	6.6 W	911401548441	DN593B LED30/840 PSU C D200 WH WB GM	32.5 W
911401547841	DN589B LED10/840 PSU C D150 WH WB GM	8.4 W	911401548541	DN594B LED40/830 PSU C D200 WH WB GM	39.7 W
911401548041	DN590B LED15/840 PSU C D150 WH WB GM	8.4 W	911401548641	DN594B LED40/840 PSU C D200 WH WB GM	39.7 W
911401548141	DN591B LED20/830 PSU C D200 WH WB GM	18 W	911401548941	DN589B LED10/840 PSD C D150 WH WB GM	8.4 W
911401548241	DN591B LED20/840 PSU C D200 WH WB GM	18 W	911401549141	DN591B LED20/830 PSD C D200 WH WB GM	19.3 W

Order Code	Full Product Name	Power Consumption
911401549241	DN591B LED20/840 PSD C D200 WH WB GM	19.3 W
911401549441	DN594B LED40/840 PSD C D200 WH WB GM	39.7 W
911401549741	DN589B LED10/830 PSU C D150 WH WB WP GM	8.4 W
911401549841	DN589B LED10/840 PSU C D150 WH WB WP GM	8.4 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401549541	DN588B LED6/830 PSU C D125 WH WB WP GM	No
911401549641	DN588B LED6/840 PSU C D125 WH WB WP GM	No
911401547841	DN589B LED10/840 PSU C D150 WH WB GM	No
911401548041	DN590B LED15/840 PSU C D150 WH WB GM	No
911401548141	DN591B LED20/830 PSU C D200 WH WB GM	No
911401548241	DN591B LED20/840 PSU C D200 WH WB GM	No
911401548341	DN593B LED30/830 PSU C D200 WH WB GM	No
911401548441	DN593B LED30/840 PSU C D200 WH WB GM	No
911401548541	DN594B LED40/830 PSU C D200 WH WB GM	No
911401548641	DN594B LED40/840 PSU C D200 WH WB GM	No

Approval and Application

Order Code	Full Product Name	Protection class IEC	Ingress protection code
911401549541	DN588B LED6/830 PSU C D125 WH WB WP GM	Safety class II	IP20/54
911401549641	DN588B LED6/840 PSU C D125 WH WB WP GM	Safety class II	IP20/54
911401547841	DN589B LED10/840 PSU C D150 WH WB GM	Safety class II	IP20
911401548041	DN590B LED15/840 PSU C D150 WH WB GM	Safety class II	IP20
911401548141	DN591B LED20/830 PSU C D200 WH WB GM	Safety class II	IP20
911401548241	DN591B LED20/840 PSU C D200 WH WB GM	Safety class II	IP20
911401548341	DN593B LED30/830 PSU C D200 WH WB GM	Safety class II	IP20
911401548441	DN593B LED30/840 PSU C D200 WH WB GM	Safety class II	IP20
911401548541	DN594B LED40/830 PSU C D200 WH WB GM	Safety class II	IP20
911401548641	DN594B LED40/840 PSU C D200 WH WB GM	Safety class II	IP20

Application Conditions

Order Code	Full Product Name	Maximum dim level
911401549541	DN588B LED6/830 PSU C D125 WH WB WP GM	Not applicable
911401549641	DN588B LED6/840 PSU C D125 WH WB WP GM	Not applicable
911401547841	DN589B LED10/840 PSU C D150 WH WB GM	Not applicable

Order Code	Full Product Name	Power Consumption
911401550041	DN590B LED15/840 PSU C D150 WH WB WP GM	13.5 W
911401550241	DN591B LED20/840 PSU C D200 WH WB WP GM	18 W
911401550341	DN593B LED30/840 PSU C D200 WH WB WP GM	32.5 W

Order Code	Full Product Name	Dimmable
911401548941	DN589B LED10/840 PSD C D150 WH WB GM	Yes
911401549141	DN591B LED20/830 PSD C D200 WH WB GM	Yes
911401549241	DN591B LED20/840 PSD C D200 WH WB GM	Yes
911401549441	DN594B LED40/840 PSD C D200 WH WB GM	Yes
911401549741	DN589B LED10/830 PSU C D150 WH WB WP GM	No
911401549841	DN589B LED10/840 PSU C D150 WH WB WP GM	No
911401550041	DN590B LED15/840 PSU C D150 WH WB WP GM	No
911401550241	DN591B LED20/840 PSU C D200 WH WB WP GM	No
911401550341	DN593B LED30/840 PSU C D200 WH WB WP GM	No

Order Code	Full Product Name	Protection class IEC	Ingress protection code
911401548941	DN589B LED10/840 PSD C D150 WH WB GM	Safety class II	IP20
911401549141	DN591B LED20/830 PSD C D200 WH WB GM	Safety class I	IP20
911401549241	DN591B LED20/840 PSD C D200 WH WB GM	Safety class I	IP20
911401549441	DN594B LED40/840 PSD C D200 WH WB GM	Safety class I	IP20
911401549741	DN589B LED10/830 PSU C D150 WH WB WP GM	Safety class II	IP20/54
911401549841	DN589B LED10/840 PSU C D150 WH WB WP GM	Safety class II	IP20/54
911401550041	DN590B LED15/840 PSU C D150 WH WB WP GM	Safety class II	IP20/54
911401550241	DN591B LED20/840 PSU C D200 WH WB WP GM	Safety class II	IP20/54
911401550341	DN593B LED30/840 PSU C D200 WH WB WP GM	Safety class II	IP20/54

Order Code	Full Product Name	Maximum dim level
911401548041	DN590B LED15/840 PSU C D150 WH WB GM	Not applicable
911401548141	DN591B LED20/830 PSU C D200 WH WB GM	Not applicable
911401548241	DN591B LED20/840 PSU C D200 WH WB GM	Not applicable

Order Code	Full Product Name	Maximum dim level
911401548341	DN593B LED30/830 PSU C D200 WH WB GM	Not applicable
911401548441	DN593B LED30/840 PSU C D200 WH WB GM	Not applicable
911401548541	DN594B LED40/830 PSU C D200 WH WB GM	Not applicable
911401548641	DN594B LED40/840 PSU C D200 WH WB GM	Not applicable
911401548941	DN589B LED10/840 PSD C D150 WH WB GM	1%
911401549141	DN591B LED20/830 PSD C D200 WH WB GM	1%
911401549241	DN591B LED20/840 PSD C D200 WH WB GM	1%

Order Code	Full Product Name	Maximum dim level
911401549441	DN594B LED40/840 PSD C D200 WH WB GM	1%
911401549741	DN589B LED10/830 PSU C D150 WH WB WP GM	Not applicable
911401549841	DN589B LED10/840 PSU C D150 WH WB WP GM	Not applicable
911401550041	DN590B LED15/840 PSU C D150 WH WB WP GM	Not applicable
911401550241	DN591B LED20/840 PSU C D200 WH WB WP GM	Not applicable
911401550341	DN593B LED30/840 PSU C D200 WH WB WP GM	Not applicable

