



The affordable LEDTube T8 solution

Ecofit LED tubes T8 Mains

Upgrade to efficient, long-lasting LED tubes with the Ecofit LED tubes. Ecofit LED tubes are a fast and easy way to replace your old fluorescent tubes with modern, efficient LED technology. Good quality of light with a natural lighting effect for use in general lighting applications with low initial investment — an environmentally friendly solution.

Benefits

- \cdot Up to 50% energy saving compared with conventional fluorescent systems
- Easy installation: retrofit replacement of existing T8 lamps improving the quality of light
- · Low initial investment

Features

- · Retrofit solution with a long lifetime of 15,000 hrs
- Up to 50% energy saving
- Instant on, no flicker or buzz

Application


- Domestic applications
- · Small offices and retailers

Ecofit LED tubes T8 Mains

Versions



Dimensional drawing



D1	D2	A1	A2	А3	С	D
25.68	28	588.5	595.5	602.5	602.5	27.8
mm	mm	mm	mm	mm	mm	mm
25.68	28	1198	1205	1212 mm	1212 mm	27.8
mm	mm	mm	mm			mm
25.68	28	588.5	595.5	602.5	602.5	27.8
mm	mm	mm	mm	mm	mm	mm
	25.68 mm 25.68 mm	25.68 28 mm mm 25.68 28 mm mm	25.68 28 588.5 mm mm mm 25.68 28 1198 mm mm mm 25.68 28 588.5	25.68 28 588.5 595.5 mm mm mm mm mm 25.68 28 1198 1205 mm mm mm mm mm 25.68 28 588.5 595.5	25.68 28 588.5 595.5 602.5 mm mm mm mm mm 25.68 28 1198 1205 1212 mm mm mm mm mm 25.68 28 588.5 595.5 602.5	25.68

Ecofit LED tubes T8 Mains

Energy Efficiency Label (EEL)	Δ+
inergy Emiliency Laber (EEL)	A
Operating and Electrical	
Input Frequency	50 to 60 Hz
Voltage (Nom)	220-240 V
Starting Time (Nom)	0.5 s
starting rime (Nom)	0.5 \$
General Information	
Cap-Base	G13
Nominal Lifetime (Nom)	15000 h
Rated Lifetime (Hours)	15000 h
Switching Cycle	50000X
Light Technical	
Colour Rendering Index (Nom)	73
Llmf At End Of Nominal Lifetime	70 %
(Nom)	
Temperature	
T-Ambient (Max)	45 °C
T-Ambient (Min)	-20 °C
T-Case Maximum (Nom)	60 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
929001184508	LEDtube 1200mm 16W 740 T8 AP C G	16 kWh
929001184708	LEDtube 600mm 8W 740 T8 AP C G	8 kWh
929001184808	LEDtube 600mm 8W 765 T8 AP C G	8 kWh

Controls and Dimming

Order Code	Full Product Name	Dimmable
929001184508	LEDtube 1200mm 16W 740 T8 AP C G	No
929001184708	LEDtube 600mm 8W 740 T8 AP C G	no

Order Code	Full Product Name	Dimmable
929001184808	LEDtube 600mm 8W 765 T8 AP C G	no

Operating and Electrical

Order Code	Full Product Name	Power (Rated) (Nom)
929001184508	LEDtube 1200mm 16W 740 T8 AP C G	16 W
929001184708	LEDtube 600mm 8W 740 T8 AP C G	8 W


Order Code	Full Product Name	Power (Rated) (Nom)
929001184808	LEDtube 600mm 8W 765 T8 AP C G	8 W


Light Technical

			Correlated Colour		Luminous
	Full Product	Colour	Temperature	Luminous	Flux (Rated)
Order Code	Name	Code	(Nom)	Flux (Nom)	(Nom)
929001184508	LEDtube	740	4000 K	1600 lm	1600 lm
	1200mm 16W				
	740 T8 AP C G				
929001184708	LEDtube	740	4000 K	800 lm	800 lm
	600mm 8W 740				
	T8 AP C G				

			Correlated		
			Colour		Luminous
	Full Product	Colour	Temperature	Luminous	Flux (Rated)
Order Code	Name	Code	(Nom)	Flux (Nom)	(Nom)
929001184808	LEDtube	765	6500 K	800 lm	800 lm
	600mm 8W 765				
	T8 AP C G				

Ecofit LED tubes T8 Mains







© 2019 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.