



Energy saving without compromise

GreenPerform Troffer

GreenPerform troffer improves the compact design of the last generation with performance improvement and more variants for different markets. Integrating with all available system: POE, InterAct office wireless, InterAct Office Pro, ActiLume controller, GreenPerform troffer offers additional energy saving and connected features.

Benefits

- \cdot Upgrade to smart office with more options
- Energy saving
- Slim housing
- · Comfortable light
- · Good light quality
- · Office compliant
- · Reliable performance

Features

- \cdot Compatible with all available Philips systems
- \cdot Efficacy up to 125lm/W
- · Slim design with height less than 46mm
- · Improved optical design without zebra effect
- · CRI > 80, SDCM<4, Flicker free
- · UGR 19 available
- · Lifetime L70 50,000 hours

Application

- · Open Office
- Public Area
- Meeting Room
- · Training Room


GreenPerform Troffer


Specifications


Ceiling type	T-bar ceiling
Mains Voltage	220-240V / 50-60Hz
Dimming	PSU: non-dimmable
	PSD: Dimmable via Dali-broadcasting
	WIA: Wireless control, compatible with Interact
	SIA: Wireless control, compatible with Interact and with SNS210
	sensor
Control system input	Dali


Lumen maintenance at	L70B50
median useful life	
50.000h	
Correlated color	840
temperature - CCT	865
UGR	19 is available through certain types
Installation	Recessed


Dimensional drawing











GreenPerform Troffer

General Information	
CE mark	CE mark
Driver included	Yes
Flammability mark	For mounting on
	normally
	flammable
	surfaces
Glow-wire test	Temperature 600
	°C, duration 30 s
Light source replaceable	No
Number of gear units	1 unit
Light Technical	
Optical cover type	Variable linear-
	lens array in
	polycarbonate
	cover
Color rendering index (CRI)	80
Operating and Electrical	
Line Frequency	50 to 60 Hz
Temperature	
Ambient temperature range	-20 to +40 ℃
Mechanical and Housing	
Housing Color	White
Approval and Application	
Protection class IEC	Safety class I
Mech. impact protection code	IK03
Ingress protection code	IP20
Initial Devicements (IEC Commit	iont)
Initial Performance (IEC Compl	
Initial chromaticity	SDCM<4
Luminous flux tolerance	+/-10%
Application Conditions	
	Ne
Suitable for random switching	No

Light Technical

		Correlated Color	Luminous Efficacy	
Order Code	Full Product Name	Temperature (Nom)	(rated) (Nom)	Luminous Flux
911401513051	RC100B LED37S 840 W30L120	4000 K	121 lm/W	3,700 lm
	PSD OC G3			
911401513251	RC100B LED37S 840 W30L120	4000 K	116 lm/W	3,700 lm
	PSD G3			
911401513351	RC100B LED37S 840 W30L120	4000 K	116 lm/W	3,700 lm
	PSU G3			
911401513751	RC100B LED37S 865 W30L120	6500 K	116 lm/W	3,700 lm
	PSU UNV G3			
911401519451	SM100C LED37S 840 W30L120	4000 K	116 lm/W	3,700 lm
	PSU G3			
911401519551	SM100C LED37S 840 W30L120	4000 K	116 lm/W	3,700 lm
	PSD G3			
911401508451	RC100B LED27S 840 W60L60	4000 K	117 lm/W	2,700 lm
	PSU G3			
911401509551	RC100B LED37S 840 W603L603	4000 K	116 lm/W	3,700 lm
	PSU UNV G3			
11401509951	SM100C LED27S 840 W60L60	4000 K	117 lm/W	2,700 lm
	PSU G3			
911401510751	RC100B LED37S 840 W60L60	4000 K	116 lm/W	3,700 lm
	PSU G3			
911401510851	RC100B LED37S 840 W60L60	4000 K	121 lm/W	3,700 lm
	PSD OC G3			
911401510951	RC100B LED37S 865 W60L60 PSU	6500 K	116 lm/W	3,700 lm
	G3			
911401511151	RC100B LED37S 840 W60L60	4000 K	116 lm/W	3,700 lm
	PSD G3			
911401511451	RC100B LED37S 840 W60L60	4000 K	116 lm/W	3,700 lm
	PSU UNV G3			
911401514051	RC100B LED37S 840 W60L120	4000 K	129 lm/W	3,700 lm
	PSD OC CAU			
911401514351	RC100B LED54S 840 W60L120	4000 K	123 lm/W	5,400 lm
	PSU G3			

Operating and Electrical

Order Code	Full Product Name	Input Voltage	Power Consumption
911401513051	RC100B LED37S 840 W30L120 PSD	220 to 240 V	32 W
	OC G3		
911401513251	RC100B LED37S 840 W30L120 PSD	220 to 240 V	32 W
	G3		
911401513351	RC100B LED37S 840 W30L120 PSU	220 to 240 V	32 W
	G3		
911401513751	RC100B LED37S 865 W30L120 PSU	110 to 277 V	32 W
	UNV G3		
911401519451	SM100C LED37S 840 W30L120 PSU	220 to 240 V	32 W
	G3		

Order Code	Full Product Name	Input Voltage	Power Consumption
911401519551	SM100C LED37S 840 W30L120 PSD	220 to 240 V	32 W
	G3		
911401508451	RC100B LED27S 840 W60L60 PSU	220 to 240 V	23 W
	G3		
911401509551	RC100B LED37S 840 W603L603	110 to 277 V	32 W
	PSU UNV G3		
911401509951	SM100C LED27S 840 W60L60 PSU	220 to 240 V	23 W
	G3		
911401510751	RC100B LED37S 840 W60L60 PSU	220 to 240 V	32 W
	G3		

GreenPerform Troffer

Order Code	Full Product Name	Input Voltage	Power Consumption
911401510851	RC100B LED37S 840 W60L60 PSD	220 to 240 V	32 W
	OC G3		
911401510951	RC100B LED37S 865 W60L60 PSU	220 to 240 V	32 W
	G3		
911401511151	RC100B LED37S 840 W60L60 PSD	220 to 240 V	32 W
	G3		

Order Code	Full Product Name	Input Voltage	Power Consumption
911401511451	RC100B LED37S 840 W60L60 PSU UNV G3	110 to 277 V	32 W
911401514051	RC100B LED37S 840 W60L120 PSD OC CAU	220 to 240 V	32 W
911401514351	RC100B LED54S 840 W60L120 PSU G3	220 to 240 V	44 W

Controls and Dimming

	•	
Order Code	Full Product Name	Dimmable
911401513051	RC100B LED37S 840 W30L120 PSD OC G3	Yes
911401513251	RC100B LED37S 840 W30L120 PSD G3	Yes
911401513351	RC100B LED37S 840 W30L120 PSU G3	No
911401513751	RC100B LED37S 865 W30L120 PSU UNV G3	No
911401519451	SM100C LED37S 840 W30L120 PSU G3	No
911401519551	SM100C LED37S 840 W30L120 PSD G3	Yes
911401508451	RC100B LED27S 840 W60L60 PSU G3	No
911401509551	RC100B LED37S 840 W603L603 PSU UNV G3	No

Order Code	Full Product Name	Dimmable
911401509951	SM100C LED27S 840 W60L60 PSU G3	No
911401510751	RC100B LED37S 840 W60L60 PSU G3	No
911401510851	RC100B LED37S 840 W60L60 PSD OC G3	Yes
911401510951	RC100B LED37S 865 W60L60 PSU G3	No
911401511151	RC100B LED37S 840 W60L60 PSD G3	Yes
911401511451	RC100B LED37S 840 W60L60 PSU UNV G3	No
911401514051	RC100B LED37S 840 W60L120 PSD OC CAU	Yes
911401514351	RC100B LED54S 840 W60L120 PSU G3	No

