



# Switch light settings without switching spots

## SceneSwitch LEDspot

Some situations call for cool light, others benefit from the ambience of a warm, cosy glow. With Philips SceneSwitch LEDspot, you can have different light settings from just one spot. And you don't need a dimmer! Optimise your lighting for relaxing, hobbies, recreation or working. Simply at the flick of a switch. And that's your existing switch! No extra installation is required.

### Benefits

- Create your own scene with one lamp simply using your existing light switch
- No dimmer or additional installation needed
- Auto memory: recall your last setting automatically

### Features

- Multiple light settings in one lamp
- Plug and play
- Built-in memory chip

### Application


- Indoor applications in open luminaires (with an open/free air gap of min. 10 mm)
- Accent and general lighting (e.g. hotels, shops and offices)

# SceneSwitch LEDspot

## Versions



## Dimensional drawing



Product	D	C
LEDSSW 4.5-50W GU10 827 36D 1BC/3	50 mm	54 mm
LED SceneSwitch 50W GU10 WH-CDL 36D ND	50 mm	54 mm
LED SceneSwitch 50W GU10 WW-CW 36D ND 1BC/6	50 mm	54 mm

### Approval and Application

Energy Consumption kWh/1000 h	5 kWh
Energy Efficiency Label (EEL)	A+

### Controls and Dimming

Dimmable	No
----------	----

### Operating and Electrical

Input Frequency	50 to 60 Hz
Voltage (Nom)	220-240 V

### General Information

Cap-Base	GU10
Nominal Lifetime (Nom)	15000 h
Switching Cycle	50000X

### Light Technical

Beam Angle (Nom)	36 °
Colour Rendering Index (Nom)	80
Llmf At End Of Nominal Lifetime (Nom)	70 %

### Mechanical and Housing

Bulb Shape	PAR16
------------	-------

## Operating and Electrical

Order Code	Full Product Name	Wattage Equivalent	Power (Rated) (Nom)	Starting Time (Nom)
929001346019	LEDSSW 4.5-50W GU10 827 36D 1BC/3	-	1.5/3.5/5 W	0.5 s
929001894501	LED SceneSwitch 50W GU10 WW-CW 36D ND 1BC/6	50 W	5 W	0.4 s
929001894607	LED SceneSwitch 50W GU10 WH-CDL 36D ND	50 W	5 W	0.4 s

# SceneSwitch LEDspot


## Light Technical

Order Code	Full Product Name	Colour Code	Correlated Colour Temperature (Nom)	Luminous Flux (Nom)	Luminous Intensity (Nom)
929001346019	LEDSSW 4.5-50W GU10 827 36D 1BC/3	827/825/822	2200/2500/2700 K	390 lm	-
929001894501	LED SceneSwitch 50W GU10	827/840	2700/4000 K	385 lm	-

Order Code	Full Product Name	Colour Code	Correlated Colour Temperature (Nom)	Luminous Flux (Nom)	Luminous Intensity (Nom)
929001894607	LED SceneSwitch 50W GU10 WH-CDL 36D ND	865/830	3000/6500 K	450 lm	700 cd

## Temperature


Order Code	Full Product Name	T-Case Maximum (Nom)
929001346019	LEDSSW 4.5-50W GU10 827 36D 1BC/3	80 °C
929001894501	LED SceneSwitch 50W GU10 WW-CW 36D ND 1BC/6	85 °C
929001894607	LED SceneSwitch 50W GU10 WH-CDL 36D ND	85 °C





# SceneSwitch LEDspot


## Accent Diagrams



SceneSwitch LED Lamps 50W GU10 827 36D  
SSW

LEDspot SSW 50W GU10 PAR16 827-840 36D  
ND

## Beam Diagrams



SceneSwitch LED Lamps 50W GU10 827 36D  
SSW

LEDspot SSW 50W GU10 PAR16 827-840 36D  
ND

