



It delivers super flexibility, complete product range and seamlessly system integration to Hospitality customers..

Greenspace Flex

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.

Benefits

- Complete portfolio covering from 400lm to 3000lm, 3CCT and 3 beam angles.
- Super flexibility with modular design, and different trims to suit different application.
- Smart connectivity to seamlessly integration with Interact Hospitality.
- Deep recess for visual comfort
- Easy installation and maintenance

Greenspace Flex

Features

- 6w ~42w (400lm~3200lm)
- CRI 90, SDCM <3
- Beam Angle: NB, MB, WB
- CCT: 2700K, 3000K, 4000K
- High reliability, 50Khrs (L80B50@25°C)

Application

- Guest room
- Bath room
- Corridor
- Lobby

Specifications

Mounting type	Recessed
Operating Temperature range	-20 to +45 °C
Light Source	COB
Mains Voltage	220-240V AC/ 50-60Hz
Optical Accessories	available through ETO
Dimming	PSU: non-dimmable PSD: dimmable via Dali protocol PSR: trailing dimmable PSR 1-10V: 1-10v dimmable DMX: dimmable via DMX protocol
Control system input	DALI / 1-10V / DMX / trailing edge
Material	Heat sink: die-cast aluminum
Main color of the luminaire	Housing: dark Grey Reflector: color available through ETO
Lumen maintenance at median useful life 50.000h	L80
Luminous flux	468-3990lm
Power consumption	6W-42W

Correlated color temperature - CCT	2700K, 3000K, 4000K
Color Rendering index - CRI	90
Beam angle	NB (Narrow Beam): 15-18° MB (Medium Beam): 20-24° WB (Wide Beam): 30-40° VWB (Very Wide Beam): 50°
Protection Class IEC61140	Class II & Class III for MR16 version
Mechanical impact protection	IK04
Ingress protection	IP20 / IP54(Front side) for selected SKU only
Light source replaceable	No
Driver replaceable	yes
Overall diameter	D55-D150
Installation	recessed Fixation by means of spring fasteners

Versions



RS378B P11 M55





RS378B P6 M55





RS378B P15 M55

Dimensional drawing



Modular Type	D, mm	H, mm
RS378B P6/P11 M55	55	49
RS378B P15 M55	55	49
RS378B P24 M70	70	90
RS378B P33 M87	87	107
RS378B P42 M102	102	116



General Information

CE mark	-
ENEC mark	-
Flammability mark	-

Light Technical

Optical cover type	-
Color rendering index (CRI)	>90
Optic type	-

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz

Temperature

Ambient temperature range	-20 to +45 °C
---------------------------	---------------

Mechanical and Housing

Housing Color	Dark gray
---------------	-----------

Approval and Application

Protection class IEC	Safety class II
Mech. impact protection code	IK04
Ingress protection code	IP20

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

General Information

Order Code	Full Product Name	Driver included	Glow-wire test	Number of gear units
911401535971	RS378B P11 927 PSD-E MB M55	-	-	-
911401720962	RS378B P6 930 PSU-E WB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
911401720972	RS378B P6 940 PSU-E WB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
911401720982	RS378B P11 927 PSU-E NB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
911401721042	RS378B P11 927 PSU-E WB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
911401721062	RS378B P11 940 PSU-E WB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
911401535171	RS378B P6 927 PSD-E WB M55	-	-	-
911401538071	RS378B P24 930 PSD-E MB M70	-	-	-
911401721442	RS378B P24 930 PSU-E NB M70	Yes	Temperature 600 °C, duration 30 s	1 unit
911401536771	RS378B P15 927 PSD-E NB M55	-	-	-
911401536871	RS378B P15 927 PSD-E MB M55	-	-	-
911401536971	RS378B P15 927 PSD-E WB M55	-	-	-
911401721252	RS378B P15 927 PSU-E NB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
911401721282	RS378B P15 927 PSU-E MB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
911401721312	RS378B P15 927 PSU-E WB M55	Yes	Temperature 600 °C, duration 30 s	1 unit

Order Code	Full Product Name	Driver included	Glow-wire test	Number of gear units
911401721322	RS378B P15 930 PSU-E WB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
911401721332	RS378B P15 940 PSU-E WB M55	Yes	Temperature 600 °C, duration 30 s	1 unit

Light Technical

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401535971	RS378B P11 927 PSD-E MB M55	-	2700 K	87 lm/W	957 lm
911401720962	RS378B P6 930 PSU-E WB M55	- degree(s)	3000 K	78 lm/W	468 lm
911401720972	RS378B P6 940 PSU-E WB M55	- degree(s)	4000 K	82 lm/W	492 lm
911401720982	RS378B P11 927 PSU-E NB M55	-	2700 K	76 lm/W	836 lm
911401721042	RS378B P11 927 PSU-E WB M55	-	2700 K	87 lm/W	957 lm
911401721062	RS378B P11 940 PSU-E WB M55	-	4000 K	100 lm/W	1,100 lm
911401535171	RS378B P6 927 PSD-E WB M55	-	2700 K	70 lm/W	420 lm
911401538071	RS378B P24 930 PSD-E MB M70	-	3000 K	83 lm/W	1,992 lm
911401721442	RS378B P24 930 PSU-E NB M70	-	3000 K	83 lm/W	1,992 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401536771	RS378B P15 927 PSD-E NB M55	-	2700 K	76 lm/W	1,140 lm
911401536871	RS378B P15 927 PSD-E MB M55	-	2700 K	78 lm/W	1,170 lm
911401536971	RS378B P15 927 PSD-E WB M55	-	2700 K	87 lm/W	1,305 lm
911401721252	RS378B P15 927 PSU-E NB M55	-	2700 K	76 lm/W	1,140 lm
911401721282	RS378B P15 927 PSU-E MB M55	-	2700 K	76 lm/W	1,140 lm
911401721312	RS378B P15 927 PSU-E WB M55	-	2700 K	76 lm/W	1,140 lm
911401721322	RS378B P15 930 PSU-E WB M55	-	3000 K	78 lm/W	1,170 lm
911401721332	RS378B P15 940 PSU-E WB M55	-	4000 K	87 lm/W	1,305 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401535971	RS378B P11 927 PSD-E MB M55	11 W
911401720962	RS378B P6 930 PSU-E WB M55	6 W
911401720972	RS378B P6 940 PSU-E WB M55	6 W
911401720982	RS378B P11 927 PSU-E NB M55	11 W
911401721042	RS378B P11 927 PSU-E WB M55	11 W
911401721062	RS378B P11 940 PSU-E WB M55	11 W
911401535171	RS378B P6 927 PSD-E WB M55	6 W
911401538071	RS378B P24 930 PSD-E MB M70	24 W
911401721442	RS378B P24 930 PSU-E NB M70	24 W

Order Code	Full Product Name	Power Consumption
911401536771	RS378B P15 927 PSD-E NB M55	15 W
911401536871	RS378B P15 927 PSD-E MB M55	15 W
911401536971	RS378B P15 927 PSD-E WB M55	15 W
911401721252	RS378B P15 927 PSU-E NB M55	15 W
911401721282	RS378B P15 927 PSU-E MB M55	15 W
911401721312	RS378B P15 927 PSU-E WB M55	15 W
911401721322	RS378B P15 930 PSU-E WB M55	15 W
911401721332	RS378B P15 940 PSU-E WB M55	15 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401535971	RS378B P11 927 PSD-E MB M55	Yes
911401720962	RS378B P6 930 PSU-E WB M55	No
911401720972	RS378B P6 940 PSU-E WB M55	No
911401720982	RS378B P11 927 PSU-E NB M55	No
911401721042	RS378B P11 927 PSU-E WB M55	No
911401721062	RS378B P11 940 PSU-E WB M55	No
911401535171	RS378B P6 927 PSD-E WB M55	Yes
911401538071	RS378B P24 930 PSD-E MB M70	Yes
911401721442	RS378B P24 930 PSU-E NB M70	No

Order Code	Full Product Name	Dimmable
911401536771	RS378B P15 927 PSD-E NB M55	Yes
911401536871	RS378B P15 927 PSD-E MB M55	Yes
911401536971	RS378B P15 927 PSD-E WB M55	Yes
911401721252	RS378B P15 927 PSU-E NB M55	No
911401721282	RS378B P15 927 PSU-E MB M55	No
911401721312	RS378B P15 927 PSU-E WB M55	No
911401721322	RS378B P15 930 PSU-E WB M55	No
911401721332	RS378B P15 940 PSU-E WB M55	No

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
911401535971	RS378B P11 927 PSD-E MB M55	-
911401720962	RS378B P6 930 PSU-E WB M55	SDCM<3
911401720972	RS378B P6 940 PSU-E WB M55	SDCM<3
911401720982	RS378B P11 927 PSU-E NB M55	SDCM<3
911401721042	RS378B P11 927 PSU-E WB M55	SDCM<3
911401721062	RS378B P11 940 PSU-E WB M55	SDCM<3
911401535171	RS378B P6 927 PSD-E WB M55	-
911401538071	RS378B P24 930 PSD-E MB M70	-
911401721442	RS378B P24 930 PSU-E NB M70	SDCM<3

Order Code	Full Product Name	Initial chromaticity
911401536771	RS378B P15 927 PSD-E NB M55	-
911401536871	RS378B P15 927 PSD-E MB M55	-
911401536971	RS378B P15 927 PSD-E WB M55	-
911401721252	RS378B P15 927 PSU-E NB M55	SDCM<3
911401721282	RS378B P15 927 PSU-E MB M55	SDCM<3
911401721312	RS378B P15 927 PSU-E WB M55	SDCM<3
911401721322	RS378B P15 930 PSU-E WB M55	SDCM<3
911401721332	RS378B P15 940 PSU-E WB M55	SDCM<3

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Median useful life L80B50
911401535971	RS378B P11 927 PSD-E MB M55	-
911401720962	RS378B P6 930 PSU-E WB M55	50,000 hour(s)
911401720972	RS378B P6 940 PSU-E WB M55	50,000 hour(s)
911401720982	RS378B P11 927 PSU-E NB M55	50,000 hour(s)
911401721042	RS378B P11 927 PSU-E WB M55	50,000 hour(s)
911401721062	RS378B P11 940 PSU-E WB M55	50,000 hour(s)
911401535171	RS378B P6 927 PSD-E WB M55	-
911401538071	RS378B P24 930 PSD-E MB M70	-
911401721442	RS378B P24 930 PSU-E NB M70	50,000 hour(s)

Order Code	Full Product Name	Median useful life L80B50
911401536771	RS378B P15 927 PSD-E NB M55	-
911401536871	RS378B P15 927 PSD-E MB M55	-
911401536971	RS378B P15 927 PSD-E WB M55	-
911401721252	RS378B P15 927 PSU-E NB M55	50,000 hour(s)
911401721282	RS378B P15 927 PSU-E MB M55	50,000 hour(s)
911401721312	RS378B P15 927 PSU-E WB M55	50,000 hour(s)
911401721322	RS378B P15 930 PSU-E WB M55	50,000 hour(s)
911401721332	RS378B P15 940 PSU-E WB M55	50,000 hour(s)

Application Conditions

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
911401535971	RS378B P11 927 PSD-E MB M55	-	-
911401720962	RS378B P6 930 PSU-E WB M55	Not applicable	No
911401720972	RS378B P6 940 PSU-E WB M55	Not applicable	No
911401720982	RS378B P11 927 PSU-E NB M55	Not applicable	No
911401721042	RS378B P11 927 PSU-E WB M55	Not applicable	No
911401721062	RS378B P11 940 PSU-E WB M55	Not applicable	No
911401535171	RS378B P6 927 PSD-E WB M55	-	-
911401538071	RS378B P24 930 PSD-E MB M70	-	-
911401721442	RS378B P24 930 PSU-E NB M70	Not applicable	No

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
911401536771	RS378B P15 927 PSD-E NB M55	-	-
911401536871	RS378B P15 927 PSD-E MB M55	-	-
911401536971	RS378B P15 927 PSD-E WB M55	-	-
911401721252	RS378B P15 927 PSU-E NB M55	Not applicable	No
911401721282	RS378B P15 927 PSU-E MB M55	Not applicable	No
911401721312	RS378B P15 927 PSU-E WB M55	Not applicable	No
911401721322	RS378B P15 930 PSU-E WB M55	Not applicable	No
911401721332	RS378B P15 940 PSU-E WB M55	Not applicable	No

