



# Extending the home feel onto the street

## TownTune Asymmetric Lyre

As a luminaire family prepared for existing and scalable urban spaces, TownTune offers all the recent lighting innovations in terms of performance, quality of light and connectivity. The Philips TownTune family consists of three members: a central post top, an asymmetric spigot version and a version using an extending lyre post-top bracket. Each of these three can be customised with a choice of different shapes for housing and an optional decorative ring which comes in two colours. By having these options available, you can create your very own lighting signature and give a distinctive identity to districts and cities. The luminaire family is also equipped with the QR code-based Philips Service tag, which supports installation and maintenance work and enables you to create a digital library of lighting assets and spare parts. TownTune also makes use of the Philips Ledgine optimised lighting platform, ensuring that you always have the right amount and direction of light on your street. Furthermore, thanks to being SR (System-Ready), TownTune is also future-proof and is ready to be paired with both standalone and advanced control and lighting software applications, such as Interact City.

# TownTune Asymmetric Lyre

## Benefits

- Delivers visual comfort, and comfortable lighting experiences in urban spaces through its dedicatedly designed bowl
- A simple, pure design, making it possible to integrate it into various urban environments and the option for customisation through a wide range of accessories, lets cities create a unique light signature, which can also become part of the urban furniture in the daytime
- Wide application coverage and offers great performance by using the latest Ledgine LED platform and providing access to a wide range of light distributions
- Ready to be paired with lighting control and software applications, by being equipped with the Philips SR (System Ready) socket
- Equipped with a service tag, a QR-based identification system that makes each luminaire uniquely identifiable and provides maintenance, installation and spare part information

## Features

- Optimised Total Cost of Ownership and option of CLO (Constant Light Output)
- Excellent quality of light enabled by the Philips Ledgine optimised platform, and further optimisation in L-Tune is also possible
- Choice of different shapes for housing (cone, dome), option of decorative ring and colours (clear and golden)
- Ready to be paired with standalone lighting controls such as LumiStep, DynaDimmer and LineSwitch, and advanced system and software applications, such as Interact City
- Wide choice of lumen packages, ranging from 600 to 12,000 lumens
- Choice of colour temperature: 3,000 K (warm white) or 4,000 K (neutral white)
- Long lifetime of 100,000 hours at minimum L80
- Suitable for new and retrofit installations
- IK08, IP66

## Application

- Urban and residential areas
- City centres and high streets
- Cycle paths, footpaths and pedestrian crossings
- Car parks

## Versions



TownTune Asymmetric Lyre

Product details



TownTune LYR BDP270



TownTune ASY BDP265



TownTune ASY BDP265



TownTune ASY BDP265



TownTune ASY BDP265



TownTune ASY DR BDP266



TownTune ASY BDP265

# TownTune Asymmetric Lyre

## Application Conditions

Maximum dim level	10%
-------------------	-----

## Approval and Application

Mech. impact protection code	IK09
Surge Protection (Common/Differential)	Philips standard surge protection level kV

## Controls and Dimming

Dimmable	Yes
----------	-----

## General Information

CE mark	CE mark
Optical cover/lens type	PC-UV
Driver included	Yes
Flammability mark	F
Light source replaceable	Yes
Number of gear units	1 unit
Product Family Code	BDP270

## Light Technical

Standard tilt angle side entry	-
Standard tilt angle posttop	0°
Upward light output ratio	0

## Mechanical and Housing

Colour	Dark Grey
--------	-----------

## General Information

Order Code	Full Product Name	Luminaire light beam	Light source	Lamp	Optic type
		spread	colour	family code	
49765100	BDP270 LED40-4S/830 DM50 CLO DDF3 62P	6° - 79° × 154°	830 warm white	LED40	Distribution medium 50
49769900	BDP270 LED12-4S/740 DN10 CLO SRT SRB 62P	12° - 59° × 158°	740 neutral white	LED12	Distribution narrow 10

## Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Colour	Init. Colour	Initial luminous flux
		Temperature	Rendering Index	
49765100	BDP270 LED40-4S/830 DM50 CLO DDF3 62P	3000 K	>80	2888 lm

Order Code	Full Product Name	Init. Corr. Colour	Init. Colour	Initial luminous flux
		Temperature	Rendering Index	
49769900	BDP270 LED12-4S/740 DN10 CLO SRT SRB 62P	4000 K	>70	885.5 lm

