



Extending the home feel onto the street

TownTune Asymmetric Lyre DR

As a luminaire family prepared for existing and scalable urban spaces, TownTune offers all the recent lighting innovations in terms of performance, quality of light and connectivity. The Philips TownTune family consists of three members: a central post top, an asymmetric spigot version and a version using an extending lyre post-top bracket. Each of these three can be customised with a choice of different shapes for housing and an optional decorative ring which comes in two colours. By having these options available, you can create your very own lighting signature and give a distinctive identity to districts and cities. The luminaire family is also equipped with the QR code-based Philips Service tag, which supports installation and maintenance work and enables you to create a digital library of lighting assets and spare parts. TownTune also makes use of the Philips Ledgine optimised lighting platform, ensuring that you always have the right amount and direction of light on your street. Furthermore, thanks to being SR (System-Ready), TownTune is also future-proof and is ready to be paired with both standalone and advanced control and lighting software applications, such as Interact City.

Benefits

Features

Application

TownTune Asymmetric Lyre DR

Versions



Product details



TownTune LYR BDP270



TownTune ASY BDP265




TownTune ASY BDP265



TownTune ASY BDP265



TownTune ASY BDP265



TownTune ASY DR BDP266



TownTune ASY BDP265

TownTune Asymmetric Lyre DR

Application Conditions

Maximum dim level	10%
-------------------	-----

Approval and Application

Mech. impact protection code	IK09
Surge Protection (Common/Differential)	Philips standard surge protection level kV

Controls and Dimming

Dimmable	Yes
----------	-----

General Information

CE mark	CE mark
Optical cover/lens type	PC-UV
Driver included	Yes
Flammability mark	F
Light source replaceable	Yes
Number of gear units	1 unit
Product Family Code	BDP271

Light Technical

Standard tilt angle side entry	-
Standard tilt angle posttop	0°
Upward light output ratio	0

Mechanical and Housing

Colour	Dark Grey
--------	-----------

General Information

Order Code	Full Product Name	Luminaire light	Light source	Lamp	Optic type
		beam spread	colour	family code	
49766800	BDP271 LED50-4S/740	152° x 155°	740 neutral	LED50	Distribution symmetrical 50
	DS50 CLO DDF2 62P		white		
49770500	BDP271 LED69-4S/830 II	12° - 76° x 157°	830 warm	LED69	Distribution medium 10
	DM10 CLO SRT SRB		white		

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Colour Temperature	Init. Colour	
			Rendering Index	Initial luminous flux
49766800	BDP271 LED50-4S/740	4000 K	>70	3504 lm
	DS50 CLO DDF2 62P			

Order Code	Full Product Name	Init. Corr. Colour Temperature	Init. Colour	
			Rendering Index	Initial luminous flux
49770500	BDP271 LED69-4S/830	3000 K	>80	5148 lm
	II DM10 CLO SRT SRB			

