



# Exquisite, stylish yet classic and versatile urban lighting

## UNIUrban

UNIUrban is ideal for the urban lighting across the sidewalks, parks, gardens, residential areas, shopping center plazas. Its exquisite, stylish yet classic design is not only suitable for modern cities but also for historical architecture.

### Benefits

- Exquisite, stylish yet classic design to beautify your space
- State-of-the-art LEDs and drivers ensure better lighting performance and reliability
- Comfort and safety for urban
- Future-oriented

### Features

- 5 even more look-and-feels
- 3 options of wattage packages– 33W/ 65W / 100W
- 3000K/4000K CCT , 100+lm/w for energy-saving
- 3 options for installation – Side-entry, Post-top and Suspension
- 3 options for lighting distribution – Symmetrical / Asymmetrical / Omni
- IP65 / IK08 , professional design to ensure reliability
- 50K hrs. lifetime with 3 yrs. warranty
- Various mounting installation

### Application

- Sidewalks
- Parks, gardens
- Residential areas
- Shopping center plazas

Versions



uniurban



uniurban

Dimensional drawing

| General Information                |                                             |
|------------------------------------|---------------------------------------------|
| CE mark                            | CE mark                                     |
| Driver included                    | Yes                                         |
| Flammability mark                  | For mounting on normally flammable surfaces |
| Light Technical                    |                                             |
| Light source color                 | 740 neutral white                           |
| Correlated Color Temperature (Nom) | 4000 K                                      |
| Optical cover type                 | Acrylate micro-lens optic                   |
| Color rendering index (CRI)        | >70                                         |
| Operating and Electrical           |                                             |
| Power Consumption                  | 100 W                                       |
| Controls and Dimming               |                                             |
| Dimmable                           | Yes                                         |
| Mechanical and Housing             |                                             |
| Housing Color                      | Aluminum and gray                           |
| Approval and Application           |                                             |
| Mech. impact protection code       | IK08                                        |
| Ingress protection code            | IP65                                        |

Light Technical

| Order Code   | Full Product Name                     | Luminous Flux |
|--------------|---------------------------------------|---------------|
| 911401767062 | BDP461 LED100 NW 230V PSC TS 7P       | 10,000 lumen  |
| 911401767072 | BGP461 LED120 NW 230V PSC TA 7P Spg77 | 12,000 lumen  |

