



# SPEC fighter for full window panel solution

## SmartBright Direct Panel

High efficacy LED office solution to replace conventional solutions, achieving the most affordable LED panel delivering comfortable light with excellent uniformity

### Benefits

- Strong energy saving story
- Visual comfort
- Good color rendering with control on red saturation
- Reduced luminaire height covering wider potential applications
- Long lifetime with good quality & reliability

### Features

- system efficacy 100lm/W
- Flicker Free, Ripple  $<1\%$
- $UGR \leq 22$
- CRI 80,  $R9 > 0$
- Overall height is 35mm, including driver
- 30Khrs @L70B50

### Application

- Open Office
- Meeting Room
- Library & Circulation
- Hospital