PHILIPS

Lighting



Bring out the beauty in merchandise with brighter, high performance lighting

MASTER LEDspot PAR High Lumen

Philips High Lumen PAR30L integrates a leading COB LED light source and a compact high efficiency driver into a traditional CDM PAR30L form-factor. It brings out the beauty in merchandise with brighter, high performance lighting. Additionally, the lamp features an over temperature protection (OTP) to ensure a long operating life time.

Benefits

- Lower initial investment for LED CDM replacement PAR30
- Up to 43% energy saving compared to standard CDM lamps
- High efficiency solution <gt/>100lm/W

Features


- Easy retrofit to CDM PAR30L lamps with E27 base
- Emits virtually no heat and will not fade colors
- Lifetime of 25,000 hours
- UV- and IR-free light
- Free of mercury and hazardous materials – RoHS Compliant

Application

- Shops, hotels, restaurants, museums

MASTER LEDspot PAR High Lumen

Dimensional drawing



Product	D	C
Master LED PAR30L 20W 15D 830	95.5 mm	129 mm
Master LED PAR30L 20W 30D 830	95.5 mm	129 mm
Master LED PAR30L 20W 30D 840	95.5 mm	129 mm
Master LED PAR30L 32W 15D 830	95.5 mm	129 mm
Master LED PAR30L 32W 15D 840	95.5 mm	129 mm
Master LED PAR30L 32W 30D 840	95.5 mm	129 mm
Master LED PAR30L 32W 30D 857	95.5 mm	129 mm
Master LED PAR30L 40W 15D 840	95.5 mm	129 mm
Master LED PAR30L 40W 30D 827	95.5 mm	129 mm
Master LED PAR30L 40W 30D 840	95.5 mm	129 mm

General Information	
Cap-Base	E27
Light Technical	
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Voltage (Nom)	220-240 V
Starting Time (Nom)	0.5 s
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	PAR30L

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Luminous Intensity (Nom)
929001353808	Master LED PAR30L 20W 15D 830	15 degree(s)	3000 K	18,000 cd
929001354008	Master LED PAR30L 20W 30D 830	30 degree(s)	3000 K	5,400 cd
929001354108	Master LED PAR30L 20W 30D 840	30 degree(s)	4000 K	-
929001354308	Master LED PAR30L 32W 15D 830	15 degree(s)	3000 K	-
929001354408	Master LED PAR30L 32W 15D 840	15 degree(s)	4000 K	-

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Luminous Intensity (Nom)
929001354808	Master LED PAR30L 32W 30D 840	30 degree(s)	4000 K	-
929001354908	Master LED PAR30L 32W 30D 857	30 degree(s)	5700 K	-
929001374508	Master LED PAR30L 40W 15D 840	15 degree(s)	4000 K	42,000 cd
929001374708	Master LED PAR30L 40W 30D 827	30 degree(s)	2700 K	13,000 cd
929001374908	Master LED PAR30L 40W 30D 840	30 degree(s)	4000 K	14,000 cd

Temperature


MASTER LEDspot PAR High Lumen


Order Code	Full Product Name	T-Case Maximum (Nom)
929001353808	Master LED PAR30L 20W 15D 830	67 °C
929001354008	Master LED PAR30L 20W 30D 830	67 °C
929001354108	Master LED PAR30L 20W 30D 840	67 °C
929001354308	Master LED PAR30L 32W 15D 830	79 °C
929001354408	Master LED PAR30L 32W 15D 840	79 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929001354808	Master LED PAR30L 32W 30D 840	79 °C
929001354908	Master LED PAR30L 32W 30D 857	79 °C
929001374508	Master LED PAR30L 40W 15D 840	90 °C
929001374708	Master LED PAR30L 40W 30D 827	90 °C
929001374908	Master LED PAR30L 40W 30D 840	90 °C


Approval and Application


Order Code	Full Product Name	Energy Consumption kWh/1000 h
929001353808	Master LED PAR30L 20W 15D 830	20 kWh
929001354008	Master LED PAR30L 20W 30D 830	20 kWh
929001354108	Master LED PAR30L 20W 30D 840	20 kWh
929001354308	Master LED PAR30L 32W 15D 830	32 kWh
929001354408	Master LED PAR30L 32W 15D 840	32 kWh
929001354808	Master LED PAR30L 32W 30D 840	32 kWh
929001354908	Master LED PAR30L 32W 30D 857	32 kWh
929001374508	Master LED PAR30L 40W 15D 840	40 kWh
929001374708	Master LED PAR30L 40W 30D 827	40 kWh
929001374908	Master LED PAR30L 40W 30D 840	40 kWh







MASTER LEDspot PAR High Lumen









Accent Diagrams




Accent Diagram - Master LED PAR30L 40W 15D 840




Accent Diagram - Master LED PAR30L 40W 30D 840




Accent Diagram - Master LED PAR30L 32W 30D 840



Accent Diagram - Master LED PAR30L 32W 15D 830




Accent Diagram - Master LED PAR30L 40W 30D 827




Accent Diagram - Master LED PAR30L 32W 15D 840

MASTER LEDspot PAR High Lumen


Accent Diagrams




Accent Diagram - Master LED PAR30L 32W 30D 857



Accent Diagram - Master LED PAR30L 20W 30D 840




Accent Diagram - Master LED PAR30L 20W 15D 830




Accent Diagram - Master LED PAR30L 20W 30D 830


Beam Diagrams



Beam diagram - Master LED PAR30L 32W 15D 830




Beam diagram - Master LED PAR30L 40W 30D 827




Beam diagram - Master LED PAR30L 32W 30D 857

Beam Diagrams




h (m)	E_0 (lx)	d(m) VBA	$^{1}/_{2}I_{max}$	$^{1}/_{2}E_0$
1.0	28550		0.28	0.28
1.5	12689		0.42	0.42
2.0	7138		0.56	0.56
2.5	4568		0.70	0.70
3.0	3172		0.84	0.84
3.5	2331		0.98	0.98
4.0	1784		1.12	1.12
4.5	1410		1.26	1.26

Beam diagram - Master LED PAR30L 32W 15D 840




h (m)	E_0 (lx)	d(m) VBA	$^{1}/_{2}I_{max}$	$^{1}/_{2}E_0$
1.0	15663		0.57	0.54
1.5	6961		0.86	0.80
2.0	3916		1.15	1.07
2.5	2506		1.43	1.34
3.0	1740		1.72	1.61
3.5	1279		2.01	1.88
4.0	979		2.29	2.14
4.5	773		2.58	2.41

Beam diagram - Master LED PAR30L 40W 30D 840




h (m)	E_0 (lx)	d(m) VBA	$^{1}/_{2}I_{max}$	$^{1}/_{2}E_0$
1.0	7325		0.50	0.46
1.5	3256		0.75	0.69
2.0	1831		1.00	0.92
2.5	1172		1.25	1.15
3.0	814		1.50	1.39
3.5	598		1.75	1.62
4.0	458		1.99	1.85
4.5	362		2.24	2.08

Beam diagram - Master LED PAR30L 20W 30D 840




h (m)	E_0 (lx)	d(m) VBA	$^{1}/_{2}I_{max}$	$^{1}/_{2}E_0$
1.0	7394		0.46	0.46
1.5	3286		0.69	0.69
2.0	1848		0.92	0.92
2.5	1183		1.15	1.15
3.0	822		1.39	1.39
3.5	604		1.62	1.62
4.0	462		1.85	1.85
4.5	365		2.08	2.08

Beam diagram - Master LED PAR30L 20W 30D 830




h (m)	E_0 (lx)	d(m) VBA	$^{1}/_{2}I_{max}$	$^{1}/_{2}E_0$
1.0	11294		0.54	0.50
1.5	5020		0.80	0.75
2.0	2824		1.07	1.00
2.5	1807		1.34	1.25
3.0	1255		1.61	1.50
3.5	922		1.88	1.75
4.0	706		2.14	1.99
4.5	558		2.41	2.24

Beam diagram - Master LED PAR30L 32W 30D 840



h (m)	E_0 (lx)	d(m) VBA	$^{1}/_{2}I_{max}$	$^{1}/_{2}E_0$
1.0	40955		0.28	0.28
1.5	18202		0.42	0.42
2.0	10239		0.56	0.56
2.5	6553		0.70	0.70
3.0	4551		0.84	0.84
3.5	3343		0.98	0.98
4.0	2560		1.12	1.12
4.5	2022		1.26	1.26

Beam diagram - Master LED PAR30L 40W 15D 840



h (m)	E_0 (lx)	d(m) VBA	$^{1}/_{2}I_{max}$	$^{1}/_{2}E_0$
1.0	19912		0.28	0.28
1.5	8850		0.42	0.42
2.0	4978		0.56	0.56
2.5	3186		0.70	0.70
3.0	2212		0.84	0.84
3.5	1625		0.98	0.98
4.0	1244		1.12	1.12
4.5	983		1.26	1.26

Beam diagram - Master LED PAR30L 20W 15D 830

MASTER LEDspot PAR High Lumen

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

www.lighting.philips.com
2023, May 15 - data subject to change