



Simply great LED

Ledinaire High-bay

The Ledinaire range contains a selection of popular off-the-shelf LED luminaires, each of which come with the high Philips' quality levels and competitive price. Reliable, energy-efficient and affordable – just what you need.

Benefits

- Philips quality and reliability
- Energy savings
- Wide application coverage

Features

- Modern, unobtrusive design
- Two lumen packages and sizes; 10,000lm with 24cm diameter, 20,000lm with 34cm diameter
- The IP65 rating is perfect for any application
- Including IP65 connector
- Single suspension with installation hook(included) or pipe mounting(not included)
- Optional reflector accessory for medium beam
- Non-dimming with driver on board

Application

- Warehouses & Logistic centres
- General Manufacturing
- Exhibition halls & high ceiling lounges

Ledinaire High-bay

Versions



Product details



Accessories



Ordercode 33992499



Ordercode 33994899

Ledinaire High-bay

Application Conditions

Ambient temperature range	-20 to +45 °C
Maximum dim level	Not applicable
Suitable for random switching	Yes

Approval and Application

Mech. impact protection code	IK06
Ingress protection code	IP65

Controls and Dimming

Dimmable	No
----------	----

Operating and Electrical

Input Voltage	220 to 240 V
---------------	--------------

General Information

Beam angle of light source	100 °
CE mark	CE mark
Protection class IEC	Safety class I
Driver included	Yes
ENEC mark	-
Flammability mark	NO
Glow-wire test	Temperature 650 °C, duration 30 s
Light source replaceable	No
Number of gear units	1 unit
Optic type	WB

Initial Performance (IEC Compliant)

Initial chromaticity	(0.38, 0.38) SDCM <5
Init. Corr. Colour Temperature	4000 K
Init. Colour Rendering Index	>80
Luminous flux tolerance	+/-10%

Mechanical and Housing

Colour	Dark Grey
--------	-----------

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
33996299	BYO20P LED100S/840 PSU WB GR	103 lm/W	10000 lm	97 W
33998699	BYO21P LED200S/840 PSU WB GR	105 lm/W	20000 lm	190 W

