



# Switch light settings without switching bulbs

## LED SceneSwitch

Philips SceneSwitch LED bulbs, adapt your room's ambiance to suit whatever you're doing, by changing the setting from cool day light to warm white, or dimming the brightness. All you need is your existing switch no extra installation is required.

### Benefits

- Long life -- lowers maintenance costs by reducing re-lamp frequency
- Excellent color consistency with high 80+ color rendering (CRI)
- Create your own scene with one lamp simply using your existing light switch

### Features

- All-in-one replacement lamp that gives you three different light settings
- Plug and play with existing E26 medium screw base
- 15,000 hour rated average life
- Instant on
- ENERGY STAR qualified

### Application

- Hotels/Motels
- Restaurants
- Residential & Assisted Living

# LED SceneSwitch

## Versions



E26 A19 Frosted





E26 A19 Frosted



E26 A19 Frosted

## Dimensional drawing



| Product                           | D       | C      |
|-----------------------------------|---------|--------|
| 9.5A19/LED/827-50-22/ND SSCC 120V | 61.0 mm | 111 mm |
| 9A19/LED/827-25-22/ND SSWG 120V   | 61.0 mm | 111 mm |

| Product                   | D       | C      |
|---------------------------|---------|--------|
| 9A19/LED/850/ND SSDL 120V | 61.0 mm | 111 mm |

LED SceneSwitch

|                                       |                |
|---------------------------------------|----------------|
| Approval and Application              |                |
| Energy Efficiency Label (EEL)         | Not applicable |
| Controls and Dimming                  |                |
| Dimmable                              | No             |
| Operating and Electrical              |                |
| Voltage (Nom)                         | 120 V          |
| Wattage Equivalent                    | 60 W           |
| Starting Time (Nom)                   | 0.5 s          |
| General Information                   |                |
| Cap-Base                              | E26            |
| Nominal Lifetime (Nom)                | 15000 h        |
| Switching Cycle                       | 100000X        |
| Light Technical                       |                |
| Color Rendering Index (Nom)           | 80             |
| Llmf At End Of Nominal Lifetime (Nom) | 70 %           |
| Mechanical and Housing                |                |
| Bulb Finish                           | Frosted        |
| Bulb Shape                            | A19 (A19)      |

Approval and Application

| Order Code   | Full Product Name                 | Energy Consumption kWh/1000 h |
|--------------|-----------------------------------|-------------------------------|
| 929001261304 | 9A19/LED/827-25-22/ND SSWG 120V   | - kWh                         |
| 929001261404 | 9A19/LED/850/ND SSDL 120V         | - kWh                         |
| 929001263204 | 9.5A19/LED/827-50-22/ND SSCC 120V | 9.5-8-3 kWh                   |

Operating and Electrical

| Order Code   | Full Product Name               | Input Frequency | Power (Rated) |
|--------------|---------------------------------|-----------------|---------------|
|              |                                 |                 | (Nom)         |
| 929001261304 | 9A19/LED/827-25-22/ND SSWG 120V | 50 to 60 Hz     | 9, 4, 2 W     |
| 929001261404 | 9A19/LED/850/ND SSDL 120V       | 50 to 60 Hz     | 9, 3, 1 W     |

| Order Code   | Full Product Name                 | Input Frequency | Power (Rated) |
|--------------|-----------------------------------|-----------------|---------------|
|              |                                   |                 | (Nom)         |
| 929001263204 | 9.5A19/LED/827-50-22/ND SSCC 120V | 60 Hz           | 9.5 W         |

Light Technical

| Order Code   | Full Product Name               | Beam Angle (Nom) | Color Code  | Correlated Color Temperature | Luminous Flux     |
|--------------|---------------------------------|------------------|-------------|------------------------------|-------------------|
|              |                                 |                  |             | (Nom)                        | (Nom)             |
| 929001261304 | 9A19/LED/827-25-22/ND SSWG 120V | 300 °            | 827/825/822 | - K                          | 800 / 320 / 80 lm |
| 929001261404 | 9A19/LED/850 /ND SSDL 120V      | 300 °            | 850         | 5000 K                       | 800-320-80 lm     |

| Order Code   | Full Product Name                 | Beam Angle (Nom) | Color Code  | Correlated Color Temperature | Luminous Flux |
|--------------|-----------------------------------|------------------|-------------|------------------------------|---------------|
|              |                                   |                  |             | (Nom)                        | (Nom)         |
| 929001263204 | 9.5A19/LED/827-50-22/ND SSCC 120V | -                | 827-850-822 | 2700, 5000, 2200 K           | 800 lm        |

Temperature

| Order Code   | Full Product Name                 | T-Case Maximum (Nom) |
|--------------|-----------------------------------|----------------------|
| 929001261304 | 9A19/LED/827-25-22/ND SSWG 120V   | 80 °C                |
| 929001261404 | 9A19/LED/850/ND SSDL 120V         | 80 °C                |
| 929001263204 | 9.5A19/LED/827-50-22/ND SSCC 120V | 89 °C                |

## LED SceneSwitch

