



A TLED solution for your application

T8

Our TLEDs are available in InstantFit (Type A / Type C) or MainsFit (Ballast bypass / Type B) versions. The InstantFit lamps work on a broad variety of ballasts and LED drivers. Only InstantFit has over 15,000 lamp & ballast combinations delivering even light output, energy savings and a long lifetime. Our MainsFit products feature a double-ended design, simplifying installation while a proprietary safety circuit minimizes a shock risk. Lamp sizes range from 2-foot to 8-foot and U-bend with a variety of lumen outputs.

Benefits

- Minimizes overall lighting costs
- Offers cheapest and easiest upgrade to LED lighting technology
- Excellent compatibility with existing ballasts

Features



- InstantFit works with over 350 ballasts and drivers
- Lifetime of up to 70,000 hours & a limited warranty of up to 7-years
- Plug-and-play, ballast bypass or UL Type C options available
- Shatter-resistant, polycarbonate tubes available
- All T8 replacement TLEDs are NSF certified and most are DLC certified

Application

- Office and Shopping
- Industrial and warehouses
- Parking lots and covered car parks

T8

Versions





TLED Ess 35W FA8 T8 IF

LEDtube 500mm 13W G13

LEDtubes G13 T8 16W 4000K

LEDtube COR 8ft 42W FA8

Dimensional drawing




Product	D1	D2	B	A1	D
15.5T8-6U/COR/24-830/MF20/G 10/1	25.7 mm	28.1 mm	152 mm	570 mm	27.9 mm
15.5T8-6U/COR/24-835/MF20/G 10/1	25.7 mm	28.1 mm	152 mm	570 mm	27.9 mm
15.5T8-6U/COR/24-840/MF21/G 10/1	25.7 mm	28.1 mm	152 mm	570 mm	27.9 mm
15.5T8-6U/COR/24-850/MF21/G 10/1	25.7 mm	28.1 mm	152 mm	570 mm	27.9 mm

Product	D1	D2	A1	A2	A3
12T8/COR/48-830/MF17/G 10/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
12T8/COR/48-830/MF17/G/DIM 25/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
12T8/COR/48-835/MF17/G 10/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
12T8/COR/48-835/MF17/G/DIM 25/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
12T8/COR/48-840/MF18/G 10/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
12T8/COR/48-840/MF18/G/DIM 25/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
12T8/COR/48-850/MF18/G 10/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
12T8/COR/48-850/MF18/G/DIM 25/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
14.5T8/CNG/48-835/MF17/G 25/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
14.5T8/CNG/48-840/MF18/G 25/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
14.5T8/CNG/48-850/MF18/G 25/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
14.5T8/CNG/48-865/MF18/G 25/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
14.5T8/COR/48-5CCT/MF18/G/DIM 25/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
14.5T8/COR/48-830/MF20/G 10/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
14.5T8/COR/48-830/MF20/G/DIM 25/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
14.5T8/COR/48-835/MF20/G 10/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
14.5T8/COR/48-835/MF20/G/DIM 25/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
14.5T8/COR/48-840/MF21/G 10/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
14.5T8/COR/48-840/MF21/G/DIM 25/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
14.5T8/COR/48-850/MF21/G 10/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
14.5T8/COR/48-850/MF21/G/DIM 25/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm

Dimensional drawing


Product	D1	D2	A1	A2	A3
14T8/COR/48-830/IF20/G/DIM 10/1	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
14T8/COR/48-835/IF20/G/DIM 10/1	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
14T8/COR/48-840/IF21/G/DIM 10/1	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
14T8/COR/48-850/IF21/G/DIM 10/1	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
14T8/LED/48-5CCT/MF18/G/DS 1/10	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
14T8/LED/48-5CCT/MF18/G/DS 5/2 FB	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
16.5T8/CNG/48-835/MF20/G 25/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
16.5T8/CNG/48-840/MF21/G 25/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
16.5T8/CNG/48-850/MF21/G 25/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
9.9T8/COR/48-835/MF15/G 10/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
9.9T8/COR/48-835/MF15/G/DIM 25/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
9.9T8/COR/48-840/MF16/G 10/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
9.9T8/COR/48-840/MF16/G/DIM 25/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
9.9T8/COR/48-850/MF16/G 10/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
9.9T8/COR/48-850/MF16/G/DIM 25/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm



Product	D1	D2	A1	A2	A3
10.5T8/MAS/48-835/MF15/P 10/1	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
10.5T8/MAS/48-835/MF15/P/DIM 25/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
10.5T8/MAS/48-840/MF16/P 10/1	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
10.5T8/MAS/48-840/MF16/P/DIM 25/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
10.5T8/MAS/48-850/MF16/P 10/1	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
10.5T8/MAS/48-850/MF16/P/DIM 25/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
12.5T8/COR/48-835/FF17/G/DIM 25/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
12.5T8/COR/48-840/FF18/G/DIM 25/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
12.5T8/COR/48-850/FF18/G/DIM 25/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
14.5T8/MAS/48-830/MF20/P/DIM 25/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm

Dimensional drawing




Product	D1	D2	A1	A2	A3
14.5T8/MAS/48-835/MF20/P 10/1	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
14.5T8/MAS/48-835/ MF20/P/DIM 25/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
14.5T8/MAS/48-840/MF21/P 10/1	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
14.5T8/MAS/48-840/ MF21/P/DIM 25/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
14.5T8/MAS/48-850/MF21/P 10/1	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
14.5T8/MAS/48-850/ MF21/P/DIM 25/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
16.5T8/MAS/48-835/ MF24/P/DIM 25/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
16.5T8/MAS/48-840/ MF25/P/DIM 25/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
16.5T8/MAS/48-850/ MF25/P/DIM 25/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
16.9T8/MAS/48-835/MF25/P 10/1	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm



Product	D1	D2	A1	A2	A3
13T8/MAS/48-830/IF20/P/DIM 10/1	25.7 mm	26.3 mm	1,198.1 mm	1,205.2 mm	1,212.3 mm
13T8/MAS/48-835/IF20/P/DIM 10/1	25.7 mm	26.3 mm	1,198.1 mm	1,205.2 mm	1,212.3 mm
13T8/MAS/48-840/IF21/P/DIM 10/1	25.7 mm	26.3 mm	1,198.1 mm	1,205.2 mm	1,212.3 mm
13T8/MAS/48-850/IF21/P/DIM 10/1	25.7 mm	26.3 mm	1,198.1 mm	1,205.2 mm	1,212.3 mm
15.5T8/MAS/48-830/ IF23/P/DIM 25/1	25.7 mm	28 mm	1,198.1 mm	1,205.2 mm	1,212.3 mm
15.5T8/MAS/48-835/ IF24/P/DIM 25/1	25.7 mm	28 mm	1,198.1 mm	1,205.2 mm	1,212.3 mm
15.5T8/MAS/48-840/ IF25/P/DIM 25/1	25.7 mm	28 mm	1,198.1 mm	1,205.2 mm	1,212.3 mm
15.5T8/MAS/48-850/ IF25/P/DIM 25/1	25.7 mm	28 mm	1,198.1 mm	1,205.2 mm	1,212.3 mm
7T8/MAS/24-830/IF10/P/DIM 10/1	25.7 mm	26.3 mm	588.6 mm	595.7 mm	602.8 mm
7T8/MAS/24-835/IF10/P/DIM 10/1	25.7 mm	26.3 mm	588.6 mm	595.7 mm	602.8 mm
7T8/MAS/24-840/IF11/P/DIM 10/1	25.7 mm	26.3 mm	588.6 mm	595.7 mm	602.8 mm
7T8/MAS/24-850/IF11/P/DIM 10/1	25.7 mm	26.3 mm	588.6 mm	595.7 mm	602.8 mm
8.5T8/MAS/36-830/IF13/P/DIM 10/1	25.7 mm	26.3 mm	893.4 mm	900.5 mm	907.6 mm

Dimensional drawing

Product	D1	D2	A1	A2	A3
8.5T8/MAS/36-835/IF13/P/DIM 10/1	25.7 mm	26.3 mm	893.4 mm	900.5 mm	907.6 mm
8.5T8/MAS/36-840/IF14/P/DIM 10/1	25.7 mm	26.3 mm	893.4 mm	900.5 mm	907.6 mm
8.5T8/MAS/36-850/IF14/P/DIM 10/1	25.7 mm	26.3 mm	893.4 mm	900.5 mm	907.6 mm
8.9T8/MAS/48-830/IF15/P/DIM 10/1	25.7 mm	26.3 mm	1,198.1 mm	1,205.2 mm	1,212.3 mm
8.9T8/MAS/48-835/IF15/P/DIM 10/1	25.7 mm	26.3 mm	1,198.1 mm	1,205.2 mm	1,212.3 mm
8.9T8/MAS/48-840/IF16/P/DIM 10/1	25.7 mm	26.3 mm	1,198.1 mm	1,205.2 mm	1,212.3 mm
8.9T8/MAS/48-850/IF16/P/DIM 10/1	25.7 mm	26.3 mm	1,198.1 mm	1,205.2 mm	1,212.3 mm






Product	D1	D2	A1	A2	A3
13T8-6U/MAS/24-830/IF20/P/DIM 10/1	25.7 mm	28 mm	152 mm	570 mm	27.8 mm
13T8-6U/MAS/24-835/IF20/P/DIM 10/1	25.7 mm	28 mm	152 mm	570 mm	27.8 mm
13T8-6U/MAS/24-840/IF21/P/DIM 10/1	25.7 mm	28 mm	152 mm	570 mm	27.8 mm
13T8-6U/MAS/24-850/IF21/P/DIM 10/1	25.7 mm	28 mm	152 mm	570 mm	27.8 mm

Product	D2	A1	A2	A3
33T8/COR/96-840/MF44/G/FA8 10/1	27.9 mm	2,369.8 mm	2,378.7 mm	2,387.8 mm
33T8/COR/96-850/MF44/G/FA8 10/1	27.9 mm	2,369.8 mm	2,378.7 mm	2,387.8 mm
42T8HO/COR/96-840/MF54/G/FA8 10/1	27.9 mm	2,369.8 mm	2,378.7 mm	2,387.8 mm
42T8HO/COR/96-850/MF54/G/FA8 10/1	27.9 mm	2,369.8 mm	2,378.7 mm	2,387.8 mm

Product	D1	D2	A1	A2	A3
28T8/COR/96-835/IF40/G/FA8 10/1	25.5 mm	28 mm	2,366.9 mm	2,375.8 mm	2,384.7 mm
28T8/COR/96-840/IF42/G/FA8 10/1	25.5 mm	28 mm	2,366.9 mm	2,375.8 mm	2,384.7 mm
30T8/COR/96-835/IF39/G/FA8 10/1	25.5 mm	28 mm	2,366.9 mm	2,375.8 mm	2,384.7 mm
30T8/COR/96-840/IF42/G/FA8 10/1	25.5 mm	28 mm	2,366.9 mm	2,375.8 mm	2,384.7 mm
30T8/COR/96-850/IF42/G/FA8 10/1	25.5 mm	28 mm	2,366.9 mm	2,375.8 mm	2,384.7 mm

Dimensional drawing

Product	D1	D2	A1	A2	A3
35T8/96-3500 IF FA8 10/1	27.9	2,366.9	2,375.2 mm	2,383.5	
	mm	mm		mm	
35T8/96-4000 IF FA8 10/1	27.9	2,366.9	2,375.2 mm	2,383.5	
	mm	mm		mm	



Product	D2	A1	A2	A3
42T8HO/COR/96-840/MF54/G/R17d 10/1	27.9 mm	2,369.8 mm	2,378.7 mm	2,385.3 mm
42T8HO/COR/96-850/MF54/G/R17d 10/1	27.9 mm	2,369.8 mm	2,378.7 mm	2,385.3 mm

Product	D1	D2	A1	A2	A3
10T8/COR/48-830/IF15/G/DIM 10/1	25.7 mm	28 mm	1,198.1 mm	1,205.2 mm	1,212.3 mm
10T8/COR/48-835/IF15/G/DIM 10/1	25.7 mm	28 mm	1,198.1 mm	1,205.2 mm	1,212.3 mm
10T8/COR/48-840/IF16/G/DIM 10/1	25.7 mm	28 mm	1,198.1 mm	1,205.2 mm	1,212.3 mm
10T8/COR/48-850/IF16/G/DIM 10/1	25.7 mm	28 mm	1,198.1 mm	1,205.2 mm	1,212.3 mm
11.5T8/COR/48-835/ IF20/G/DIM 25/1	25.7 mm	26.3 mm	1,198.1 mm	1,205.2 mm	1,212.3 mm
11.5T8/COR/48-840/ IF21/G/DIM 25/1	25.7 mm	26.3 mm	1,198.1 mm	1,205.2 mm	1,212.3 mm
16T8/LED/48-840/IF18/G 25/1	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm
16T8/LED/48-850/IF18/G 25/1	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm

Product	D	A1	A2	A3	
10.5T8/COR/48-835/ IF15/G/DIM/BAA 25/1	25.7 mm	25.7 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
10.5T8/COR/48-840/ IF16/G/DIM/BAA 25/1	25.7 mm	25.7 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
10.5T8/COR/48-850/ IF16/G/DIM/BAA 25/1	25.7 mm	25.7 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
11.5T8/COR/36-830/MF13/G 10/1	25.9 mm	894.3 mm	900.5 mm	908.8 mm	
11.5T8/COR/36-835/MF13/G 10/1	25.9 mm	894.3 mm	900.5 mm	908.8 mm	
11.5T8/COR/36-840/MF14/G 10/1	25.9 mm	894.3 mm	900.5 mm	908.8 mm	
11.5T8/COR/36-850/MF14/G 10/1	25.9 mm	894.3 mm	900.5 mm	908.8 mm	

Dimensional drawing

Product	D	A1	A2	A3	
11T8/COR/48-835/ MF16/G/BAA 25/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
11T8/COR/48-840/ MF16/G/BAA 25/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
11T8/COR/48-850/ MF16/G/BAA 25/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
14T8/COR/48-835/ IF21/G/DIM/BAA 25/1	25.7 mm	25.7 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
14T8/COR/48-840/ IF22/G/DIM/BAA 25/1	25.7 mm	25.7 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
14T8/COR/48-850/ IF22/G/DIM/BAA 25/1	25.7 mm	25.7 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
15.5T8/COR/48-835/ MF21/G/BAA 25/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
15.5T8/COR/48-840/ MF21/G/BAA 25/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
15.5T8/COR/48-850/ MF21/G/BAA 25/1	25.7 mm	28 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
15T8/COR/48-835/MF20/G/ 120-347V 25/1	25.7 mm	29 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
15T8/COR/48-840/MF21/G/ 120-347V 25/1	25.7 mm	29 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
15T8/COR/48-850/MF21/G/ 120-347V 25/1	25.7 mm	29 mm	1,198.2 mm	1,205.3 mm	1,212.4 mm
8.5T8/COR/24-830/MF11/G 10/1	25.9 mm	589.5 mm	595.7 mm	604 mm	
8.5T8/COR/24-835/MF11/G 10/1	25.9 mm	589.5 mm	595.7 mm	604 mm	
8.5T8/COR/24-835/ MF11/G/BAA 25/1	25.9 mm	28 mm	589.5 mm	595.7 mm	604 mm
8.5T8/COR/24-840/MF11/G 10/1	25.9 mm	589.5 mm	595.7 mm	604 mm	
8.5T8/COR/24-840/ MF11/G/BAA 25/1	25.9 mm	28 mm	589.5 mm	595.7 mm	604 mm
8.5T8/COR/24-850/MF11/G 10/1	25.9 mm	589.5 mm	595.7 mm	604 mm	
8.5T8/COR/24-850/ MF11/G/BAA 25/1	25.9 mm	28 mm	589.5 mm	595.7 mm	604 mm

General Information

Switching Cycle 50,000

Light Technical

LLMF At End Of Nominal Lifetime (Nom) 70 %

Mechanical and Housing

Bulb Finish Frosted

Bulb Shape Tube, double-ended

General Information

Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)	Nominal lifetime
929002317304	12.5T8/COR/48-840/FF18/G/DIM 25/1	G13	-	50,000 hour(s)
929002317404	12.5T8/COR/48-850/FF18/G/DIM 25/1	G13	-	50,000 hour(s)
929002402204	12.5T8/COR/48-835/FF17/G/DIM 25/1	G13	-	50,000 hour(s)
929001307804	35T8/96-3500 IF FA8 10/1	FA8	-	50,000 hour(s)
929001314604	35T8/96-4000 IF FA8 10/1	FA8	-	50,000 hour(s)
929001967504	8.5T8/MAS/36-830/IF13/P/DIM 10/1	G13	-	70,000 hour(s)
929001967604	8.5T8/MAS/36-840/IF14/P/DIM 10/1	G13	-	70,000 hour(s)
929001967704	8.5T8/MAS/36-850/IF14/P/DIM 10/1	G13	-	70,000 hour(s)
929001967904	8.5T8/MAS/36-835/IF13/P/DIM 10/1	G13	-	70,000 hour(s)
929001986904	7T8/MAS/24-830/IF10/P/DIM 10/1	G13	-	70,000 hour(s)
929001987004	7T8/MAS/24-835/IF10/P/DIM 10/1	G13	-	70,000 hour(s)
929001987104	7T8/MAS/24-840/IF11/P/DIM 10/1	G13	-	70,000 hour(s)
929001987204	7T8/MAS/24-850/IF11/P/DIM 10/1	G13	-	70,000 hour(s)
929001987404	13T8-6U/MAS/24-830/IF20/P/DIM 10/1	G13	-	70,000 hour(s)
929001987504	13T8-6U/MAS/24-835/IF20/P/DIM 10/1	G13	-	70,000 hour(s)
929001987604	13T8-6U/MAS/24-840/IF21/P/DIM 10/1	G13	-	70,000 hour(s)
929001987704	13T8-6U/MAS/24-850/IF21/P/DIM 10/1	G13	-	70,000 hour(s)
929001397634	13T8/MAS/48-830/IF20/P/DIM 10/1	G13	-	70,000 hour(s)

Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)	Nominal lifetime
929001397734	13T8/MAS/48-835/IF20/P/DIM 10/1	G13	-	70,000 hour(s)
929001397834	13T8/MAS/48-840/IF21/P/DIM 10/1	G13	-	70,000 hour(s)
929001397934	13T8/MAS/48-850/IF21/P/DIM 10/1	G13	-	70,000 hour(s)
929002016204	15.5T8/MAS/48-830/IF23/P/DIM 25/1	G13	-	70,000 hour(s)
929002016304	15.5T8/MAS/48-835/IF24/P/DIM 25/1	G13	-	70,000 hour(s)
929002016404	15.5T8/MAS/48-840/IF25/P/DIM 25/1	G13	-	70,000 hour(s)
929002016504	15.5T8/MAS/48-850/IF25/P/DIM 25/1	G13	-	70,000 hour(s)
929003025304	8.9T8/MAS/48-830/IF15/P/DIM 10/1	G13	-	70,000 hour(s)
929003025404	8.9T8/MAS/48-835/IF15/P/DIM 10/1	G13	-	70,000 hour(s)
929003025504	8.9T8/MAS/48-840/IF16/P/DIM 10/1	G13	-	70,000 hour(s)
929003025604	8.9T8/MAS/48-850/IF16/P/DIM 10/1	G13	-	70,000 hour(s)
929001897204	30T8/COR/96-835/IF39/G/FA8 10/1	FA8	-	50,000 hour(s)
929001897304	30T8/COR/96-840/IF42/G/FA8 10/1	FA8	-	50,000 hour(s)
929001897404	30T8/COR/96-850/IF42/G/FA8 10/1	FA8	-	50,000 hour(s)
929002483704	9.9T8/COR/48-835/MF15/G 10/1	G13	-	50,000 hour(s)
929002483804	9.9T8/COR/48-840/MF16/G 10/1	G13	-	50,000 hour(s)
929002483904	9.9T8/COR/48-850/MF16/G 10/1	G13	-	50,000 hour(s)
929002484004	12T8/COR/48-830/MF17/G 10/1	G13	-	50,000 hour(s)

Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)	Nominal lifetime
929002484104	12T8/COR/48-835/MF17/G 10/1	G13	-	50,000 hour(s)
929002484204	12T8/COR/48-840/MF18/G 10/1	G13	-	50,000 hour(s)
929002484304	12T8/COR/48-850/MF18/G 10/1	G13	-	50,000 hour(s)
929002484404	14.5T8/COR/48-830/MF20/G 10/1	G13	-	50,000 hour(s)
929002484504	14.5T8/COR/48-835/MF20/G 10/1	G13	-	50,000 hour(s)
929002484604	14.5T8/COR/48-840/MF21/G 10/1	G13	-	50,000 hour(s)
929002484704	14.5T8/COR/48-850/MF21/G 10/1	G13	-	50,000 hour(s)
929003523704	9.9T8/COR/48-835/MF15/G/DIM 25/1	G13	-	50,000 hour(s)
929003523804	9.9T8/COR/48-840/MF16/G/DIM 25/1	G13	-	50,000 hour(s)
929003523904	9.9T8/COR/48-850/MF16/G/DIM 25/1	G13	-	50,000 hour(s)
929003524104	12T8/COR/48-830/MF17/G/DIM 25/1	G13	-	50,000 hour(s)
929003524204	12T8/COR/48-835/MF17/G/DIM 25/1	G13	-	50,000 hour(s)
929003524304	12T8/COR/48-840/MF18/G/DIM 25/1	G13	-	50,000 hour(s)
929003524404	12T8/COR/48-850/MF18/G/DIM 25/1	G13	-	50,000 hour(s)
929003524604	14.5T8/COR/48-830/MF20/G/DIM 25/1	G13	-	50,000 hour(s)
929003524704	14.5T8/COR/48-835/MF20/G/DIM 25/1	G13	-	50,000 hour(s)
929003524804	14.5T8/COR/48-840/MF21/G/DIM 25/1	G13	-	50,000 hour(s)
929003524904	14.5T8/COR/48-850/MF21/G/DIM 25/1	G13	-	50,000 hour(s)
929001960604	16T8/LED/48-840/IF18/G 25/1	G13	-	36,000 hour(s)
929001960704	16T8/LED/48-850/IF18/G 25/1	G13	-	36,000 hour(s)
929003112304	42T8HO/COR/96-840/MF54/G/ R17d 10/1	R17D	-	50,000 hour(s)
929003112404	42T8HO/COR/96-850/MF54/G/ R17d 10/1	R17D	-	50,000 hour(s)
929001934604	15.5T8-6U/COR/24-830/MF20/G 10/1	2G13	-	50,000 hour(s)
929001934704	15.5T8-6U/COR/24-835/MF20/G 10/1	2G13	-	50,000 hour(s)
929001934804	15.5T8-6U/COR/24-840/MF21/G 10/1	2G13	-	50,000 hour(s)

Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)	Nominal lifetime
929001934904	15.5T8-6U/COR/24-850/MF21/G 10/1	2G13	-	50,000 hour(s)
929001343034	14T8/COR/48-830/IF20/G/DIM 10/1	G13	-	70,000 hour(s)
929001343134	14T8/COR/48-835/IF20/G/DIM 10/1	G13	-	70,000 hour(s)
929001343234	14T8/COR/48-840/IF21/G/DIM 10/1	G13	-	70,000 hour(s)
929001343334	14T8/COR/48-850/IF21/G/DIM 10/1	G13	-	70,000 hour(s)
929001991734	10T8/COR/48-840/IF16/G/DIM 10/1	G13	-	70,000 hour(s)
929001991834	10T8/COR/48-850/IF16/G/DIM 10/1	G13	-	70,000 hour(s)
929002252734	10T8/COR/48-830/IF15/G/DIM 10/1	G13	-	70,000 hour(s)
929002252834	10T8/COR/48-835/IF15/G/DIM 10/1	G13	-	70,000 hour(s)
929003556504	11.5T8/COR/48-835/IF20/G/DIM 25/1	G13	-	50,000 hour(s)
929003556604	11.5T8/COR/48-840/IF21/G/DIM 25/1	G13	-	50,000 hour(s)
929003556704	28T8/COR/96-835/IF40/G/FA8 10/1	FA8	-	50,000 hour(s)
929003556804	28T8/COR/96-840/IF42/G/FA8 10/1	FA8	-	50,000 hour(s)
929001933804	8.5T8/COR/24-830/MF11/G 10/1	G13	-	50,000 hour(s)
929001933904	8.5T8/COR/24-835/MF11/G 10/1	G13	-	50,000 hour(s)
929001934004	8.5T8/COR/24-840/MF11/G 10/1	G13	-	50,000 hour(s)
929001934104	8.5T8/COR/24-850/MF11/G 10/1	G13	-	50,000 hour(s)
929001934204	11.5T8/COR/36-830/MF13/G 10/1	G13	-	50,000 hour(s)
929001934304	11.5T8/COR/36-835/MF13/G 10/1	G13	-	50,000 hour(s)
929001934404	11.5T8/COR/36-840/MF14/G 10/1	G13	-	50,000 hour(s)
929001934504	11.5T8/COR/36-850/MF14/G 10/1	G13	-	50,000 hour(s)
929002497304	11T8/COR/48-835/MF16/G/BAA 25/1	G13	-	50,000 hour(s)
929002497404	11T8/COR/48-840/MF16/G/BAA 25/1	G13	-	50,000 hour(s)
929002497504	11T8/COR/48-850/MF16/G/BAA 25/1	G13	-	50,000 hour(s)
929002497604	15.5T8/COR/48-835/MF21/G/BAA 25/1	G13	-	50,000 hour(s)

Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)	Nominal lifetime
929002497704	15.5T8/COR/48-840/MF21/G/BAA 25/1	G13	-	50,000 hour(s)
929002497804	15.5T8/COR/48-850/MF21/G/BAA 25/1	G13	-	50,000 hour(s)
929002497904	8.5T8/COR/24-835/MF11/G/BAA 25/1	G13	-	50,000 hour(s)
929002498004	8.5T8/COR/24-840/MF11/G/BAA 25/1	G13	-	50,000 hour(s)
929002498104	8.5T8/COR/24-850/MF11/G/BAA 25/1	G13	-	50,000 hour(s)
929003051303	14T8/LED/48-5CCT/MF18/G/DS 5/2 FB	G13	50,000 hour(s)	50,000 hour(s)
929003051333	14T8/LED/48-5CCT/MF18/G/DS 1/10	G13	50,000 hour(s)	50,000 hour(s)
929003540104	14.5T8/COR/48-5CCT/MF18/G/DIM 25/1	G13	-	50,000 hour(s)
929002325134	10.5T8/MAS/48-835/MF15/P 10/1	G13	-	70,000 hour(s)
929002325234	10.5T8/MAS/48-840/MF16/P 10/1	G13	-	70,000 hour(s)
929002325334	10.5T8/MAS/48-850/MF16/P 10/1	G13	-	70,000 hour(s)
929002325534	14.5T8/MAS/48-835/MF20/P 10/1	G13	-	70,000 hour(s)
929002325634	14.5T8/MAS/48-840/MF21/P 10/1	G13	-	70,000 hour(s)
929002325734	14.5T8/MAS/48-850/MF21/P 10/1	G13	-	70,000 hour(s)
929002442434	16.9T8/MAS/48-835/MF25/P 10/1	G13	-	70,000 hour(s)
929003525104	10.5T8/MAS/48-835/MF15/P/DIM 25/1	G13	-	70,000 hour(s)
929003525204	10.5T8/MAS/48-840/MF16/P/DIM 25/1	G13	-	70,000 hour(s)
929003525304	10.5T8/MAS/48-850/MF16/P/DIM 25/1	G13	-	70,000 hour(s)
929003525404	14.5T8/MAS/48-830/MF20/P/DIM 25/1	G13	-	70,000 hour(s)
929003525504	14.5T8/MAS/48-835/MF20/P/DIM 25/1	G13	-	70,000 hour(s)
929003525604	14.5T8/MAS/48-840/MF21/P/DIM 25/1	G13	-	70,000 hour(s)
929003525704	14.5T8/MAS/48-850/MF21/P/DIM 25/1	G13	-	70,000 hour(s)
929003525804	16.5T8/MAS/48-835/MF24/P/DIM 25/1	G13	-	70,000 hour(s)

Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)	Nominal lifetime
929003525904	16.5T8/MAS/48-840/MF25/P/DIM 25/1	G13	-	70,000 hour(s)
929003526004	16.5T8/MAS/48-850/MF25/P/DIM 25/1	G13	-	70,000 hour(s)
929003523304	15T8/COR/48-835/MF20/G/120-347V 25/1	G13	-	50,000 hour(s)
929003523404	15T8/COR/48-840/MF21/G/120-347V 25/1	G13	-	50,000 hour(s)
929003523504	15T8/COR/48-850/MF21/G/120-347V 25/1	G13	-	50,000 hour(s)
929003144504	10.5T8/COR/48-835/IF15/G/DIM/BAA 25/1	G13	-	50,000 hour(s)
929003144604	10.5T8/COR/48-840/IF16/G/DIM/BAA 25/1	G13	-	50,000 hour(s)
929003144704	10.5T8/COR/48-850/IF16/G/DIM/BAA 25/1	G13	-	50,000 hour(s)
929003144804	14T8/COR/48-835/IF21/G/DIM/BAA 25/1	G13	-	50,000 hour(s)
929003144904	14T8/COR/48-840/IF22/G/DIM/BAA 25/1	G13	-	50,000 hour(s)
929003145004	14T8/COR/48-850/IF22/G/DIM/BAA 25/1	G13	-	50,000 hour(s)
929003474504	14.5T8/CNG/48-835/MF17/G 25/1	G13	-	50,000 hour(s)
929003474604	14.5T8/CNG/48-840/MF18/G 25/1	G13	-	50,000 hour(s)
929003474704	14.5T8/CNG/48-850/MF18/G 25/1	G13	-	50,000 hour(s)
929003474804	14.5T8/CNG/48-865/MF18/G 25/1	G13	-	50,000 hour(s)
929003510604	16.5T8/CNG/48-835/MF20/G 25/1	G13	-	50,000 hour(s)
929003510704	16.5T8/CNG/48-840/MF21/G 25/1	G13	-	50,000 hour(s)
929003510804	16.5T8/CNG/48-850/MF21/G 25/1	G13	-	50,000 hour(s)
92900309940	42T8HO/COR/96-840/MF54/G/FA8 10/1	FA8	-	50,000 hour(s)
92900309950	42T8HO/COR/96-850/MF54/G/FA8 10/1	FA8	-	50,000 hour(s)
929003112104	33T8/COR/96-840/MF44/G/FA8 10/1	FA8	-	50,000 hour(s)
929003112204	33T8/COR/96-850/MF44/G/FA8 10/1	FA8	-	50,000 hour(s)

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color rendering index		
				(CRI)	Color Code	Luminous Flux
929002317304	12.5T8/COR/48-840/FF18/G/DIM 25/1	220 degree(s)	4000 K	82	840	1,800 lumen
929002317404	12.5T8/COR/48-850/FF18/G/DIM 25/1	220 degree(s)	5000 K	82	850	1,800 lumen
929002402204	12.5T8/COR/48-835/FF17/G/DIM 25/1	220 degree(s)	3500 K	82	835	1,700 lumen
929001307804	35T8/96-3500 IF FA8 10/1	180 degree(s)	3500 K	82	835	4,000 lumen
929001314604	35T8/96-4000 IF FA8 10/1	180 degree(s)	4000 K	82	840	4,200 lumen
929001967504	8.5T8/MAS/36-830/IF13/P/DIM 10/1	180 degree(s)	3000 K	80	830	1,350 lumen
929001967604	8.5T8/MAS/36-840/IF14/P/DIM 10/1	180 degree(s)	4000 K	80	840	1,400 lumen
929001967704	8.5T8/MAS/36-850/IF14/P/DIM 10/1	180 degree(s)	5000 K	80	850	1,400 lumen
929001967904	8.5T8/MAS/36-835/IF13/P/DIM 10/1	180 degree(s)	3500 K	80	835	1,350 lumen
929001986904	7T8/MAS/24-830/IF10/P/DIM 10/1	180 degree(s)	3000 K	80	830	1,150 lumen
929001987004	7T8/MAS/24-835/IF10/P/DIM 10/1	180 degree(s)	3500 K	80	835	1,150 lumen
929001987104	7T8/MAS/24-840/IF11/P/DIM 10/1	180 degree(s)	4000 K	80	840	1,200 lumen
929001987204	7T8/MAS/24-850/IF11/P/DIM 10/1	180 degree(s)	5000 K	80	850	1,200 lumen
929001987404	13T8-6U/MAS/24-830/IF20/P/DIM 10/1	180 degree(s)	3000 K	80	830	2,000 lumen
929001987504	13T8-6U/MAS/24-835/IF20/P/DIM 10/1	180 degree(s)	3500 K	80	835	2,000 lumen
929001987604	13T8-6U/MAS/24-840/IF21/P/DIM 10/1	180 degree(s)	4000 K	80	840	2,100 lumen
929001987704	13T8-6U/MAS/24-850/IF21/P/DIM 10/1	180 degree(s)	5000 K	80	850	2,100 lumen
929001397634	13T8/MAS/48-830/IF20/P/DIM 10/1	180 degree(s)	3000 K	80	830	2,000 lumen
929001397734	13T8/MAS/48-835/IF20/P/DIM 10/1	180 degree(s)	3500 K	80	835	2,000 lumen
929001397834	13T8/MAS/48-840/IF21/P/DIM 10/1	180 degree(s)	4000 K	80	840	2,100 lumen
929001397934	13T8/MAS/48-850/IF21/P/DIM 10/1	180 degree(s)	5000 K	80	850	2,100 lumen
929002016204	15.5T8/MAS/48-830/IF23/P/DIM 25/1	180 degree(s)	3000 K	80	830	2,350 lumen
929002016304	15.5T8/MAS/48-835/IF24/P/DIM 25/1	180 degree(s)	3500 K	80	835	2,400 lumen
929002016404	15.5T8/MAS/48-840/IF25/P/DIM 25/1	180 degree(s)	4000 K	80	840	2,500 lumen
929002016504	15.5T8/MAS/48-850/IF25/P/DIM 25/1	180 degree(s)	5000 K	80	850	2,500 lumen
929003025304	8.9T8/MAS/48-830/IF15/P/DIM 10/1	180 degree(s)	3000 K	80	830	1,500 lumen
929003025404	8.9T8/MAS/48-835/IF15/P/DIM 10/1	180 degree(s)	3500 K	80	835	1,500 lumen
929003025504	8.9T8/MAS/48-840/IF16/P/DIM 10/1	180 degree(s)	4000 K	80	840	1,600 lumen
929003025604	8.9T8/MAS/48-850/IF16/P/DIM 10/1	180 degree(s)	5000 K	80	850	1,600 lumen
929001897204	30T8/COR/96-835/IF39/G/FA8 10/1	240 degree(s)	3500 K	80	835	3,950 lumen
929001897304	30T8/COR/96-840/IF42/G/FA8 10/1	240 degree(s)	4000 K	80	840	4,200 lumen
929001897404	30T8/COR/96-850/IF42/G/FA8 10/1	240 degree(s)	5000 K	80	850	4,200 lumen
929002483704	9.9T8/COR/48-835/MF15/G 10/1	240 degree(s)	3500 K	80	835	1,550 lumen
929002483804	9.9T8/COR/48-840/MF16/G 10/1	240 degree(s)	4000 K	80	840	1,600 lumen
929002483904	9.9T8/COR/48-850/MF16/G 10/1	240 degree(s)	5000 K	80	850	1,600 lumen
929002484004	12T8/COR/48-830/MF17/G 10/1	240 degree(s)	3000 K	80	830	1,700 lumen
929002484104	12T8/COR/48-835/MF17/G 10/1	240 degree(s)	3500 K	80	835	1,700 lumen
929002484204	12T8/COR/48-840/MF18/G 10/1	240 degree(s)	4000 K	80	840	1,800 lumen
929002484304	12T8/COR/48-850/MF18/G 10/1	240 degree(s)	5000 K	80	850	1,800 lumen
929002484404	14.5T8/COR/48-830/MF20/G 10/1	240 degree(s)	3000 K	80	830	2,000 lumen
929002484504	14.5T8/COR/48-835/MF20/G 10/1	240 degree(s)	3500 K	80	835	2,000 lumen
929002484604	14.5T8/COR/48-840/MF21/G 10/1	240 degree(s)	4000 K	80	840	2,100 lumen
929002484704	14.5T8/COR/48-850/MF21/G 10/1	240 degree(s)	5000 K	80	850	2,100 lumen
929003523704	9.9T8/COR/48-835/MF15/G/DIM 25/1	240 degree(s)	3500 K	80	835	1,550 lumen
929003523804	9.9T8/COR/48-840/MF16/G/DIM 25/1	240 degree(s)	4000 K	80	840	1,600 lumen
929003523904	9.9T8/COR/48-850/MF16/G/DIM 25/1	240 degree(s)	5000 K	80	850	1,600 lumen
929003524104	12T8/COR/48-830/MF17/G/DIM 25/1	240 degree(s)	3000 K	80	830	1,700 lumen
929003524204	12T8/COR/48-835/MF17/G/DIM 25/1	240 degree(s)	3500 K	80	835	1,700 lumen
929003524304	12T8/COR/48-840/MF18/G/DIM 25/1	240 degree(s)	4000 K	80	840	1,800 lumen
929003524404	12T8/COR/48-850/MF18/G/DIM 25/1	240 degree(s)	5000 K	80	850	1,800 lumen
929003524604	14.5T8/COR/48-830/MF20/G/DIM 25/1	240 degree(s)	3000 K	80	830	2,000 lumen

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color rendering index		Luminous Flux
				(CRI)	Color Code	
929003524704	14.5T8/COR/48-835/MF20/G/DIM 25/1	240 degree(s)	3500 K	80	835	2,000 lumen
929003524804	14.5T8/COR/48-840/MF21/G/DIM 25/1	240 degree(s)	4000 K	80	840	2,100 lumen
929003524904	14.5T8/COR/48-850/MF21/G/DIM 25/1	240 degree(s)	5000 K	80	850	2,100 lumen
929001960604	16T8/LED/48-840/IF18/G 25/1	240 degree(s)	4000 K	80	840	1,800 lumen
929001960704	16T8/LED/48-850/IF18/G 25/1	240 degree(s)	5000 K	80	850	1,800 lumen
929003112304	42T8HO/COR/96-840/MF54/G/R17d 10/1	240 degree(s)	4000 K	80	840	5,400 lumen
929003112404	42T8HO/COR/96-850/MF54/G/R17d 10/1	240 degree(s)	5000 K	80	850	5,400 lumen
929001934604	15.5T8-6U/COR/24-830/MF20/G 10/1	180 degree(s)	3000 K	82	830	2,000 lumen
929001934704	15.5T8-6U/COR/24-835/MF20/G 10/1	180 degree(s)	3500 K	82	835	2,000 lumen
929001934804	15.5T8-6U/COR/24-840/MF21/G 10/1	180 degree(s)	4000 K	82	840	2,100 lumen
929001934904	15.5T8-6U/COR/24-850/MF21/G 10/1	180 degree(s)	5000 K	82	850	2,100 lumen
929001343034	14T8/COR/48-830/IF20/G/DIM 10/1	240 degree(s)	3000 K	82	830	2,000 lumen
929001343134	14T8/COR/48-835/IF20/G/DIM 10/1	240 degree(s)	3500 K	82	835	2,000 lumen
929001343234	14T8/COR/48-840/IF21/G/DIM 10/1	240 degree(s)	4000 K	82	840	2,100 lumen
929001343334	14T8/COR/48-850/IF21/G/DIM 10/1	240 degree(s)	5000 K	82	850	2,100 lumen
929001991734	10T8/COR/48-840/IF16/G/DIM 10/1	240 degree(s)	4000 K	82	840	1,600 lumen
929001991834	10T8/COR/48-850/IF16/G/DIM 10/1	240 degree(s)	5000 K	82	850	1,600 lumen
929002252734	10T8/COR/48-830/IF15/G/DIM 10/1	240 degree(s)	3000 K	82	830	1,500 lumen
929002252834	10T8/COR/48-835/IF15/G/DIM 10/1	240 degree(s)	3500 K	82	835	1,500 lumen
929003556504	11.5T8/COR/48-835/IF20/G/DIM 25/1	240 degree(s)	3500 K	80	835	2,000 lumen
929003556604	11.5T8/COR/48-840/IF21/G/DIM 25/1	240 degree(s)	4000 K	80	840	2,100 lumen
929003556704	28T8/COR/96-835/IF40/G/FA8 10/1	240 degree(s)	3500 K	80	835	4,000 lumen
929003556804	28T8/COR/96-840/IF42/G/FA8 10/1	240 degree(s)	4000 K	80	840	4,200 lumen
929001933804	8.5T8/COR/24-830/MF11/G 10/1	180 degree(s)	3000 K	82	830	1,100 lumen
929001933904	8.5T8/COR/24-835/MF11/G 10/1	180 degree(s)	3500 K	82	835	1,100 lumen
929001934004	8.5T8/COR/24-840/MF11/G 10/1	180 degree(s)	4000 K	82	840	1,150 lumen
929001934104	8.5T8/COR/24-850/MF11/G 10/1	180 degree(s)	5000 K	82	850	1,150 lumen
929001934204	11.5T8/COR/36-830/MF13/G 10/1	180 degree(s)	3000 K	82	830	1,300 lumen
929001934304	11.5T8/COR/36-835/MF13/G 10/1	180 degree(s)	3500 K	82	835	1,300 lumen
929001934404	11.5T8/COR/36-840/MF14/G 10/1	180 degree(s)	4000 K	82	840	1,400 lumen
929001934504	11.5T8/COR/36-850/MF14/G 10/1	180 degree(s)	5000 K	82	850	1,400 lumen
929002497304	11T8/COR/48-835/MF16/G/BAA 25/1	240 degree(s)	3500 K	80	835	1,650 lumen
929002497404	11T8/COR/48-840/MF16/G/BAA 25/1	240 degree(s)	4000 K	80	840	1,700 lumen
929002497504	11T8/COR/48-850/MF16/G/BAA 25/1	240 degree(s)	5000 K	80	850	1,700 lumen
929002497604	15.5T8/COR/48-835/MF21/G/BAA 25/1	240 degree(s)	3500 K	80	835	2,100 lumen
929002497704	15.5T8/COR/48-840/MF21/G/BAA 25/1	240 degree(s)	4000 K	80	840	2,200 lumen
929002497804	15.5T8/COR/48-850/MF21/G/BAA 25/1	240 degree(s)	5000 K	80	850	2,200 lumen
929002497904	8.5T8/COR/24-835/MF11/G/BAA 25/1	240 degree(s)	3500 K	80	835	1,100 lumen
929002498004	8.5T8/COR/24-840/MF11/G/BAA 25/1	240 degree(s)	4000 K	80	840	1,150 lumen
929002498104	8.5T8/COR/24-850/MF11/G/BAA 25/1	240 degree(s)	5000 K	80	850	1,150 lumen
929003051303	14T8/LED/48-5CCT/MF18/G/DS 5/2 FB	240 degree(s)	3000 K	80	3000K/3500K/ 4000K/5000K/ 6500K	1,800 lumen
929003051333	14T8/LED/48-5CCT/MF18/G/DS 1/10	240 degree(s)	Selectable	80	3000K/3500K/ 4000K/5000K/ 6500K	1,800 lumen
929003540104	14.5T8/COR/48-5CCT/MF18/G/DIM 25/1	240 degree(s)	Selectable	80	3000K/3500K/ 4000K/5000K/ 6500K	1,800 lumen
929002325134	10.5T8/MAS/48-835/MF15/P 10/1	180 degree(s)	3500 K	80	835	1,600 lumen
929002325234	10.5T8/MAS/48-840/MF16/P 10/1	180 degree(s)	4000 K	80	840	1,650 lumen

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color rendering index		Luminous Flux
				(CRI)	Color Code	
929002325334	10.5T8/MAS/48-850/MF16/P 10/1	180 degree(s)	5000 K	80	850	1,650 lumen
929002325534	14.5T8/MAS/48-835/MF20/P 10/1	180 degree(s)	3500 K	80	835	2,000 lumen
929002325634	14.5T8/MAS/48-840/MF21/P 10/1	180 degree(s)	4000 K	80	840	2,100 lumen
929002325734	14.5T8/MAS/48-850/MF21/P 10/1	180 degree(s)	5000 K	80	850	2,100 lumen
929002442434	16.9T8/MAS/48-835/MF25/P 10/1	180 degree(s)	3500 K	80	835	2,400 lumen
929003525104	10.5T8/MAS/48-835/MF15/P/DIM 25/1	180 degree(s)	3500 K	80	835	1,550 lumen
929003525204	10.5T8/MAS/48-840/MF16/P/DIM 25/1	180 degree(s)	4000 K	80	840	1,600 lumen
929003525304	10.5T8/MAS/48-850/MF16/P/DIM 25/1	180 degree(s)	5000 K	80	850	1,600 lumen
929003525404	14.5T8/MAS/48-830/MF20/P/DIM 25/1	180 degree(s)	3000 K	80	830	2,000 lumen
929003525504	14.5T8/MAS/48-835/MF20/P/DIM 25/1	180 degree(s)	3500 K	80	835	2,000 lumen
929003525604	14.5T8/MAS/48-840/MF21/P/DIM 25/1	180 degree(s)	4000 K	80	840	2,100 lumen
929003525704	14.5T8/MAS/48-850/MF21/P/DIM 25/1	180 degree(s)	5000 K	80	850	2,100 lumen
929003525804	16.5T8/MAS/48-835/MF24/P/DIM 25/1	180 degree(s)	3500 K	80	835	2,450 lumen
929003525904	16.5T8/MAS/48-840/MF25/P/DIM 25/1	180 degree(s)	4000 K	80	840	2,500 lumen
929003526004	16.5T8/MAS/48-850/MF25/P/DIM 25/1	180 degree(s)	5000 K	80	850	2,500 lumen
929003523304	15T8/COR/48-835/MF20/G/120-347V 25/1	240 degree(s)	3500 K	80	835	2,000 lumen
929003523404	15T8/COR/48-840/MF21/G/120-347V 25/1	240 degree(s)	4000 K	80	840	2,100 lumen
929003523504	15T8/COR/48-850/MF21/G/120-347V 25/1	240 degree(s)	5000 K	80	850	2,100 lumen
929003144504	10.5T8/COR/48-835/IF15/G/DIM/BAA 25/1	240 degree(s)	3500 K	80	835	1,550 lumen
929003144604	10.5T8/COR/48-840/IF16/G/DIM/BAA 25/1	240 degree(s)	4000 K	80	840	1,650 lumen
929003144704	10.5T8/COR/48-850/IF16/G/DIM/BAA 25/1	240 degree(s)	5000 K	80	850	1,650 lumen
929003144804	14T8/COR/48-835/IF21/G/DIM/BAA 25/1	240 degree(s)	3500 K	80	835	2,100 lumen
929003144904	14T8/COR/48-840/IF22/G/DIM/BAA 25/1	240 degree(s)	4000 K	80	840	2,200 lumen
929003145004	14T8/COR/48-850/IF22/G/DIM/BAA 25/1	240 degree(s)	5000 K	80	850	2,200 lumen
929003474504	14.5T8/CNG/48-835/MF17/G 25/1	240 degree(s)	3500 K	80	835	1,750 lumen
929003474604	14.5T8/CNG/48-840/MF18/G 25/1	240 degree(s)	4000 K	80	840	1,800 lumen
929003474704	14.5T8/CNG/48-850/MF18/G 25/1	240 degree(s)	5000 K	80	850	1,800 lumen
929003474804	14.5T8/CNG/48-865/MF18/G 25/1	240 degree(s)	6500 K	80	865	1,800 lumen
929003510604	16.5T8/CNG/48-835/MF20/G 25/1	240 degree(s)	3500 K	80	835	2,000 lumen
929003510704	16.5T8/CNG/48-840/MF21/G 25/1	240 degree(s)	4000 K	80	840	2,100 lumen
929003510804	16.5T8/CNG/48-850/MF21/G 25/1	240 degree(s)	5000 K	80	850	2,100 lumen
929003099404	42T8HO/COR/96-840/MF54/G/FA8 10/1	240 degree(s)	4000 K	80	840	5,400 lumen
929003099504	42T8HO/COR/96-850/MF54/G/FA8 10/1	240 degree(s)	5000 K	80	850	5,400 lumen
929003112104	33T8/COR/96-840/MF44/G/FA8 10/1	240 degree(s)	4000 K	80	840	4,400 lumen
929003112204	33T8/COR/96-850/MF44/G/FA8 10/1	240 degree(s)	5000 K	80	850	4,400 lumen

Operating and Electrical

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Starting Time (Nom)	Wattage Equivalent
929002317304	12.5T8/COR/48-840/FF18/G/DIM 25/1	50 to 60 Hz	50 to 60 Hz	12.5 W	0.5 s	32 W
929002317404	12.5T8/COR/48-850/FF18/G/DIM 25/1	50 to 60 Hz	50 to 60 Hz	12.5 W	0.5 s	32 W
929002402204	12.5T8/COR/48-835/FF17/G/DIM 25/1	50 to 60 Hz	50 to 60 Hz	12.5 W	0.5 s	32 W
929001307804	35T8/96-3500 IF FA8 10/1	50000-64000 Hz	50000-64000 Hz	35 W	-	96 W

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Starting Time (Nom)	Wattage Equivalent
929001314604	35T8/96-4000 IF FA8 10/1	50000-64000 Hz	50000-64000 Hz	35 W	-	96 W
929001967504	8.5T8/MAS/36-830/IF13/P/DIM 10/1	20K to 120K Hz	20K to 120K Hz	8.5 W	0.5 s	25 W
929001967604	8.5T8/MAS/36-840/IF14/P/DIM 10/1	20K to 120K Hz	20K to 120K Hz	8.5 W	0.5 s	25 W
929001967704	8.5T8/MAS/36-850/IF14/P/DIM 10/1	20K to 120K Hz	20K to 120K Hz	8.5 W	0.5 s	25 W
929001967904	8.5T8/MAS/36-835/IF13/P/DIM 10/1	20K to 120K Hz	20K to 120K Hz	8.5 W	0.5 s	25 W
929001986904	7T8/MAS/24-830/IF10/P/DIM 10/1	20K to 120K Hz	20K to 120K Hz	7 W	0.5 s	17 W
929001987004	7T8/MAS/24-835/IF10/P/DIM 10/1	20K to 120K Hz	20K to 120K Hz	7 W	0.5 s	17 W
929001987104	7T8/MAS/24-840/IF11/P/DIM 10/1	20K to 120K Hz	20K to 120K Hz	7 W	0.5 s	17 W
929001987204	7T8/MAS/24-850/IF11/P/DIM 10/1	20K to 120K Hz	20K to 120K Hz	7 W	0.5 s	17 W
929001987404	13T8-6U/MAS/24-830/IF20/P/DIM 10/1	20K to 120K Hz	20K to 120K Hz	13 W	0.5 s	32 W
929001987504	13T8-6U/MAS/24-835/IF20/P/DIM 10/1	20K to 120K Hz	20K to 120K Hz	13 W	0.5 s	32 W
929001987604	13T8-6U/MAS/24-840/IF21/P/DIM 10/1	20K to 120K Hz	20K to 120K Hz	13 W	0.5 s	32 W
929001987704	13T8-6U/MAS/24-850/IF21/P/DIM 10/1	20K to 120K Hz	20K to 120K Hz	13 W	0.5 s	32 W
929001397634	13T8/MAS/48-830/IF20/P/DIM 10/1	20K to 120K Hz	20K to 120K Hz	13 W	0.5 s	-
929001397734	13T8/MAS/48-835/IF20/P/DIM 10/1	20K to 120K Hz	20K to 120K Hz	13 W	0.5 s	-
929001397834	13T8/MAS/48-840/IF21/P/DIM 10/1	20K to 120K Hz	20K to 120K Hz	13 W	0.5 s	-
929001397934	13T8/MAS/48-850/IF21/P/DIM 10/1	20K to 120K Hz	20K to 120K Hz	13 W	0.5 s	-
929002016204	15.5T8/MAS/48-830/IF23/P/DIM 25/1	20K to 120K Hz	20K to 120K Hz	15.5 W	0.5 s	32 W
929002016304	15.5T8/MAS/48-835/IF24/P/DIM 25/1	20K to 120K Hz	20K to 120K Hz	15.5 W	0.5 s	32 W
929002016404	15.5T8/MAS/48-840/IF25/P/DIM 25/1	20K to 120K Hz	20K to 120K Hz	15.5 W	0.5 s	32 W
929002016504	15.5T8/MAS/48-850/IF25/P/DIM 25/1	20K to 120K Hz	20K to 120K Hz	15.5 W	0.5 s	32 W
929003025304	8.9T8/MAS/48-830/IF15/P/DIM 10/1	20K to 120K Hz	20K to 120K Hz	8.9 W	0.5 s	32 W
929003025404	8.9T8/MAS/48-835/IF15/P/DIM 10/1	20K to 120K Hz	20K to 120K Hz	8.9 W	0.5 s	32 W
929003025504	8.9T8/MAS/48-840/IF16/P/DIM 10/1	20K to 120K Hz	20K to 120K Hz	8.9 W	0.5 s	32 W
929003025604	8.9T8/MAS/48-850/IF16/P/DIM 10/1	20K to 120K Hz	20K to 120K Hz	8.9 W	0.5 s	32 W
929001897204	30T8/COR/96-835/IF39/G/FA8 10/1	35000-150000 Hz	35000-150000 Hz	30 W	0.5 s	60 W
929001897304	30T8/COR/96-840/IF42/G/FA8 10/1	35000-150000 Hz	35000-150000 Hz	30 W	0.5 s	60 W
929001897404	30T8/COR/96-850/IF42/G/FA8 10/1	35000-150000 Hz	35000-150000 Hz	30 W	0.5 s	60 W
929002483704	9.9T8/COR/48-835/MF15/G 10/1	50 to 60 Hz	50 to 60 Hz	9.9 W	0.5 s	32 W
929002483804	9.9T8/COR/48-840/MF16/G 10/1	50 to 60 Hz	50 to 60 Hz	9.9 W	0.5 s	32 W
929002483904	9.9T8/COR/48-850/MF16/G 10/1	50 to 60 Hz	50 to 60 Hz	9.9 W	0.5 s	32 W
929002484004	12T8/COR/48-830/MF17/G 10/1	50 to 60 Hz	50 to 60 Hz	12 W	0.5 s	32 W
929002484104	12T8/COR/48-835/MF17/G 10/1	50 to 60 Hz	50 to 60 Hz	12 W	0.5 s	32 W
929002484204	12T8/COR/48-840/MF18/G 10/1	50 to 60 Hz	50 to 60 Hz	12 W	0.5 s	32 W
929002484304	12T8/COR/48-850/MF18/G 10/1	50 to 60 Hz	50 to 60 Hz	12 W	0.5 s	32 W
929002484404	14.5T8/COR/48-830/MF20/G 10/1	50 to 60 Hz	50 to 60 Hz	14.5 W	0.5 s	32 W
929002484504	14.5T8/COR/48-835/MF20/G 10/1	50 to 60 Hz	50 to 60 Hz	14.5 W	0.5 s	32 W
929002484604	14.5T8/COR/48-840/MF21/G 10/1	50 to 60 Hz	50 to 60 Hz	14.5 W	0.5 s	32 W
929002484704	14.5T8/COR/48-850/MF21/G 10/1	50 to 60 Hz	50 to 60 Hz	14.5 W	0.5 s	32 W
929003523704	9.9T8/COR/48-835/MF15/G/DIM 25/1	50 to 60 Hz	50 to 60 Hz	9.9 W	0.5 s	-
929003523804	9.9T8/COR/48-840/MF16/G/DIM 25/1	50 to 60 Hz	50 to 60 Hz	9.9 W	0.5 s	-
929003523904	9.9T8/COR/48-850/MF16/G/DIM 25/1	50 to 60 Hz	50 to 60 Hz	9.9 W	0.5 s	-
929003524104	12T8/COR/48-830/MF17/G/DIM 25/1	50 to 60 Hz	50 to 60 Hz	12 W	0.5 s	-
929003524204	12T8/COR/48-835/MF17/G/DIM 25/1	50 to 60 Hz	50 to 60 Hz	12 W	0.5 s	-
929003524304	12T8/COR/48-840/MF18/G/DIM 25/1	50 to 60 Hz	50 to 60 Hz	12 W	0.5 s	-
929003524404	12T8/COR/48-850/MF18/G/DIM 25/1	50 to 60 Hz	50 to 60 Hz	12 W	0.5 s	-
929003524604	14.5T8/COR/48-830/MF20/G/DIM 25/1	50 to 60 Hz	50 to 60 Hz	14.5 W	0.5 s	-
929003524704	14.5T8/COR/48-835/MF20/G/DIM 25/1	50 to 60 Hz	50 to 60 Hz	14.5 W	0.5 s	-
929003524804	14.5T8/COR/48-840/MF21/G/DIM 25/1	50 to 60 Hz	50 to 60 Hz	14.5 W	0.5 s	-
929003524904	14.5T8/COR/48-850/MF21/G/DIM 25/1	50 to 60 Hz	50 to 60 Hz	14.5 W	0.5 s	-
929001960604	16T8/LED/48-840/IF18/G 25/1	20K to 120K Hz	20K to 120K Hz	16 W	0.5 s	32 W
929001960704	16T8/LED/48-850/IF18/G 25/1	20K to 120K Hz	20K to 120K Hz	16 W	0.5 s	32 W

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Starting Time (Nom)	Wattage Equivalent
929003112304	42T8HO/COR/96-840/MF54/G/R17d 10/1	50 to 60 Hz	50 to 60 Hz	42 W	0.5 s	96 W
929003112404	42T8HO/COR/96-850/MF54/G/R17d 10/1	50 to 60 Hz	50 to 60 Hz	42 W	0.5 s	96 W
929001934604	15.5T8-6U/COR/24-830/MF20/G 10/1	50 to 60 Hz	50 to 60 Hz	15.5 W	0.9 s	32 W
929001934704	15.5T8-6U/COR/24-835/MF20/G 10/1	50 to 60 Hz	50 to 60 Hz	15.5 W	0.9 s	32 W
929001934804	15.5T8-6U/COR/24-840/MF21/G 10/1	50 to 60 Hz	50 to 60 Hz	15.5 W	0.9 s	32 W
929001934904	15.5T8-6U/COR/24-850/MF21/G 10/1	50 to 60 Hz	50 to 60 Hz	15.5 W	0.9 s	32 W
929001343034	14T8/COR/48-830/IF20/G/DIM 10/1	25000-105000 Hz	25000-105000 Hz	14 W	0.5 s	32 W
929001343134	14T8/COR/48-835/IF20/G/DIM 10/1	25000-105000 Hz	25000-105000 Hz	14 W	0.5 s	32 W
929001343234	14T8/COR/48-840/IF21/G/DIM 10/1	25000-105000 Hz	25000-105000 Hz	14 W	0.5 s	32 W
929001343334	14T8/COR/48-850/IF21/G/DIM 10/1	25000-105000 Hz	25000-105000 Hz	14 W	0.5 s	32 W
929001991734	10T8/COR/48-840/IF16/G/DIM 10/1	25000-105000 Hz	25000-105000 Hz	10 W	0.5 s	-
929001991834	10T8/COR/48-850/IF16/G/DIM 10/1	25000-105000 Hz	25000-105000 Hz	10 W	0.5 s	-
929002252734	10T8/COR/48-830/IF15/G/DIM 10/1	25000-105000 Hz	25000-105000 Hz	10 W	0.5 s	-
929002252834	10T8/COR/48-835/IF15/G/DIM 10/1	25000-105000 Hz	25000-105000 Hz	10 W	0.5 s	-
929003556504	11.5T8/COR/48-835/IF20/G/DIM 25/1	25K to 105K Hz	25K to 105K Hz	11.5 W	0.5 s	-
929003556604	11.5T8/COR/48-840/IF21/G/DIM 25/1	25K to 105K Hz	25K to 105K Hz	11.5 W	0.5 s	-
929003556704	28T8/COR/96-835/IF40/G/FA8 10/1	35K to 150K Hz	35K to 150K Hz	28 W	0.5 s	-
929003556804	28T8/COR/96-840/IF42/G/FA8 10/1	35K to 150K Hz	35K to 150K Hz	28 W	0.5 s	-
929001933804	8.5T8/COR/24-830/MF11/G 10/1	50 to 60 Hz	50 to 60 Hz	8.5 W	0.9 s	17 W
929001933904	8.5T8/COR/24-835/MF11/G 10/1	50 to 60 Hz	50 to 60 Hz	8.5 W	0.9 s	17 W
929001934004	8.5T8/COR/24-840/MF11/G 10/1	50 to 60 Hz	50 to 60 Hz	8.5 W	0.9 s	17 W
929001934104	8.5T8/COR/24-850/MF11/G 10/1	50 to 60 Hz	50 to 60 Hz	8.5 W	0.9 s	17 W
929001934204	11.5T8/COR/36-830/MF13/G 10/1	50 to 60 Hz	50 to 60 Hz	11.5 W	0.9 s	25 W
929001934304	11.5T8/COR/36-835/MF13/G 10/1	50 to 60 Hz	50 to 60 Hz	11.5 W	0.9 s	25 W
929001934404	11.5T8/COR/36-840/MF14/G 10/1	50 to 60 Hz	50 to 60 Hz	11.5 W	0.9 s	25 W
929001934504	11.5T8/COR/36-850/MF14/G 10/1	50 to 60 Hz	50 to 60 Hz	11.5 W	0.9 s	25 W
929002497304	11T8/COR/48-835/MF16/G/BAA 25/1	50 to 60 Hz	50 to 60 Hz	11 W	0.9 s	-
929002497404	11T8/COR/48-840/MF16/G/BAA 25/1	50 to 60 Hz	50 to 60 Hz	11 W	0.9 s	-
929002497504	11T8/COR/48-850/MF16/G/BAA 25/1	50 to 60 Hz	50 to 60 Hz	11 W	0.9 s	-
929002497604	15.5T8/COR/48-835/MF21/G/BAA 25/1	50 to 60 Hz	50 to 60 Hz	15.5 W	0.9 s	-
929002497704	15.5T8/COR/48-840/MF21/G/BAA 25/1	50 to 60 Hz	50 to 60 Hz	15.5 W	0.9 s	-
929002497804	15.5T8/COR/48-850/MF21/G/BAA 25/1	50 to 60 Hz	50 to 60 Hz	15.5 W	0.9 s	-
929002497904	8.5T8/COR/24-835/MF11/G/BAA 25/1	50 to 60 Hz	50 to 60 Hz	8.5 W	0.9 s	17 W
929002498004	8.5T8/COR/24-840/MF11/G/BAA 25/1	50 to 60 Hz	50 to 60 Hz	8.5 W	0.9 s	17 W
929002498104	8.5T8/COR/24-850/MF11/G/BAA 25/1	50 to 60 Hz	50 to 60 Hz	8.5 W	0.9 s	17 W
929003051303	14T8/LED/48-5CCT/MF18/G/DS 5/2 FB	50 to 60 Hz	50 to 60 Hz	14 W	0.5 s	-
929003051333	14T8/LED/48-5CCT/MF18/G/DS 1/10	50 to 60 Hz	50 to 60 Hz	14 W	0.5 s	32 W
929003540104	14.5T8/COR/48-5CCT/MF18/G/DIM 25/1	50 to 60 Hz	50 to 60 Hz	14.5 W	0.5 s	-
929002325134	10.5T8/MAS/48-835/MF15/P 10/1	50 to 60 Hz	50 to 60 Hz	10.5 W	0.5 s	32 W
929002325234	10.5T8/MAS/48-840/MF16/P 10/1	50 to 60 Hz	50 to 60 Hz	10.5 W	0.5 s	32 W
929002325334	10.5T8/MAS/48-850/MF16/P 10/1	50 to 60 Hz	50 to 60 Hz	10.5 W	0.5 s	32 W
929002325534	14.5T8/MAS/48-835/MF20/P 10/1	50 to 60 Hz	50 to 60 Hz	14.5 W	0.5 s	32 W
929002325634	14.5T8/MAS/48-840/MF21/P 10/1	50 to 60 Hz	50 to 60 Hz	14.5 W	0.5 s	32 W
929002325734	14.5T8/MAS/48-850/MF21/P 10/1	50 to 60 Hz	50 to 60 Hz	14.5 W	0.5 s	32 W
929002442434	16.9T8/MAS/48-835/MF25/P 10/1	50 to 60 Hz	50 to 60 Hz	16.9 W	0.5 s	32 W
929003525104	10.5T8/MAS/48-835/MF15/P/DIM 25/1	50 to 60 Hz	50 to 60 Hz	10.5 W	0.5 s	-
929003525204	10.5T8/MAS/48-840/MF16/P/DIM 25/1	50 to 60 Hz	50 to 60 Hz	10.5 W	0.5 s	-
929003525304	10.5T8/MAS/48-850/MF16/P/DIM 25/1	50 to 60 Hz	50 to 60 Hz	10.5 W	0.5 s	-
929003525404	14.5T8/MAS/48-830/MF20/P/DIM 25/1	50 to 60 Hz	50 to 60 Hz	14.5 W	0.5 s	-
929003525504	14.5T8/MAS/48-835/MF20/P/DIM 25/1	50 to 60 Hz	50 to 60 Hz	14.5 W	0.5 s	-
929003525604	14.5T8/MAS/48-840/MF21/P/DIM 25/1	50 to 60 Hz	50 to 60 Hz	14.5 W	0.5 s	-
929003525704	14.5T8/MAS/48-850/MF21/P/DIM 25/1	50 to 60 Hz	50 to 60 Hz	14.5 W	0.5 s	-

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Starting Time (Nom)	Wattage Equivalent
929003525804	16.5T8/MAS/48-835/MF24/P/DIM 25/1	50 to 60 Hz	50 to 60 Hz	16.5 W	0.5 s	-
929003525904	16.5T8/MAS/48-840/MF25/P/DIM 25/1	50 to 60 Hz	50 to 60 Hz	16.5 W	0.5 s	-
929003526004	16.5T8/MAS/48-850/MF25/P/DIM 25/1	50 to 60 Hz	50 to 60 Hz	16.5 W	0.5 s	-
929003523304	15T8/COR/48-835/MF20/G/120-347V 25/1	50 to 60 Hz	50 to 60 Hz	15 W	0.5 s	-
929003523404	15T8/COR/48-840/MF21/G/120-347V 25/1	50 to 60 Hz	50 to 60 Hz	15 W	0.5 s	-
929003523504	15T8/COR/48-850/MF21/G/120-347V 25/1	50 to 60 Hz	50 to 60 Hz	15 W	0.5 s	-
929003144504	10.5T8/COR/48-835/IF15/G/DIM/BAA 25/1	20K to 120K Hz	20K to 120K Hz	10.5 W	0.5 s	-
929003144604	10.5T8/COR/48-840/IF16/G/DIM/BAA 25/1	20K to 120K Hz	20K to 120K Hz	10.5 W	0.5 s	-
929003144704	10.5T8/COR/48-850/IF16/G/DIM/BAA 25/1	20K to 120K Hz	20K to 120K Hz	10.5 W	0.5 s	-
929003144804	14T8/COR/48-835/IF21/G/DIM/BAA 25/1	20K to 120K Hz	20K to 120K Hz	14 W	0.5 s	-
929003144904	14T8/COR/48-840/IF22/G/DIM/BAA 25/1	20K to 120K Hz	20K to 120K Hz	14 W	0.5 s	-
929003145004	14T8/COR/48-850/IF22/G/DIM/BAA 25/1	20K to 120K Hz	20K to 120K Hz	14 W	0.5 s	-
929003474504	14.5T8/CNG/48-835/MF17/G 25/1	50 to 60 Hz	50 to 60 Hz	14.5 W	0.5 s	-
929003474604	14.5T8/CNG/48-840/MF18/G 25/1	50 to 60 Hz	50 to 60 Hz	14.5 W	0.5 s	-
929003474704	14.5T8/CNG/48-850/MF18/G 25/1	50 to 60 Hz	50 to 60 Hz	14.5 W	0.5 s	32 W
929003474804	14.5T8/CNG/48-865/MF18/G 25/1	50 to 60 Hz	50 to 60 Hz	14.5 W	0.5 s	-
929003510604	16.5T8/CNG/48-835/MF20/G 25/1	50 to 60 Hz	50 to 60 Hz	16.5 W	0.5 s	-
929003510704	16.5T8/CNG/48-840/MF21/G 25/1	50 to 60 Hz	50 to 60 Hz	16.5 W	0.5 s	-
929003510804	16.5T8/CNG/48-850/MF21/G 25/1	50 to 60 Hz	50 to 60 Hz	16.5 W	0.5 s	-
929003099404	42T8HO/COR/96-840/MF54/G/FA8 10/1	50 to 60 Hz	50 to 60 Hz	42 W	0.5 s	96 W
929003099504	42T8HO/COR/96-850/MF54/G/FA8 10/1	50 to 60 Hz	50 to 60 Hz	42 W	0.5 s	96 W
929003112104	33T8/COR/96-840/MF44/G/FA8 10/1	50 to 60 Hz	50 to 60 Hz	33 W	0.5 s	96 W
929003112204	33T8/COR/96-850/MF44/G/FA8 10/1	50 to 60 Hz	50 to 60 Hz	33 W	0.5 s	96 W

Temperature

Order Code	Full Product Name	Ambient temperature range	T-Case Maximum (Nom)
929002317304	12.5T8/COR/48-840/FF18/G/DIM 25/1	-20 °C to 45 °C	60 °C
929002317404	12.5T8/COR/48-850/FF18/G/DIM 25/1	-20 °C to 45 °C	60 °C
929002402204	12.5T8/COR/48-835/FF17/G/DIM 25/1	-20 °C to 45 °C	60 °C
929001307804	35T8/96-3500 IF FA8 10/1	-20 °C to 45 °C	45 °C
929001314604	35T8/96-4000 IF FA8 10/1	-20 °C to 45 °C	45 °C
929001967504	8.5T8/MAS/36-830/IF13/P/DIM 10/1	-20 °C to 45 °C	40 °C
929001967604	8.5T8/MAS/36-840/IF14/P/DIM 10/1	-20 °C to 45 °C	40 °C
929001967704	8.5T8/MAS/36-850/IF14/P/DIM 10/1	-20 °C to 45 °C	40 °C
929001967904	8.5T8/MAS/36-835/IF13/P/DIM 10/1	-20 °C to 45 °C	40 °C
929001986904	7T8/MAS/24-830/IF10/P/DIM 10/1	-20 °C to 45 °C	40 °C
929001987004	7T8/MAS/24-835/IF10/P/DIM 10/1	-20 °C to 45 °C	40 °C
929001987104	7T8/MAS/24-840/IF11/P/DIM 10/1	-20 °C to 45 °C	40 °C
929001987204	7T8/MAS/24-850/IF11/P/DIM 10/1	-20 °C to 45 °C	40 °C
929001987404	13T8-6U/MAS/24-830/IF20/P/DIM 10/1	-20 °C to 45 °C	50 °C
929001987504	13T8-6U/MAS/24-835/IF20/P/DIM 10/1	-20 °C to 45 °C	50 °C
929001987604	13T8-6U/MAS/24-840/IF21/P/DIM 10/1	-20 °C to 45 °C	50 °C
929001987704	13T8-6U/MAS/24-850/IF21/P/DIM 10/1	-20 °C to 45 °C	50 °C
929001397634	13T8/MAS/48-830/IF20/P/DIM 10/1	-20 °C to 45 °C	40 °C
929001397734	13T8/MAS/48-835/IF20/P/DIM 10/1	-20 °C to 45 °C	40 °C
929001397834	13T8/MAS/48-840/IF21/P/DIM 10/1	-20 °C to 45 °C	40 °C
929001397934	13T8/MAS/48-850/IF21/P/DIM 10/1	-20 °C to 45 °C	40 °C
929002016204	15.5T8/MAS/48-830/IF23/P/DIM 25/1	-20 °C to 55 °C	40 °C
929002016304	15.5T8/MAS/48-835/IF24/P/DIM 25/1	-20 °C to 55 °C	40 °C

Order Code	Full Product Name	Ambient temperature range	T-Case Maximum (Nom)
929002016404	15.5T8/MAS/48-840/IF25/P/DIM 25/1	-20 °C to 55 °C	40 °C
929002016504	15.5T8/MAS/48-850/IF25/P/DIM 25/1	-20 °C to 55 °C	40 °C
929003025304	8.9T8/MAS/48-830/IF15/P/DIM 10/1	-20 °C to 45 °C	40 °C
929003025404	8.9T8/MAS/48-835/IF15/P/DIM 10/1	-20 °C to 45 °C	40 °C
929003025504	8.9T8/MAS/48-840/IF16/P/DIM 10/1	-20 °C to 45 °C	40 °C
929003025604	8.9T8/MAS/48-850/IF16/P/DIM 10/1	-20 °C to 45 °C	40 °C
929001897204	30T8/COR/96-835/IF39/G/FA8 10/1	-20 °C to 45 °C	45 °C
929001897304	30T8/COR/96-840/IF42/G/FA8 10/1	-20 °C to 45 °C	45 °C
929001897404	30T8/COR/96-850/IF42/G/FA8 10/1	-20 °C to 45 °C	45 °C
929002483704	9.9T8/COR/48-835/MF15/G 10/1	-20 °C to 45 °C	70 °C
929002483804	9.9T8/COR/48-840/MF16/G 10/1	-20 °C to 45 °C	70 °C
929002483904	9.9T8/COR/48-850/MF16/G 10/1	-20 °C to 45 °C	70 °C
929002484004	12T8/COR/48-830/MF17/G 10/1	-20 °C to 45 °C	70 °C
929002484104	12T8/COR/48-835/MF17/G 10/1	-20 °C to 45 °C	70 °C
929002484204	12T8/COR/48-840/MF18/G 10/1	-20 °C to 45 °C	70 °C
929002484304	12T8/COR/48-850/MF18/G 10/1	-20 °C to 45 °C	70 °C
929002484404	14.5T8/COR/48-830/MF20/G 10/1	-20 °C to 45 °C	70 °C
929002484504	14.5T8/COR/48-835/MF20/G 10/1	-20 °C to 45 °C	70 °C
929002484604	14.5T8/COR/48-840/MF21/G 10/1	-20 °C to 45 °C	70 °C
929002484704	14.5T8/COR/48-850/MF21/G 10/1	-20 °C to 45 °C	70 °C
929003523704	9.9T8/COR/48-835/MF15/G/DIM 25/1	-20 °C to 45 °C	70 °C
929003523804	9.9T8/COR/48-840/MF16/G/DIM 25/1	-20 °C to 45 °C	70 °C
929003523904	9.9T8/COR/48-850/MF16/G/DIM 25/1	-20 °C to 45 °C	70 °C
929003524104	12T8/COR/48-830/MF17/G/DIM 25/1	-20 °C to 45 °C	70 °C
929003524204	12T8/COR/48-835/MF17/G/DIM 25/1	-20 °C to 45 °C	70 °C

Order Code	Full Product Name	Ambient temperature range	T-Case Maximum (Nom)
929003524304	12T8/COR/48-840/MF18/G/DIM 25/1	-20 °C to 45 °C	70 °C
929003524404	12T8/COR/48-850/MF18/G/DIM 25/1	-20 °C to 45 °C	70 °C
929003524604	14.5T8/COR/48-830/MF20/G/DIM 25/1	-20 °C to 45 °C	70 °C
929003524704	14.5T8/COR/48-835/MF20/G/DIM 25/1	-20 °C to 45 °C	70 °C
929003524804	14.5T8/COR/48-840/MF21/G/DIM 25/1	-20 °C to 45 °C	70 °C
929003524904	14.5T8/COR/48-850/MF21/G/DIM 25/1	-20 °C to 45 °C	70 °C
929001960604	16T8/LED/48-840/IF18/G 25/1	-20 °C to 45 °C	35 °C
929001960704	16T8/LED/48-850/IF18/G 25/1	-20 °C to 45 °C	35 °C
929003112304	42T8HO/COR/96-840/MF54/G/R17d 10/1	-20 °C to 45 °C	55 °C
929003112404	42T8HO/COR/96-850/MF54/G/R17d 10/1	-20 °C to 45 °C	55 °C
929001934604	15.5T8-6U/COR/24-830/MF20/G 10/1	-20 °C to 45 °C	51 °C
929001934704	15.5T8-6U/COR/24-835/MF20/G 10/1	-20 °C to 45 °C	51 °C
929001934804	15.5T8-6U/COR/24-840/MF21/G 10/1	-20 °C to 45 °C	51 °C
929001934904	15.5T8-6U/COR/24-850/MF21/G 10/1	-20 °C to 45 °C	51 °C
929001343034	14T8/COR/48-830/IF20/G/DIM 10/1	-20 °C to 45 °C	50 °C
929001343134	14T8/COR/48-835/IF20/G/DIM 10/1	-20 °C to 45 °C	50 °C
929001343234	14T8/COR/48-840/IF21/G/DIM 10/1	-20 °C to 45 °C	50 °C
929001343334	14T8/COR/48-850/IF21/G/DIM 10/1	-20 °C to 45 °C	50 °C
929001991734	10T8/COR/48-840/IF16/G/DIM 10/1	-20 °C to 45 °C	50 °C
929001991834	10T8/COR/48-850/IF16/G/DIM 10/1	-20 °C to 45 °C	50 °C
929002252734	10T8/COR/48-830/IF15/G/DIM 10/1	-20 °C to 45 °C	50 °C
929002252834	10T8/COR/48-835/IF15/G/DIM 10/1	-20 °C to 45 °C	50 °C
929003556504	11.5T8/COR/48-835/IF20/G/DIM 25/1	-20 °C to 45 °C	40 °C
929003556604	11.5T8/COR/48-840/IF21/G/DIM 25/1	-20 °C to 45 °C	40 °C
929003556704	28T8/COR/96-835/IF40/G/FA8 10/1	-20 °C to 45 °C	45 °C

Order Code	Full Product Name	Ambient temperature range	T-Case Maximum (Nom)
929003556804	28T8/COR/96-840/IF42/G/FA8 10/1	-20 °C to 45 °C	45 °C
929001933804	8.5T8/COR/24-830/MF11/G 10/1	-20 °C to 45 °C	50 °C
929001933904	8.5T8/COR/24-835/MF11/G 10/1	-20 °C to 45 °C	50 °C
929001934004	8.5T8/COR/24-840/MF11/G 10/1	-20 °C to 45 °C	50 °C
929001934104	8.5T8/COR/24-850/MF11/G 10/1	-20 °C to 45 °C	50 °C
929001934204	11.5T8/COR/36-830/MF13/G 10/1	-20 °C to 45 °C	50 °C
929001934304	11.5T8/COR/36-835/MF13/G 10/1	-20 °C to 45 °C	50 °C
929001934404	11.5T8/COR/36-840/MF14/G 10/1	-20 °C to 45 °C	50 °C
929001934504	11.5T8/COR/36-850/MF14/G 10/1	-20 °C to 45 °C	50 °C
929002497304	11T8/COR/48-835/MF16/G/BAA 25/1	-20 °C to 45 °C	70 °C
929002497404	11T8/COR/48-840/MF16/G/BAA 25/1	-20 °C to 45 °C	70 °C
929002497504	11T8/COR/48-850/MF16/G/BAA 25/1	-20 °C to 45 °C	70 °C
929002497604	15.5T8/COR/48-835/MF21/G/BAA 25/1	-20 °C to 45 °C	70 °C
929002497704	15.5T8/COR/48-840/MF21/G/BAA 25/1	-20 °C to 45 °C	70 °C
929002497804	15.5T8/COR/48-850/MF21/G/BAA 25/1	-20 °C to 45 °C	70 °C
929002497904	8.5T8/COR/24-835/MF11/G/BAA 25/1	-20 °C to 45 °C	50 °C
929002498004	8.5T8/COR/24-840/MF11/G/BAA 25/1	-20 °C to 45 °C	50 °C
929002498104	8.5T8/COR/24-850/MF11/G/BAA 25/1	-20 °C to 45 °C	50 °C
929003051303	14T8/LED/48-5CCT/MF18/G/DS 5/2 FB	-20 °C to 45 °C	70 °C
929003051333	14T8/LED/48-5CCT/MF18/G/DS 1/10	-	70 °C
929003540104	14.5T8/COR/48-5CCT/MF18/G/DIM 25/1	-	70 °C
929002325134	10.5T8/MAS/48-835/MF15/P 10/1	-20 °C to 45 °C	70 °C
929002325234	10.5T8/MAS/48-840/MF16/P 10/1	-20 °C to 45 °C	70 °C
929002325334	10.5T8/MAS/48-850/MF16/P 10/1	-20 °C to 45 °C	70 °C
929002325534	14.5T8/MAS/48-835/MF20/P 10/1	-20 °C to 45 °C	70 °C

Order Code	Full Product Name	Ambient temperature range	T-Case Maximum (Nom)
929002325634	14.5T8/MAS/48-840/MF21/P 10/1	-20 °C to 45 °C	70 °C
929002325734	14.5T8/MAS/48-850/MF21/P 10/1	-20 °C to 45 °C	70 °C
929002442434	16.9T8/MAS/48-835/MF25/P 10/1	-20 °C to 45 °C	70 °C
929003525104	10.5T8/MAS/48-835/MF15/P/DIM 25/1	-20 °C to 45 °C	70 °C
929003525204	10.5T8/MAS/48-840/MF16/P/DIM 25/1	-20 °C to 45 °C	70 °C
929003525304	10.5T8/MAS/48-850/MF16/P/DIM 25/1	-20 °C to 45 °C	70 °C
929003525404	14.5T8/MAS/48-830/MF20/P/DIM 25/1	-20 °C to 45 °C	70 °C
929003525504	14.5T8/MAS/48-835/MF20/P/DIM 25/1	-20 °C to 45 °C	70 °C
929003525604	14.5T8/MAS/48-840/MF21/P/DIM 25/1	-20 °C to 45 °C	70 °C
929003525704	14.5T8/MAS/48-850/MF21/P/DIM 25/1	-20 °C to 45 °C	70 °C
929003525804	16.5T8/MAS/48-835/MF24/P/DIM 25/1	-20 °C to 45 °C	70 °C
929003525904	16.5T8/MAS/48-840/MF25/P/DIM 25/1	-20 °C to 45 °C	70 °C
929003526004	16.5T8/MAS/48-850/MF25/P/DIM 25/1	-20 °C to 45 °C	70 °C
929003523304	15T8/COR/48-835/MF20/G/120-347V 25/1	-20 °C to 45 °C	70 °C
929003523404	15T8/COR/48-840/MF21/G/120-347V 25/1	-20 °C to 45 °C	70 °C
929003523504	15T8/COR/48-850/MF21/G/120-347V 25/1	-20 °C to 45 °C	70 °C
929003144504	10.5T8/COR/48-835/IF15/G/DIM/BAA 25/1	-20 °C to 45 °C	50 °C
929003144604	10.5T8/COR/48-840/IF16/G/DIM/BAA 25/1	-20 °C to 45 °C	50 °C
929003144704	10.5T8/COR/48-850/IF16/G/DIM/BAA 25/1	-20 °C to 45 °C	50 °C
929003144804	14T8/COR/48-835/IF21/G/DIM/BAA 25/1	-20 °C to 45 °C	50 °C
929003144904	14T8/COR/48-840/IF22/G/DIM/BAA 25/1	-20 °C to 45 °C	50 °C
929003145004	14T8/COR/48-850/IF22/G/DIM/BAA 25/1	-20 °C to 45 °C	50 °C
929003474504	14.5T8/CNG/48-835/MF17/G 25/1	-20 °C to 45 °C	70 °C
929003474604	14.5T8/CNG/48-840/MF18/G 25/1	-20 °C to 45 °C	70 °C
929003474704	14.5T8/CNG/48-850/MF18/G 25/1	-20 °C to 45 °C	70 °C

Order Code	Full Product Name	Ambient temperature range	T-Case Maximum (Nom)
929003474804	14.5T8/CNG/48-865/MF18/G 25/1	-20 °C to 45 °C	70 °C
929003510604	16.5T8/CNG/48-835/MF20/G 25/1	-20 °C to 45 °C	70 °C
929003510704	16.5T8/CNG/48-840/MF21/G 25/1	-20 °C to 45 °C	70 °C
929003510804	16.5T8/CNG/48-850/MF21/G 25/1	-20 °C to 45 °C	70 °C

Order Code	Full Product Name	Ambient temperature range	T-Case Maximum (Nom)
92900309940	42T8HO/COR/96-840/MF54/G/FA8 10/1	-20 °C to 45 °C	55 °C
92900309950	42T8HO/COR/96-850/MF54/G/FA8 10/1	-20 °C to 45 °C	55 °C
929003112104	33T8/COR/96-840/MF44/G/FA8 10/1	-20 °C to 45 °C	50 °C
929003112204	33T8/COR/96-850/MF44/G/FA8 10/1	-20 °C to 45 °C	50 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
929002317304	12.5T8/COR/48-840/FF18/G/DIM 25/1	Only with specific dimmers
929002317404	12.5T8/COR/48-850/FF18/G/DIM 25/1	Only with specific dimmers
929002402204	12.5T8/COR/48-835/FF17/G/DIM 25/1	Only with specific dimmers
929001307804	35T8/96-3500 IF FA8 10/1	No
929001314604	35T8/96-4000 IF FA8 10/1	No
929001967504	8.5T8/MAS/36-830/IF13/P/DIM 10/1	Only with specific dimmers
929001967604	8.5T8/MAS/36-840/IF14/P/DIM 10/1	Only with specific dimmers
929001967704	8.5T8/MAS/36-850/IF14/P/DIM 10/1	Only with specific dimmers
929001967904	8.5T8/MAS/36-835/IF13/P/DIM 10/1	Only with specific dimmers
929001986904	7T8/MAS/24-830/IF10/P/DIM 10/1	Only with specific dimmers
929001987004	7T8/MAS/24-835/IF10/P/DIM 10/1	Only with specific dimmers
929001987104	7T8/MAS/24-840/IF11/P/DIM 10/1	Only with specific dimmers
929001987204	7T8/MAS/24-850/IF11/P/DIM 10/1	Only with specific dimmers
929001987404	13T8-6U/MAS/24-830/IF20/P/DIM 10/1	Yes
929001987504	13T8-6U/MAS/24-835/IF20/P/DIM 10/1	Yes
929001987604	13T8-6U/MAS/24-840/IF21/P/DIM 10/1	Yes
929001987704	13T8-6U/MAS/24-850/IF21/P/DIM 10/1	Yes
929001397634	13T8/MAS/48-830/IF20/P/DIM 10/1	Only with specific dimmers
929001397734	13T8/MAS/48-835/IF20/P/DIM 10/1	Only with specific dimmers
929001397834	13T8/MAS/48-840/IF21/P/DIM 10/1	Only with specific dimmers
929001397934	13T8/MAS/48-850/IF21/P/DIM 10/1	Only with specific dimmers
929002016204	15.5T8/MAS/48-830/IF23/P/DIM 25/1	Only with specific dimmers
929002016304	15.5T8/MAS/48-835/IF24/P/DIM 25/1	Only with specific dimmers
929002016404	15.5T8/MAS/48-840/IF25/P/DIM 25/1	Only with specific dimmers
929002016504	15.5T8/MAS/48-850/IF25/P/DIM 25/1	Only with specific dimmers
929003025304	8.9T8/MAS/48-830/IF15/P/DIM 10/1	Only with specific dimmers
929003025404	8.9T8/MAS/48-835/IF15/P/DIM 10/1	Only with specific dimmers
929003025504	8.9T8/MAS/48-840/IF16/P/DIM 10/1	Only with specific dimmers
929003025604	8.9T8/MAS/48-850/IF16/P/DIM 10/1	Only with specific dimmers
929001897204	30T8/COR/96-835/IF39/G/FA8 10/1	No
929001897304	30T8/COR/96-840/IF42/G/FA8 10/1	No
929001897404	30T8/COR/96-850/IF42/G/FA8 10/1	No
929002483704	9.9T8/COR/48-835/MF15/G 10/1	Limited
929002483804	9.9T8/COR/48-840/MF16/G 10/1	Limited
929002483904	9.9T8/COR/48-850/MF16/G 10/1	Limited
929002484004	12T8/COR/48-830/MF17/G 10/1	Limited
929002484104	12T8/COR/48-835/MF17/G 10/1	Limited
929002484204	12T8/COR/48-840/MF18/G 10/1	Limited

Order Code	Full Product Name	Dimmable
929002484304	12T8/COR/48-850/MF18/G 10/1	Limited
929002484404	14.5T8/COR/48-830/MF20/G 10/1	Limited
929002484504	14.5T8/COR/48-835/MF20/G 10/1	Limited
929002484604	14.5T8/COR/48-840/MF21/G 10/1	Limited
929002484704	14.5T8/COR/48-850/MF21/G 10/1	Limited
929003523704	9.9T8/COR/48-835/MF15/G/DIM 25/1	Only with specific dimmers
929003523804	9.9T8/COR/48-840/MF16/G/DIM 25/1	Only with specific dimmers
929003523904	9.9T8/COR/48-850/MF16/G/DIM 25/1	Only with specific dimmers
929003524104	12T8/COR/48-830/MF17/G/DIM 25/1	Only with specific dimmers
929003524204	12T8/COR/48-835/MF17/G/DIM 25/1	Only with specific dimmers
929003524304	12T8/COR/48-840/MF18/G/DIM 25/1	Only with specific dimmers
929003524404	12T8/COR/48-850/MF18/G/DIM 25/1	Only with specific dimmers
929003524604	14.5T8/COR/48-830/MF20/G/DIM 25/1	Only with specific dimmers
929003524704	14.5T8/COR/48-835/MF20/G/DIM 25/1	Only with specific dimmers
929003524804	14.5T8/COR/48-840/MF21/G/DIM 25/1	Only with specific dimmers
929003524904	14.5T8/COR/48-850/MF21/G/DIM 25/1	Only with specific dimmers
929001960604	16T8/LED/48-840/IF18/G 25/1	No
929001960704	16T8/LED/48-850/IF18/G 25/1	No
929003112304	42T8HO/COR/96-840/MF54/G/R17d 10/1	Limited
929003112404	42T8HO/COR/96-850/MF54/G/R17d 10/1	Limited
929001934604	15.5T8-6U/COR/24-830/MF20/G 10/1	No
929001934704	15.5T8-6U/COR/24-835/MF20/G 10/1	No
929001934804	15.5T8-6U/COR/24-840/MF21/G 10/1	No
929001934904	15.5T8-6U/COR/24-850/MF21/G 10/1	No
929001343034	14T8/COR/48-830/IF20/G/DIM 10/1	Yes
929001343134	14T8/COR/48-835/IF20/G/DIM 10/1	Yes
929001343234	14T8/COR/48-840/IF21/G/DIM 10/1	Yes
929001343334	14T8/COR/48-850/IF21/G/DIM 10/1	Yes
929001991734	10T8/COR/48-840/IF16/G/DIM 10/1	Yes
929001991834	10T8/COR/48-850/IF16/G/DIM 10/1	Yes
929002252734	10T8/COR/48-830/IF15/G/DIM 10/1	Yes
929002252834	10T8/COR/48-835/IF15/G/DIM 10/1	Yes
929003556504	11.5T8/COR/48-835/IF20/G/DIM 25/1	No
929003556604	11.5T8/COR/48-840/IF21/G/DIM 25/1	No
929003556704	28T8/COR/96-835/IF40/G/FA8 10/1	No
929003556804	28T8/COR/96-840/IF42/G/FA8 10/1	No
929001933804	8.5T8/COR/24-830/MF11/G 10/1	No
929001933904	8.5T8/COR/24-835/MF11/G 10/1	No

Order Code	Full Product Name	Dimmable
929001934004	8.5T8/COR/24-840/MF11/G 10/1	No
929001934104	8.5T8/COR/24-850/MF11/G 10/1	No
929001934204	11.5T8/COR/36-830/MF13/G 10/1	No
929001934304	11.5T8/COR/36-835/MF13/G 10/1	No
929001934404	11.5T8/COR/36-840/MF14/G 10/1	No
929001934504	11.5T8/COR/36-850/MF14/G 10/1	No
929002497304	11T8/COR/48-835/MF16/G/BAA 25/1	No
929002497404	11T8/COR/48-840/MF16/G/BAA 25/1	No
929002497504	11T8/COR/48-850/MF16/G/BAA 25/1	No
929002497604	15.5T8/COR/48-835/MF21/G/BAA 25/1	No
929002497704	15.5T8/COR/48-840/MF21/G/BAA 25/1	No
929002497804	15.5T8/COR/48-850/MF21/G/BAA 25/1	No
929002497904	8.5T8/COR/24-835/MF11/G/BAA 25/1	No
929002498004	8.5T8/COR/24-840/MF11/G/BAA 25/1	No
929002498104	8.5T8/COR/24-850/MF11/G/BAA 25/1	No
929003051303	14T8/LED/48-5CCT/MF18/G/DS 5/2 FB	No
929003051333	14T8/LED/48-5CCT/MF18/G/DS 1/10	No
929003540104	14.5T8/COR/48-5CCT/MF18/G/DIM 25/1	Only with specific dimmers
929002325134	10.5T8/MAS/48-835/MF15/P 10/1	Limited
929002325234	10.5T8/MAS/48-840/MF16/P 10/1	Limited
929002325334	10.5T8/MAS/48-850/MF16/P 10/1	Limited
929002325534	14.5T8/MAS/48-835/MF20/P 10/1	Limited
929002325634	14.5T8/MAS/48-840/MF21/P 10/1	Limited
929002325734	14.5T8/MAS/48-850/MF21/P 10/1	Limited
929002442434	16.9T8/MAS/48-835/MF25/P 10/1	Limited
929003525104	10.5T8/MAS/48-835/MF15/P/DIM 25/1	Only with specific dimmers
929003525204	10.5T8/MAS/48-840/MF16/P/DIM 25/1	Only with specific dimmers
929003525304	10.5T8/MAS/48-850/MF16/P/DIM 25/1	Only with specific dimmers
929003525404	14.5T8/MAS/48-830/MF20/P/DIM 25/1	Only with specific dimmers
929003525504	14.5T8/MAS/48-835/MF20/P/DIM 25/1	Only with specific dimmers
929003525604	14.5T8/MAS/48-840/MF21/P/DIM 25/1	Only with specific dimmers

Order Code	Full Product Name	Dimmable
929003525704	14.5T8/MAS/48-850/MF21/P/DIM 25/1	Only with specific dimmers
929003525804	16.5T8/MAS/48-835/MF24/P/DIM 25/1	Only with specific dimmers
929003525904	16.5T8/MAS/48-840/MF25/P/DIM 25/1	Only with specific dimmers
929003526004	16.5T8/MAS/48-850/MF25/P/DIM 25/1	Only with specific dimmers
929003523304	15T8/COR/48-835/MF20/G/120-347V 25/1	Limited
929003523404	15T8/COR/48-840/MF21/G/120-347V 25/1	Limited
929003523504	15T8/COR/48-850/MF21/G/120-347V 25/1	Limited
929003144504	10.5T8/COR/48-835/IF15/G/DIM/BAA 25/1	Only with specific dimmers
929003144604	10.5T8/COR/48-840/IF16/G/DIM/BAA 25/1	Only with specific dimmers
929003144704	10.5T8/COR/48-850/IF16/G/DIM/BAA 25/1	Only with specific dimmers
929003144804	14T8/COR/48-835/IF21/G/DIM/BAA 25/1	Only with specific dimmers
929003144904	14T8/COR/48-840/IF22/G/DIM/BAA 25/1	Only with specific dimmers
929003145004	14T8/COR/48-850/IF22/G/DIM/BAA 25/1	Only with specific dimmers
929003474504	14.5T8/CNG/48-835/MF17/G 25/1	Limited
929003474604	14.5T8/CNG/48-840/MF18/G 25/1	Limited
929003474704	14.5T8/CNG/48-850/MF18/G 25/1	Limited
929003474804	14.5T8/CNG/48-865/MF18/G 25/1	Limited
929003510604	16.5T8/CNG/48-835/MF20/G 25/1	Limited
929003510704	16.5T8/CNG/48-840/MF21/G 25/1	Limited
929003510804	16.5T8/CNG/48-850/MF21/G 25/1	Limited
929003099404	42T8HO/COR/96-840/MF54/G/FA8 10/1	Limited
929003099504	42T8HO/COR/96-850/MF54/G/FA8 10/1	Limited
929003112104	33T8/COR/96-840/MF44/G/FA8 10/1	Limited
929003112204	33T8/COR/96-850/MF44/G/FA8 10/1	Limited

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/ 1000 h
929002317304	12.5T8/COR/48-840/FF18/G/DIM 25/1	-
929002317404	12.5T8/COR/48-850/FF18/G/DIM 25/1	-
929002402204	12.5T8/COR/48-835/FF17/G/DIM 25/1	-
929001307804	35T8/96-3500 IF FA8 10/1	- kWh
929001314604	35T8/96-4000 IF FA8 10/1	- kWh
929001967504	8.5T8/MAS/36-830/IF13/P/DIM 10/1	- kWh
929001967604	8.5T8/MAS/36-840/IF14/P/DIM 10/1	- kWh
929001967704	8.5T8/MAS/36-850/IF14/P/DIM 10/1	- kWh
929001967904	8.5T8/MAS/36-835/IF13/P/DIM 10/1	- kWh
929001986904	7T8/MAS/24-830/IF10/P/DIM 10/1	- kWh
929001987004	7T8/MAS/24-835/IF10/P/DIM 10/1	- kWh
929001987104	7T8/MAS/24-840/IF11/P/DIM 10/1	- kWh
929001987204	7T8/MAS/24-850/IF11/P/DIM 10/1	- kWh
929001987404	13T8-6U/MAS/24-830/IF20/P/DIM 10/1	- kWh
929001987504	13T8-6U/MAS/24-835/IF20/P/DIM 10/1	- kWh
929001987604	13T8-6U/MAS/24-840/IF21/P/DIM 10/1	- kWh

Order Code	Full Product Name	Energy Consumption kWh/ 1000 h
929001987704	13T8-6U/MAS/24-850/IF21/P/DIM 10/1	- kWh
929001397634	13T8/MAS/48-830/IF20/P/DIM 10/1	- kWh
929001397734	13T8/MAS/48-835/IF20/P/DIM 10/1	- kWh
929001397834	13T8/MAS/48-840/IF21/P/DIM 10/1	- kWh
929001397934	13T8/MAS/48-850/IF21/P/DIM 10/1	- kWh
929002016204	15.5T8/MAS/48-830/IF23/P/DIM 25/1	- kWh
929002016304	15.5T8/MAS/48-835/IF24/P/DIM 25/1	- kWh
929002016404	15.5T8/MAS/48-840/IF25/P/DIM 25/1	- kWh
929002016504	15.5T8/MAS/48-850/IF25/P/DIM 25/1	- kWh
929003025304	8.9T8/MAS/48-830/IF15/P/DIM 10/1	- kWh
929003025404	8.9T8/MAS/48-835/IF15/P/DIM 10/1	- kWh
929003025504	8.9T8/MAS/48-840/IF16/P/DIM 10/1	- kWh
929003025604	8.9T8/MAS/48-850/IF16/P/DIM 10/1	- kWh
929001897204	30T8/COR/96-835/IF39/G/FA8 10/1	- kWh
929001897304	30T8/COR/96-840/IF42/G/FA8 10/1	- kWh
929001897404	30T8/COR/96-850/IF42/G/FA8 10/1	- kWh

Order Code	Full Product Name	Energy Consumption kWh/ 1000 h
929002483704	9.9T8/COR/48-835/MF15/G 10/1	- kWh
929002483804	9.9T8/COR/48-840/MF16/G 10/1	- kWh
929002483904	9.9T8/COR/48-850/MF16/G 10/1	- kWh
929002484004	12T8/COR/48-830/MF17/G 10/1	- kWh
929002484104	12T8/COR/48-835/MF17/G 10/1	- kWh
929002484204	12T8/COR/48-840/MF18/G 10/1	- kWh
929002484304	12T8/COR/48-850/MF18/G 10/1	- kWh
929002484404	14.5T8/COR/48-830/MF20/G 10/1	- kWh
929002484504	14.5T8/COR/48-835/MF20/G 10/1	- kWh
929002484604	14.5T8/COR/48-840/MF21/G 10/1	- kWh
929002484704	14.5T8/COR/48-850/MF21/G 10/1	- kWh
929003523704	9.9T8/COR/48-835/MF15/G/DIM 25/1	-
929003523804	9.9T8/COR/48-840/MF16/G/DIM 25/1	-
929003523904	9.9T8/COR/48-850/MF16/G/DIM 25/1	-
929003524104	12T8/COR/48-830/MF17/G/DIM 25/1	-
929003524204	12T8/COR/48-835/MF17/G/DIM 25/1	-
929003524304	12T8/COR/48-840/MF18/G/DIM 25/1	-
929003524404	12T8/COR/48-850/MF18/G/DIM 25/1	-
929003524604	14.5T8/COR/48-830/MF20/G/DIM 25/1	-
929003524704	14.5T8/COR/48-835/MF20/G/DIM 25/1	-
929003524804	14.5T8/COR/48-840/MF21/G/DIM 25/1	-
929003524904	14.5T8/COR/48-850/MF21/G/DIM 25/1	-
929001960604	16T8/LED/48-840/IF18/G 25/1	- kWh
929001960704	16T8/LED/48-850/IF18/G 25/1	- kWh
929003112304	42T8HO/COR/96-840/MF54/G/R17d 10/1	-
929003112404	42T8HO/COR/96-850/MF54/G/R17d 10/1	-
929001934604	15.5T8-6U/COR/24-830/MF20/G 10/1	- kWh
929001934704	15.5T8-6U/COR/24-835/MF20/G 10/1	- kWh
929001934804	15.5T8-6U/COR/24-840/MF21/G 10/1	- kWh
929001934904	15.5T8-6U/COR/24-850/MF21/G 10/1	- kWh
929001343034	14T8/COR/48-830/IF20/G/DIM 10/1	- kWh
929001343134	14T8/COR/48-835/IF20/G/DIM 10/1	- kWh
929001343234	14T8/COR/48-840/IF21/G/DIM 10/1	- kWh
929001343334	14T8/COR/48-850/IF21/G/DIM 10/1	- kWh
929001991734	10T8/COR/48-840/IF16/G/DIM 10/1	- kWh
929001991834	10T8/COR/48-850/IF16/G/DIM 10/1	- kWh
929002252734	10T8/COR/48-830/IF15/G/DIM 10/1	- kWh
929002252834	10T8/COR/48-835/IF15/G/DIM 10/1	- kWh
929003556504	11.5T8/COR/48-835/IF20/G/DIM 25/1	-
929003556604	11.5T8/COR/48-840/IF21/G/DIM 25/1	-
929003556704	28T8/COR/96-835/IF40/G/FA8 10/1	-
929003556804	28T8/COR/96-840/IF42/G/FA8 10/1	-
929001933804	8.5T8/COR/24-830/MF11/G 10/1	- kWh
929001933904	8.5T8/COR/24-835/MF11/G 10/1	- kWh
929001934004	8.5T8/COR/24-840/MF11/G 10/1	- kWh
929001934104	8.5T8/COR/24-850/MF11/G 10/1	- kWh
929001934204	11.5T8/COR/36-830/MF13/G 10/1	- kWh
929001934304	11.5T8/COR/36-835/MF13/G 10/1	- kWh
929001934404	11.5T8/COR/36-840/MF14/G 10/1	- kWh
929001934504	11.5T8/COR/36-850/MF14/G 10/1	- kWh
929002497304	11T8/COR/48-835/MF16/G/BAA 25/1	- kWh

Order Code	Full Product Name	Energy Consumption kWh/ 1000 h
929002497404	11T8/COR/48-840/MF16/G/BAA 25/1	- kWh
929002497504	11T8/COR/48-850/MF16/G/BAA 25/1	- kWh
929002497604	15.5T8/COR/48-835/MF21/G/BAA 25/1	- kWh
929002497704	15.5T8/COR/48-840/MF21/G/BAA 25/1	- kWh
929002497804	15.5T8/COR/48-850/MF21/G/BAA 25/1	- kWh
929002497904	8.5T8/COR/24-835/MF11/G/BAA 25/1	- kWh
929002498004	8.5T8/COR/24-840/MF11/G/BAA 25/1	- kWh
929002498104	8.5T8/COR/24-850/MF11/G/BAA 25/1	- kWh
929003051303	14T8/LED/48-5CCT/MF18/G/DS 5/2 FB	- kWh
929003051333	14T8/LED/48-5CCT/MF18/G/DS 1/10	- kWh
929003540104	14.5T8/COR/48-5CCT/MF18/G/DIM 25/1	-
929002325134	10.5T8/MAS/48-835/MF15/P 10/1	-
929002325234	10.5T8/MAS/48-840/MF16/P 10/1	-
929002325334	10.5T8/MAS/48-850/MF16/P 10/1	-
929002325534	14.5T8/MAS/48-835/MF20/P 10/1	-
929002325634	14.5T8/MAS/48-840/MF21/P 10/1	-
929002325734	14.5T8/MAS/48-850/MF21/P 10/1	-
929002442434	16.9T8/MAS/48-835/MF25/P 10/1	-
929003525104	10.5T8/MAS/48-835/MF15/P/DIM 25/1	-
929003525204	10.5T8/MAS/48-840/MF16/P/DIM 25/1	-
929003525304	10.5T8/MAS/48-850/MF16/P/DIM 25/1	-
929003525404	14.5T8/MAS/48-830/MF20/P/DIM 25/1	-
929003525504	14.5T8/MAS/48-835/MF20/P/DIM 25/1	-
929003525604	14.5T8/MAS/48-840/MF21/P/DIM 25/1	-
929003525704	14.5T8/MAS/48-850/MF21/P/DIM 25/1	-
929003525804	16.5T8/MAS/48-835/MF24/P/DIM 25/1	-
929003525904	16.5T8/MAS/48-840/MF25/P/DIM 25/1	-
929003526004	16.5T8/MAS/48-850/MF25/P/DIM 25/1	-
929003523304	15T8/COR/48-835/MF20/G/120-347V 25/1	-
929003523404	15T8/COR/48-840/MF21/G/120-347V 25/1	-
929003523504	15T8/COR/48-850/MF21/G/120-347V 25/1	-
929003144504	10.5T8/COR/48-835/IF15/G/DIM/BAA 25/1	-
929003144604	10.5T8/COR/48-840/IF16/G/DIM/BAA 25/1	-
929003144704	10.5T8/COR/48-850/IF16/G/DIM/BAA 25/1	-
929003144804	14T8/COR/48-835/IF21/G/DIM/BAA 25/1	-
929003144904	14T8/COR/48-840/IF22/G/DIM/BAA 25/1	-
929003145004	14T8/COR/48-850/IF22/G/DIM/BAA 25/1	-
929003474504	14.5T8/CNG/48-835/MF17/G 25/1	-
929003474604	14.5T8/CNG/48-840/MF18/G 25/1	-
929003474704	14.5T8/CNG/48-850/MF18/G 25/1	-
929003474804	14.5T8/CNG/48-865/MF18/G 25/1	-
929003510604	16.5T8/CNG/48-835/MF20/G 25/1	-
929003510704	16.5T8/CNG/48-840/MF21/G 25/1	-
929003510804	16.5T8/CNG/48-850/MF21/G 25/1	-

Order Code	Full Product Name	Energy Consumption kWh/
		1000 h
92900309940	42T8HO/COR/96-840/MF54/G/FA8 10/1	-
4		
92900309950	42T8HO/COR/96-850/MF54/G/FA8 10/1	-
4		
929003112104	33T8/COR/96-840/MF44/G/FA8 10/1	-
929003112204	33T8/COR/96-850/MF44/G/FA8 10/1	-

