



Energy saving elegance that gives a beautiful sparkle of light

LED BA11

Philips LED BA11 candles offer energy saving ambiance with the elegant effect of incandescent candles. These designs provides light in an omnidirectional manner, giving lighting designers a long life alternative to standard incandescent sources.

Benefits

- Long life -- lowers maintenance costs by reducing re-lamp frequency
- Excellent color consistency with high color rendering (CRI)
- Certain offerings with a warm glow effect dim to a cozy glow to set the mood

Features

- Smooth Dimming
- Integrated compact driver design to achieve a decorative look and feels
- Installs into existing candelabra and medium-based fixtures
- 15,000-hour rated average life
- Wet location options available

Application

- Restaurants
- Hotels
- Residential

LED BA11

Versions



LEDbulb 3,5BA11 PER UD CL G E26
WGD 6 3PF T20



LEDbulb E12 BA11 CL



LEDbulb 5BA11 PER UD CL G E12
WGD 6 3PF T20



LEDbulb 3,5BA11 PER UD50 CL G
E26 D 6 3PF T20



LEDbulb NAM BA11 E26 FR



LEDbulb 3,5BA11 PER UD50 CL G
E12 D 6 3PF T20



LEDbulb CLA F15 E26 CL



LEDbulb 2,3BA11 PER UD CL G E12
WGD 6 3PFT20

LED BA11

Versions



LEDbulb E26 BA11 CL



LEDbulb NAM BA11 E12 FR





LEDbulb 5BA11 PER UD50 CL G
E26 D 6 3PF T20



LEDbulb 2 3,3 5,5W E12 BA11 927
CL

Dimensional drawing





Product	D	C
3.3BA11/PER/927-922/CL/G/E12/WGX 1FB T20	35 mm	110 mm
5BA11/PER/CRI95WG/FR/G/E12/WGD 1CT T20	35 mm	111 mm
6.6BA11/PER/927-922/CL/G/E12/WGX T20	35 mm	110 mm

Product	D	C
2.3BA11/PER/UD/CL/G/E12/WGD 6/3PFT20	35 mm	111 mm
3.5BA11/PER/UD50/CL/G/E12/D 6/3PF T20	35 mm	111 mm
5BA11/PER/UD/CL/G/E12/WGD 6/3PF T20	35 mm	111 mm

LED BA11

Dimensional drawing



General Information	
Switching Cycle	20,000
Nominal lifetime	15,000 hour(s)
Operating and Electrical	
Starting Time (Nom)	0.5 s

General Information

Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)
929002991703	3.5BA11/PER/UD/CL/G/E26/WGD 6/3PF T20	E26	15,000 hour(s)
929002295704	6.6BA11/PER/927-922/CL/G/E12/WGX T20	E12	-
929002991003	5BA11/PER/UD/CL/G/E12/WGD 6/3PF T20	E12	15,000 hour(s)
929002991903	3.5BA11/PER/UD50/CL/G/E26/D 6/3PF T20	E26	15,000 hour(s)
929003082404	5BA11/PER/CRI95WG/FR/G/E26/WGD 1CT T20	E26	-
929002991603	3.5BA11/PER/UD50/CL/G/E12/D 6/3PF T20	E12	15,000 hour(s)
929002091593	5.5F15/PER/927-922/CL/G/E26/WGX 1PF T20	E26	-

Product	D	C
5.5F15/PER/927-922/CL/G/E26/WGX 1PF T20	47 mm	112 mm

Product	D	C
3.5BA11/PER/UD/CL/G/E26/WGD 6/3PF T20	35 mm	99 mm
3.5BA11/PER/UD50/CL/G/E26/D 6/3PF T20	35 mm	99 mm
5BA11/PER/CRI95WG/FR/G/E26/WGD 1CT T20	35 mm	99 mm
5BA11/PER/UD50/CL/G/E26/D 6/3PF T20	35 mm	99 mm
6.6BA11/PER/927-922/CL/G/E26/WGX T20	35 mm	102 mm

Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)
929002991803	2.3BA11/PER/UD/CL/G/E12/WGD 6/3PFT20	E12	15,000 hour(s)
929002295604	6.6BA11/PER/927-922/CL/G/E26/WGX T20	E26	-
929002990804	5BA11/PER/CRI95WG/FR/G/E12/WGD 1CT T20	E12	-
929002991503	5BA11/PER/UD50/CL/G/E26/D 6/3PF T20	E26	15,000 hour(s)
929001969204	3.3BA11/PER/927-922/CL/G/E12/WGX 1FB T20	E12	15,000 hour(s)

Light Technical

LED BA11

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color	Color rendering	LLMF At End Of		
			Temperature (Nom)		index (CRI)	Color Code	Nominal Lifetime
							Luminous Flux
929002991703	3.5BA11/PER/UD/CL/G/E26/WGD 6/3PF T20	300 degree(s)	2200 K	95	922-927	70 %	300 lm
929002295704	6.6BA11/PER/927-922/CL/G/E12/WGX T20	-	2700 K	90	927-922	0.7 %	600 lm
929002991003	5BA11/PER/UD/CL/G/E12/WGD 6/3PF T20	300 degree(s)	2200 K	95	922-927	70 %	500 lm
929002991903	3.5BA11/PER/UD50/CL/G/E26/D 6/3PF T20	300 degree(s)	5000 K	95	950	70 %	300 lm
929003082404	5BA11/PER/CRI95WG/FR/G/E26/WGD 1CT T20	300 degree(s)	2700 K	95	927-922	70 %	500 lm
929002991603	3.5BA11/PER/UD50/CL/G/E12/D 6/3PF T20	300 degree(s)	5000 K	95	950	70 %	300 lm
929002091593	5.5F15/PER/927-922/CL/G/E26/WGX 1PF T20	300 degree(s)	2200 K	90	922-927	70 %	500 lm
929002991803	2.3BA11/PER/UD/CL/G/E12/WGD 6/3PFT20	300 degree(s)	2200 K	95	922-927	70 %	185 lm
929002295604	6.6BA11/PER/927-922/CL/G/E26/WGX T20	-	2700 K	90	927-922	0.7 %	600 lm
929002990804	5BA11/PER/CRI95WG/FR/G/E12/WGD 1CT T20	300 degree(s)	2700 K	95	927-922	70 %	500 lm
929002991503	5BA11/PER/UD50/CL/G/E26/D 6/3PF T20	300 degree(s)	5000 K	95	950	70 %	500 lm
929001969204	3.3BA11/PER/927-922/CL/G/E12/WGX 1FB T20	-	2700 K	90	927-922	70 %	300 lm

Operating and Electrical

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929002991703	3.5BA11/PER/UD/CL/G/E26/WGD 6/3PF T20	60 Hz	60 Hz	3.5 W	40 W
929002295704	6.6BA11/PER/927-922/CL/G/E12/WGX T20	60 Hz	60 Hz	6.6 W	75 W
929002991003	5BA11/PER/UD/CL/G/E12/WGD 6/3PF T20	60 Hz	60 Hz	5 W	60 W
929002991903	3.5BA11/PER/UD50/CL/G/E26/D 6/3PF T20	60 Hz	60 Hz	3.5 W	40 W
929003082404	5BA11/PER/CRI95WG/FR/G/E26/WGD 1CT T20	60 Hz	60 Hz	5 W	60 W
929002991603	3.5BA11/PER/UD50/CL/G/E12/D 6/3PF T20	60 Hz	60 Hz	3.5 W	40 W
929002091593	5.5F15/PER/927-922/CL/G	50 to 60 Hz	50 to 60 Hz	5.5 W	60 W

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929002991803	2.3BA11/PER/UD/CL/G/E12/WGD 6/3PFT20	60 Hz	60 Hz	2.3 W	25 W
929002295604	6.6BA11/PER/927-922/CL/G	60 Hz	60 Hz	6.6 W	75 W
929002990804	5BA11/PER/CRI95WG/FR/G/E12/WGD 1CT T20	60 Hz	60 Hz	5 W	60 W
929002991503	5BA11/PER/UD50/CL/G/E26/D 6/3PF T20	60 Hz	60 Hz	5 W	60 W
929001969204	3.3BA11/PER/927-922/CL/G/E12/WGX 1FB T20	50 to 60 Hz	50 to 60 Hz	3.3 W	40 W

Temperature

LED BA11

Order Code	Full Product Name	Ambient temperature range	T-Case Maximum (Nom)
929002991703	3.5BA11/PER/UD/CL/G/E26/WG D 6/3PF T20	-20 °C to 40 °C	-
929002295704	6.6BA11/PER/ 927-922/CL/G/E12/WGX T20	-	60 °C
929002991003	5BA11/PER/UD/CL/G/E12/WGD 6/3PF T20	-20 °C to 40 °C	-
929002991903	3.5BA11/PER/ UD50/CL/G/E26/D 6/3PF T20	-20 °C to 40 °C	-
929003082404	5BA11/PER/ CRI95WG/FR/G/E26/WGD 1CT T20	-	-
929002991603	3.5BA11/PER/UD50/CL/G/E12/D 6/3PF T20	-20 °C to 40 °C	-
929002091593	5.5F15/PER/ 927-922/CL/G/E26/WGX 1PF T20	-20 °C to 45 °C	60 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
929002991703	3.5BA11/PER/UD/CL/G/E26/WGD 6/3PF T20	Only with specific dimmers
929002295704	6.6BA11/PER/927-922/CL/G/E12/WGX T20	Yes
929002991003	5BA11/PER/UD/CL/G/E12/WGD 6/3PF T20	Only with specific dimmers
929002991903	3.5BA11/PER/UD50/CL/G/E26/D 6/3PF T20	Only with specific dimmers
929003082404	5BA11/PER/CRI95WG/FR/G/E26/WGD 1CT T20	Only with specific dimmers
929002991603	3.5BA11/PER/UD50/CL/G/E12/D 6/3PF T20	Only with specific dimmers

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929002991703	3.5BA11/PER/UD/CL/G/E26/WGD 6/3PF T20	Clear	BA11
929002295704	6.6BA11/PER/927-922/CL/G/E12/WGX T20	Clear	BA11
929002991003	5BA11/PER/UD/CL/G/E12/WGD 6/3PF T20	Clear	BA11
929002991903	3.5BA11/PER/UD50/CL/G/E26/D 6/3PF T20	Clear	BA11
929003082404	5BA11/PER/CRI95WG/FR/G/E26/WGD 1CT T20	Frosted	BA11
929002991603	3.5BA11/PER/UD50/CL/G/E12/D 6/3PF T20	Clear	BA11
929002091593	5.5F15/PER/927-922/CL/G/E26/WGX 1PF T20	Clear	F15



Approval and Application

Order Code	Full Product Name	Ambient temperature range	T-Case Maximum (Nom)
929002991803	2.3BA11/PER/UD/CL/G/E12/WG D 6/3PFT20	-20 °C to 40 °C	-
929002295604	6.6BA11/PER/ 927-922/CL/G/E26/WGX T20	-	60 °C
929002990804	5BA11/PER/ CRI95WG/FR/G/E12/WGD 1CT T20	-	-
929002991503	5BA11/PER/UD50/CL/G/E26/D 6/3PF T20	-20 °C to 40 °C	-
929001969204	3.3BA11/PER/ 927-922/CL/G/E12/WGX 1FB T20	-	50 °C

Order Code	Full Product Name	Dimmable
929002091593	5.5F15/PER/927-922/CL/G/E26/WGX 1PF T20	Only with specific dimmers
929002991803	2.3BA11/PER/UD/CL/G/E12/WGD 6/3PFT20	Only with specific dimmers
929002295604	6.6BA11/PER/927-922/CL/G/E26/WGX T20	Yes
929002990804	5BA11/PER/CRI95WG/FR/G/E12/WGD 1CT T20	Only with specific dimmers
929002991503	5BA11/PER/UD50/CL/G/E26/D 6/3PF T20	Only with specific dimmers
929001969204	3.3BA11/PER/927-922/CL/G/E12/WGX 1FB T20	Yes

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929002991803	2.3BA11/PER/UD/CL/G/E12/WGD 6/3PFT20	Clear	BA11
929002295604	6.6BA11/PER/927-922/CL/G/E26/WGX T20	Clear	BA11
929002990804	5BA11/PER/CRI95WG/FR/G/E12/WGD 1CT T20	Frosted	BA11
929002991503	5BA11/PER/UD50/CL/G/E26/D 6/3PF T20	Clear	BA11
929001969204	3.3BA11/PER/927-922/CL/G/E12/WGX 1FB T20	Clear	BA11

		Energy Consumption
Order Code	Full Product Name	kWh/1000 h
929002991703	3.5BA11/PER/UD/CL/G/E26/WGD 6/3PF T20	-
929002295704	6.6BA11/PER/927-922/CL/G/E12/WGX T20	- kWh
929002991003	5BA11/PER/UD/CL/G/E12/WGD 6/3PF T20	-
929002991903	3.5BA11/PER/UD50/CL/G/E26/D 6/3PF T20	-
929003082404	5BA11/PER/CRI95WG/FR/G/E26/WGD 1CT T20	-
929002991603	3.5BA11/PER/UD50/CL/G/E12/D 6/3PF T20	-
929002091593	5.5F15/PER/927-922/CL/G/E26/WGX 1PF T20	-
929002991803	2.3BA11/PER/UD/CL/G/E12/WGD 6/3PFT20	-
929002295604	6.6BA11/PER/927-922/CL/G/E26/WGX T20	- kWh
929002990804	5BA11/PER/CRI95WG/FR/G/E12/WGD 1CT T20	-
929002991503	5BA11/PER/UD50/CL/G/E26/D 6/3PF T20	-
929001969204	3.3BA11/PER/927-922/CL/G/E12/WGX 1FB T20	- kWh



LED BA11

