



UniEdge - Make Your Boundaries Stand Out

UniEdge

UniEdge is a surface mounted, exterior-rated and compact sized architectural LED edge lighting luminaire that is designed for façade and outdoor decorative lighting applications. The robust mechanical and unique optical designs make UniEdge ideal for edges lighting on windows and doors inner frames, building façades, landmarks and monuments. Available in white, monochromatic colors, RGB, RGBW and tunable white. Unique spread lens with DMX control option available to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

Benefits

- Unique Optical Distribution 3x90° to highlight the inner frames or outer edges of windows, balconies or doors.
- Compact Size, Light Weight and Tilttable Brackets.
- Through Wiring for power and DMX512 Signal.

Features

- Robust design & IP66 for outdoor applications
- Unique 3x90° optical distribution to illuminate architectural edges
- Drainage design to reduce dirt and water accumulation
- Adjustable -5° to +85° tilting angle
- Through wiring for power and DMX data via IP67 connectors

Application

- Bridges, Monuments, Facades
- Landscape
- Parks and Plazas

Warnings and Safety

- For outdoor use only


Versions



UniEdge 3LED

UniEdge 4LED

Dimensional drawing



General Information	
CE mark	-
Driver included	No
Flammability mark	For mounting on normally flammable surfaces
Light Technical	
Correlated Color Temperature (Nom)	-
Optical cover/lens type	Tempered glass
Mechanical and Housing	
Housing Color	Dark gray
Approval and Application	
Mech. impact protection code	IK06
Ingress protection code	IP66

Light Technical			Color rendering	
Order Code	Full Product Name	Light source color	index (CRI)	Luminous Flux
911401737273	BCP390 3LED RGB 24V 3x90 DMX D3	Red, green and blue	-	67 lumen
911401737283	BCP390 4LED 27K 24V 3x90 D3	Warm white	80	118 lumen
911401737293	BCP390 4LED 27K 24V 3x90 DMX D3	Warm white	80	115 lumen
911401737313	BCP390 4LED 30K 24V 3x90 DMX D3	Warm white	80	124 lumen
911401737323	BCP390 4LED 40K 24V 3x90 D3	Neutral white	80	144 lumen
911401737333	BCP390 4LED 40K 24V 3x90 DMX D3	Neutral white	80	142 lumen
911401737343	BCP390 4LED RGBNW 24V 3x90 DMX D3	Red, green, blue and white	-	102 lumen

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401737273	BCP390 3LED RGB 24V 3x90 DMX D3	7 W

Order Code	Full Product Name	Power Consumption
911401737283	BCP390 4LED 27K 24V 3x90 D3	10 W

Order Code	Full Product Name	Power Consumption
911401737293	BCP390 4LED 27K 24V 3x90 DMX D3	10 W
911401737313	BCP390 4LED 30K 24V 3x90 DMX D3	10 W
911401737323	BCP390 4LED 40K 24V 3x90 D3	10 W

Order Code	Full Product Name	Power Consumption
911401737333	BCP390 4LED 40K 24V 3x90 DMX D3	10 W
911401737343	BCP390 4LED RGBNW 24V 3x90 DMX D3	10 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401737273	BCP390 3LED RGB 24V 3x90 DMX D3	Yes
911401737283	BCP390 4LED 27K 24V 3x90 D3	No
911401737293	BCP390 4LED 27K 24V 3x90 DMX D3	Yes
911401737313	BCP390 4LED 30K 24V 3x90 DMX D3	Yes

Order Code	Full Product Name	Dimmable
911401737323	BCP390 4LED 40K 24V 3x90 D3	No
911401737333	BCP390 4LED 40K 24V 3x90 DMX D3	Yes
911401737343	BCP390 4LED RGBNW 24V 3x90 DMX D3	Yes

