



UniStrip G4 – Best in Class Linear LED Surface Mounted Luminaire for Exterior Fixed and Dynamic Architectural Lighting Applications

UniStrip G4

UniStrip G4 is a surface mounted, exterior-rated LED luminaire that is designed for façade and outdoor architectural lighting applications. One family that fits all your needs, wall washing, grazing and also linear flood lighting. The robust mechanical and unique optical designs make it ideal for illuminating buildings facades, bridges, overpasses and any application that requires a linear lighting solution. Available in white, monochromatic colors, RGB, RGBW and tunable white and DMX control option available with up to 8 pixels (8IDs) to give architects and designers the freedom to explore a wide range of concepts and design with no limitations.

Benefits

- High and Low Power LEDs versions available
- Various spread lenses that fit all applications
- Adjustable brackets and through wiring for end-to-end connection

UniStrip G4

Features

- Six sub-families with power ranges from 3W to 120W
- DC and AC powered versions
- Narrow, medium, wide and asymmetric beams available
- Optional glare shields for more visual comfort


Application

- Bridges, Monuments, Facades
- Landscape
- Parks and Plazas

Warnings and Safety



- For outdoor use only

Versions










BCP381

Dimensional drawing



Dimensional drawing



UniStrip G4

Product details

UniStrip G4 Detail Photo



UniStrip G4 Detail Photo



UniStrip G4 Detail Photo



UniStrip G4 Detail Photo




UniStrip G4 Detail Photo



159A3710 Detail Photo



UniStrip G4 Detail Photo



159A3691 Detail Photo



UniStrip G4 Detail Photo



UniStrip G4 Detail Photo



Product details

UniStrip G4 Detail Photo



UniStrip G4 Detail Photo



159A3731 Detail Photo



General Information	
CE mark	CE mark
Driver included	No
Mechanical and Housing	
Housing Color	Dark gray
Approval and Application	
Mech. impact protection code	IK06
Ingress protection code	IP66

General Information

Order Code	Full Product Name	Flammability mark	Light source replaceable
911401779982	BCP386 12LED 27K 24V 60 L30	-	-
911401780062	BCP386 12LED 30K 24V A11 L30	-	-
911401780082	BCP386 12LED 40K 24V A11 L30	-	-
911401780102	BCP386 12LED RGBNW 24V 45 L30 DMX	-	-
911401780122	BCP386 12LED RGBNW 24V A11 L30 DMX	-	-
911401780192	BCP386 30LED 30K 24V 45 L50	-	-
911401780232	BCP386 30LED 27K 24V 60 L50	-	-
911401780292	BCP386 30LED 27K 24V A11 L50	-	-
911401780332	BCP386 30LED 40K 24V A11 L50	-	-

Order Code	Full Product Name	Flammability mark	Light source replaceable
911401780362	BCP386 30LED RGBWW 24V A11 L50 DMX	-	-
911401780372	BCP386 30LED RGBNW 24V A11 L50 DMX	-	-
911401780442	BCP386 60LED 30K 24V 45 L100	-	-
911401780482	BCP386 60LED 27K 24V 60 L100	-	-
911401780502	BCP386 60LED 30K 24V 60 L100	-	-
911401780522	BCP386 60LED 40K 24V 60 L100	-	-
911401780562	BCP386 60LED 30K 24V A11 L100	-	-
911401780582	BCP386 60LED 40K 24V A11 L100	-	-
911401780592	BCP386 60LED RGBWW 24V 45 L100 DMX	-	-

Order Code	Full Product Name	Flammability mark	Light source replaceable
911401780602	BCP386 60LED RGBNW 24V 45 L100 DMX	-	-
911401780612	BCP386 60LED RGBWW 24V A11 L100 DMX	-	-
911401780622	BCP386 60LED RGBNW 24V A11 L100 DMX	-	-
911401780642	BCP386 60LED RGB 24V 45 L100 DMX	-	-
911401780652	BCP386 60LED RGB 24V A3 L100 DMX	-	-
911401738662	BCP381 12LED 30K 24V 40 L50	For mounting on normally flammable surfaces	No
911401738782	BCP381 24LED 27K 24V 40 L100	For mounting on normally flammable surfaces	No
911401738822	BCP381 24LED 30K 24V 40 L100	For mounting on normally flammable surfaces	No
911401738982	BCP381 6LED 30K 24V 40 L30	For mounting on normally flammable surfaces	No
911401739162	BCP382 18LED 27K 24V 40 L50	For mounting on normally flammable surfaces	No
911401739222	BCP382 18LED 30K 24V 40 L50	For mounting on normally flammable surfaces	No
911401739382	BCP382 36LED 27K 24V 40 L100	For mounting on normally flammable surfaces	No
911401739602	BCP382 9LED 27K 24V 40 L30	For mounting on normally flammable surfaces	No
911401739642	BCP382 9LED 30K 24V 17 L30	For mounting on normally flammable surfaces	No
911401739662	BCP382 9LED 30K 24V 40 L30	For mounting on normally flammable surfaces	No
911401739182	BCP382 18LED 30K 24V A2 L50	For mounting on normally flammable surfaces	No
911401739342	BCP382 36LED 27K 24V A2 L100	For mounting on normally flammable surfaces	No

Order Code	Full Product Name	Flammability mark	Light source replaceable
911401739622	BCP382 9LED 30K 24V A2 L30	For mounting on normally flammable surfaces	No
911401738602	BCP381 12LED 27K 24V A2 L50	For mounting on normally flammable surfaces	No
911401738802	BCP381 24LED 30K 24V A2 L100	For mounting on normally flammable surfaces	No
911401738962	BCP381 6LED 30K 24V A2 L30	For mounting on normally flammable surfaces	No
911401738702	BCP381 12LED 40K 24V 40 L50	For mounting on normally flammable surfaces	No
911401739022	BCP381 6LED 40K 24V 40 L30	For mounting on normally flammable surfaces	No
911401739242	BCP382 18LED 40K 24V A2 L50	For mounting on normally flammable surfaces	No
911401739262	BCP382 18LED 40K 24V 17 L50	For mounting on normally flammable surfaces	No
911401739462	BCP382 36LED 40K 24V A2 L100	For mounting on normally flammable surfaces	No
911401739482	BCP382 36LED 40K 24V 17 L100	For mounting on normally flammable surfaces	No
911401739502	BCP382 36LED 40K 24V 40 L100	For mounting on normally flammable surfaces	No
911401739702	BCP382 9LED 40K 24V 17 L30	For mounting on normally flammable surfaces	No
911401738682	BCP381 12LED 40K 24V A2 L50	For mounting on normally flammable surfaces	No
911401738842	BCP381 24LED 40K 24V A2 L100	For mounting on normally flammable surfaces	No
911401739002	BCP381 6LED 40K 24V A2 L30	For mounting on normally flammable surfaces	No

Light Technical

Order Code	Full Product Name	Luminaire light beam		Correlated Color Temperature (Nom)	Optical cover type	Color rendering index (CRI)	Luminous Flux
		spread	Light source color				
911401779982	BCP386 12LED 27K 24V 60 L30	-	Warm white	2700 K	Clear glass	80	200 lm
911401780062	BCP386 12LED 30K 24V A11 L30	-	Warm white	3000 K	Clear glass	80	195 lm
911401780082	BCP386 12LED 40K 24V A11 L30	-	Neutral white	4000 K	Clear glass	80	205 lm
911401780102	BCP386 12LED RGBNW 24V 45 L30 DMX	-	Red, green, blue and white	-	Clear glass	-	150 lm
911401780122	BCP386 12LED RGBNW 24V A11 L30 DMX	-	Red, green, blue and white	-	Clear glass	-	145 lm
911401780192	BCP386 30LED 30K 24V 45 L50	-	Warm white	3000 K	Clear glass	80	490 lm
911401780232	BCP386 30LED 27K 24V 60 L50	-	Warm white	2700 K	Clear glass	80	495 lm
911401780292	BCP386 30LED 27K 24V A11 L50	-	Warm white	2700 K	Clear glass	80	485 lm
911401780332	BCP386 30LED 40K 24V A11 L50	-	Neutral white	4000 K	Clear glass	80	515 lm
911401780362	BCP386 30LED RGBWW 24V A11 L50 DMX	-	Red, green, blue and white	-	Clear glass	-	360 lm
911401780372	BCP386 30LED RGBNW 24V A11 L50 DMX	-	Red, green, blue and white	-	Clear glass	-	375 lm
911401780442	BCP386 60LED 30K 24V 45 L100	-	Warm white	3000 K	Clear glass	80	975 lm
911401780482	BCP386 60LED 27K 24V 60 L100	-	Warm white	2700 K	Clear glass	80	985 lm
911401780502	BCP386 60LED 30K 24V 60 L100	-	Warm white	3000 K	Clear glass	80	985 lm
911401780522	BCP386 60LED 40K 24V 60 L100	-	Neutral white	4000 K	Clear glass	80	1,045 lm
911401780562	BCP386 60LED 30K 24V A11 L100	-	Warm white	3000 K	Clear glass	80	960 lm
911401780582	BCP386 60LED 40K 24V A11 L100	-	Neutral white	4000 K	Clear glass	80	1,020 lm
911401780592	BCP386 60LED RGBWW 24V 45 L100 DMX	-	Red, green, blue and white	-	Clear glass	-	720 lm
911401780602	BCP386 60LED RGBNW 24V 45 L100 DMX	-	Red, green, blue and white	-	Clear glass	-	750 lm
911401780612	BCP386 60LED RGBWW 24V A11 L100 DMX	-	Red, green, blue and white	-	Clear glass	-	695 lm
911401780622	BCP386 60LED RGBNW 24V A11 L100 DMX	-	Red, green, blue and white	-	Clear glass	-	730 lm
911401780642	BCP386 60LED RGB 24V 45 L100 DMX	-	Red, green and blue	-	Clear glass	-	375 lm
911401780652	BCP386 60LED RGB 24V A3 L100 DMX	-	Red, green and blue	-	Clear glass	-	345 lm
911401738662	BCP381 12LED 30K 24V 40 L50	40° x 40°	Warm white	3000 K	Clear flat	80	842 lm
911401738782	BCP381 24LED 27K 24V 40 L100	40° x 40°	Warm white	2700 K	Clear flat	80	1,651 lm
911401738822	BCP381 24LED 30K 24V 40 L100	40° x 40°	Warm white	3000 K	Clear flat	80	1,651 lm
911401738982	BCP381 6LED 30K 24V 40 L30	40° x 40°	Warm white	3000 K	Clear flat	80	430 lm
911401739162	BCP382 18LED 27K 24V 40 L50	40° x 40°	Warm white	2700 K	Clear flat	80	1,208 lm
911401739222	BCP382 18LED 30K 24V 40 L50	40° x 40°	Warm white	3000 K	Clear flat	80	1,208 lm
911401739382	BCP382 36LED 27K 24V 40 L100	40° x 40°	Warm white	2700 K	Clear flat	80	2,367 lm
911401739602	BCP382 9LED 27K 24V 40 L30	40° x 40°	Warm white	2700 K	Clear flat	80	619 lm
911401739642	BCP382 9LED 30K 24V 17 L30	17° x 17°	Warm white	3000 K	Clear flat	80	610 lm
911401739662	BCP382 9LED 30K 24V 40 L30	40° x 40°	Warm white	3000 K	Clear flat	80	619 lm
911401739182	BCP382 18LED 30K 24V A2 L50	16° x 35°	Warm white	3000 K	Clear flat	80	1,221 lm
911401739342	BCP382 36LED 27K 24V A2 L100	16° x 35°	Warm white	2700 K	Clear flat	80	2,393 lm
911401739622	BCP382 9LED 30K 24V A2 L30	16° x 35°	Warm white	3000 K	Clear flat	80	623 lm
911401738602	BCP381 12LED 27K 24V A2 L50	16° x 35°	Warm white	2700 K	Clear flat	80	848 lm
911401738802	BCP381 24LED 30K 24V A2 L100	16° x 35°	Warm white	3000 K	Clear flat	80	1,663 lm
911401738962	BCP381 6LED 30K 24V A2 L30	16° x 35°	Warm white	3000 K	Clear flat	80	432 lm
911401738702	BCP381 12LED 40K 24V 40 L50	40° x 40°	Neutral white	4000 K	Clear flat	80	910 lm
911401739022	BCP381 6LED 40K 24V 40 L30	40° x 40°	Neutral white	4000 K	Clear flat	80	464 lm
911401739242	BCP382 18LED 40K 24V A2 L50	16° x 35°	Neutral white	4000 K	Clear flat	80	1,318 lm

Order Code	Full Product Name	Luminaire light beam		Correlated Color	Optical cover	Color rendering	Luminous Flux
		spread	Light source color	Temperature (Nom)	type	index (CRI)	
911401739262	BCP382 18LED 40K 24V 17 L50	17° x 17°	Neutral white	4000 K	Clear flat	80	1,292 lm
911401739462	BCP382 36LED 40K 24V A2 L100	16° x 35°	Neutral white	4000 K	Clear flat	80	2,584 lm
911401739482	BCP382 36LED 40K 24V 17 L100	17° x 17°	Neutral white	4000 K	Clear flat	80	2,533 lm
911401739502	BCP382 36LED 40K 24V 40 L100	40° x 40°	Neutral white	4000 K	Clear flat	80	2,557 lm
911401739702	BCP382 9LED 40K 24V 17 L30	17° x 17°	Neutral white	4000 K	Clear flat	80	659 lm
911401738682	BCP381 12LED 40K 24V A2 L50	16° x 35°	Neutral white	4000 K	Clear flat	80	916 lm
911401738842	BCP381 24LED 40K 24V A2 L100	16° x 35°	Neutral white	4000 K	Clear flat	80	1,796 lm
911401739002	BCP381 6LED 40K 24V A2 L30	16° x 35°	Neutral white	4000 K	Clear flat	80	467 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
911401779982	BCP386 12LED 27K 24V 60 L30	3 W	911401738822	BCP381 24LED 30K 24V 40 L100	24 W
911401780062	BCP386 12LED 30K 24V A11 L30	3 W	911401738982	BCP381 6LED 30K 24V 40 L30	6 W
911401780082	BCP386 12LED 40K 24V A11 L30	3 W	911401739162	BCP382 18LED 27K 24V 40 L50	18 W
911401780102	BCP386 12LED RGBNW 24V 45 L30 DMX	3 W	911401739222	BCP382 18LED 30K 24V 40 L50	18 W
911401780122	BCP386 12LED RGBNW 24V A11 L30 DMX	3 W	911401739382	BCP382 36LED 27K 24V 40 L100	36 W
911401780192	BCP386 30LED 30K 24V 45 L50	7.5 W	911401739602	BCP382 9LED 27K 24V 40 L30	9 W
911401780232	BCP386 30LED 27K 24V 60 L50	7.5 W	911401739642	BCP382 9LED 30K 24V 17 L30	9 W
911401780292	BCP386 30LED 27K 24V A11 L50	7.5 W	911401739662	BCP382 9LED 30K 24V 40 L30	9 W
911401780332	BCP386 30LED 40K 24V A11 L50	7.5 W	911401739182	BCP382 18LED 30K 24V A2 L50	18 W
911401780362	BCP386 30LED RGBWW 24V A11 L50 DMX	8 W	911401739342	BCP382 36LED 27K 24V A2 L100	36 W
911401780372	BCP386 30LED RGBNW 24V A11 L50 DMX	8 W	911401739622	BCP382 9LED 30K 24V A2 L30	9 W
911401780442	BCP386 60LED 30K 24V 45 L100	15 W	911401738602	BCP381 12LED 27K 24V A2 L50	12 W
911401780482	BCP386 60LED 27K 24V 60 L100	15 W	911401738802	BCP381 24LED 30K 24V A2 L100	24 W
911401780502	BCP386 60LED 30K 24V 60 L100	15 W	911401738962	BCP381 6LED 30K 24V A2 L30	6 W
911401780522	BCP386 60LED 40K 24V 60 L100	15 W	911401738702	BCP381 12LED 40K 24V 40 L50	12 W
911401780562	BCP386 60LED 30K 24V A11 L100	15 W	911401739022	BCP381 6LED 40K 24V 40 L30	6 W
911401780582	BCP386 60LED 40K 24V A11 L100	15 W	911401739242	BCP382 18LED 40K 24V A2 L50	18 W
911401780592	BCP386 60LED RGBWW 24V 45 L100 DMX	15 W	911401739262	BCP382 18LED 40K 24V 17 L50	18 W
911401780602	BCP386 60LED RGBNW 24V 45 L100 DMX	15 W	911401739462	BCP382 36LED 40K 24V A2 L100	36 W
911401780612	BCP386 60LED RGBWW 24V A11 L100 DMX	15 W	911401739482	BCP382 36LED 40K 24V 17 L100	36 W
911401780622	BCP386 60LED RGBNW 24V A11 L100 DMX	15 W	911401739502	BCP382 36LED 40K 24V 40 L100	36 W
911401780642	BCP386 60LED RGB 24V 45 L100 DMX	15 W	911401739702	BCP382 9LED 40K 24V 17 L30	9 W
911401780652	BCP386 60LED RGB 24V A3 L100 DMX	15 W	911401738682	BCP381 12LED 40K 24V A2 L50	12 W
911401738662	BCP381 12LED 30K 24V 40 L50	12 W	911401738842	BCP381 24LED 40K 24V A2 L100	24 W
911401738782	BCP381 24LED 27K 24V 40 L100	24 W	911401739002	BCP381 6LED 40K 24V A2 L30	6 W

Controls and Dimming

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
911401779982	BCP386 12LED 27K 24V 60 L30	No	911401780332	BCP386 30LED 40K 24V A11 L50	No
911401780062	BCP386 12LED 30K 24V A11 L30	No	911401780362	BCP386 30LED RGBWW 24V A11 L50 DMX	Yes
911401780082	BCP386 12LED 40K 24V A11 L30	No	911401780372	BCP386 30LED RGBNW 24V A11 L50 DMX	Yes
911401780102	BCP386 12LED RGBNW 24V 45 L30 DMX	Yes	911401780442	BCP386 60LED 30K 24V 45 L100	No
911401780122	BCP386 12LED RGBNW 24V A11 L30 DMX	Yes	911401780482	BCP386 60LED 27K 24V 60 L100	No
911401780192	BCP386 30LED 30K 24V 45 L50	No	911401780502	BCP386 60LED 30K 24V 60 L100	No
911401780232	BCP386 30LED 27K 24V 60 L50	No	911401780522	BCP386 60LED 40K 24V 60 L100	No
911401780292	BCP386 30LED 27K 24V A11 L50	No	911401780562	BCP386 60LED 30K 24V A11 L100	No

Order Code	Full Product Name	Dimmable
911401780582	BCP386 60LED 40K 24V A11 L100	No
911401780592	BCP386 60LED RGBWW 24V 45 L100 DMX	Yes
911401780602	BCP386 60LED RGBNW 24V 45 L100 DMX	Yes
911401780612	BCP386 60LED RGBWW 24V A11 L100 DMX	Yes
911401780622	BCP386 60LED RGBNW 24V A11 L100 DMX	Yes
911401780642	BCP386 60LED RGB 24V 45 L100 DMX	Yes
911401780652	BCP386 60LED RGB 24V A3 L100 DMX	Yes
911401738662	BCP381 12LED 30K 24V 40 L50	No
911401738782	BCP381 24LED 27K 24V 40 L100	No
911401738822	BCP381 24LED 30K 24V 40 L100	No
911401738982	BCP381 6LED 30K 24V 40 L30	No
911401739162	BCP382 18LED 27K 24V 40 L50	No
911401739222	BCP382 18LED 30K 24V 40 L50	No
911401739382	BCP382 36LED 27K 24V 40 L100	No
911401739602	BCP382 9LED 27K 24V 40 L30	No
911401739642	BCP382 9LED 30K 24V 17 L30	No
911401739662	BCP382 9LED 30K 24V 40 L30	No

Order Code	Full Product Name	Dimmable
911401739182	BCP382 18LED 30K 24V A2 L50	No
911401739342	BCP382 36LED 27K 24V A2 L100	No
911401739622	BCP382 9LED 30K 24V A2 L30	No
911401738602	BCP381 12LED 27K 24V A2 L50	No
911401738802	BCP381 24LED 30K 24V A2 L100	No
911401738962	BCP381 6LED 30K 24V A2 L30	No
911401738702	BCP381 12LED 40K 24V 40 L50	No
911401739022	BCP381 6LED 40K 24V 40 L30	No
911401739242	BCP382 18LED 40K 24V A2 L50	No
911401739262	BCP382 18LED 40K 24V 17 L50	No
911401739462	BCP382 36LED 40K 24V A2 L100	No
911401739482	BCP382 36LED 40K 24V 17 L100	No
911401739502	BCP382 36LED 40K 24V 40 L100	No
911401739702	BCP382 9LED 40K 24V 17 L30	No
911401738682	BCP381 12LED 40K 24V A2 L50	No
911401738842	BCP381 24LED 40K 24V A2 L100	No
911401739002	BCP381 6LED 40K 24V A2 L30	No

