



# **Elegant and Brighter**

## **UNIBollard**

UNIBollard is dedicated to light up public environments of park, buildings outside area, compound areas to bring you a more bright light in evening with the safety and convenience. Its graceful appearance is also a part of public scenery to beautify area you live.

#### **Benefits**

- · Long-lasting working period
- · IP68 connector for easy connection and reliability
- · Anti-UV cover without concerns of yellowing

### Features

- $\cdot$  0.3M ( 0.45M ) / 0.6M / 1.2M height for option
- Up to 1100 lm
- · CRI80
- $\boldsymbol{\cdot}$  Look and feel: cylinder and cubic housing for alternatives
- 50K hours L70B50 @ ta 35°C

#### **Application**

- Public spaces
- · Residential gardens, pathways

#### **Warnings and Safety**

• Use additional surge protection device in electrical circuit for lighting wiring.

## **UNIBollard**

### Versions



## Dimensional drawing



### **UNIBollard**

General Information	
CE mark	-
Driver included	Yes
Flammability mark	-
Light source replaceable	No
Light Technical	
Light source color	830 warm white
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	>80
Standard tilt angle side entry	-
Standard tilt angle posttop	-
Controls and Dimming	
Dimmable	No
Approval and Application	
Mech. impact protection code	IK06
Ingress protection code	IP65

### **Light Technical**

Order Code	Full Product Name	Optical cover type	Luminous Flux
01755262	BCP310 LED760/WW 15W 100-240V Cyl black	Polycarbonate bowl/cover frosted	760 lm
51825499	BCP312 LED760/WW 15W 100-240V Cyl BK	Polycarbonate bowl/cover frosted	760 lm
01755242	BCP211 LED900/WW 13W 100-240V Rec silver	Polycarbonate bowl/cover opal	1,000 lm
51822399	BCP210 LED1000/WW 13W 100-240V Rec AL	Polycarbonate bowl/cover opal	1,000 lm
01755272	BCP311 LED760/WW 15W 100-240V Cyl BK	Polycarbonate bowl/cover frosted	760 lm
51783799	BCP212 LED1000/WW 13W 100-240V Rec AL	Polycarbonate bowl/cover opal	1,000 lm

### Operating and Electrical

Order Code	Full Product Name	Power Consumption
01755262	BCP310 LED760/WW 15W 100-240V Cyl black	15 W
51825499	BCP312 LED760/WW 15W 100-240V Cyl BK	15 W
01755242	BCP211 LED900/WW 13W 100-240V Rec silver	13 W

Order Code	Full Product Name	Power Consumption
51822399	BCP210 LED1000/WW 13W 100-240V Rec AL	13 W
01755272	BCP311 LED760/WW 15W 100-240V Cyl BK	15 W
51783799	BCP212 LED1000/WW 13W 100-240V Rec AL	13 W

#### Mechanical and Housing

Order Code	Full Product Name	Housing Color
01755262	BCP310 LED760/WW 15W 100-240V Cyl black	Black and aluminum
51825499	BCP312 LED760/WW 15W 100-240V Cyl BK	Black and aluminum
01755242	BCP211 LED900/WW 13W 100-240V Rec silver	Aluminum and white

Order Code	Full Product Name	Housing Color
51822399	BCP210 LED1000/WW 13W 100-240V Rec AL	Aluminum and white
01755272	BCP311 LED760/WW 15W 100-240V Cyl BK	Black and aluminum
51783799	BCP212 LED1000/WW 13W 100-240V Rec AL	Aluminum and white



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.