



# Elegant and Brighter

## UNIBollard

UNIBollard is dedicated to light up public environments of park, buildings outside area, compound areas to bring you a more bright light in evening with the safety and convenience. Its graceful appearance is also a part of public scenery to beautify area you live.

### Benefits

- Long-lasting working period
- IP68 connector for easy connection and reliability
- Anti-UV cover without concerns of yellowing

### Features

- 0.3M ( 0.45M ) / 0.6M / 1.2M height for option
- Up to 1100 lm
- CRI80
- Look and feel: cylinder and cubic housing for alternatives
- 50K hours L70B50 @ ta 35°C

### Application

- Public spaces
- Residential gardens, paths

### Warnings and Safety

- Use additional surge protection device in electrical circuit for lighting wiring.

Versions



BCP310 BS



BCP312 BS



BCP211 BS



BCP210 BS




BCP311 BS




BCP212 BS

Dimensional drawing



	H,mm
BCP310	300
BCP311	600
BCP312	1200



	H,mm
BCP210	450
BCP211	600
BCP212	1200

### General Information

CE mark	-
Driver included	Yes
Flammability mark	-
Light source replaceable	No

### Light Technical

Light source color	830 warm white
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	>80
Standard tilt angle side entry	-
Standard tilt angle posttop	-

### Controls and Dimming

Dimmable	No
----------	----

### Approval and Application

Mech. impact protection code	IK06
Ingress protection code	IP65

### Light Technical

Order Code	Full Product Name	Optical cover type	Luminous Flux
911401755262	BCP310 LED760/WW 15W 100-240V Cyl BK	Polycarbonate bowl/cover frosted	760 lm
911401755282	BCP312 LED760/WW 15W 100-240V Cyl BK	Polycarbonate bowl/cover frosted	760 lm
911401755242	BCP211 LED1000/WW 13W 100-240V Rec AL	Polycarbonate bowl/cover opal	1,000 lm
911401755232	BCP210 LED1000/WW 13W 100-240V Rec AL	Polycarbonate bowl/cover opal	1,000 lm
911401755272	BCP311 LED760/WW 15W 100-240V Cyl BK	Polycarbonate bowl/cover frosted	760 lm
911401755252	BCP212 LED1000/WW 13W 100-240V Rec AL	Polycarbonate bowl/cover opal	1,000 lm

### Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401755262	BCP310 LED760/WW 15W 100-240V Cyl BK	15 W
911401755282	BCP312 LED760/WW 15W 100-240V Cyl BK	15 W
911401755242	BCP211 LED1000/WW 13W 100-240V Rec AL	13 W

Order Code	Full Product Name	Power Consumption
911401755232	BCP210 LED1000/WW 13W 100-240V Rec AL	13 W
911401755272	BCP311 LED760/WW 15W 100-240V Cyl BK	15 W
911401755252	BCP212 LED1000/WW 13W 100-240V Rec AL	13 W

### Mechanical and Housing

Order Code	Full Product Name	Housing Color
911401755262	BCP310 LED760/WW 15W 100-240V Cyl BK	Black and aluminum
911401755282	BCP312 LED760/WW 15W 100-240V Cyl BK	Black and aluminum
911401755242	BCP211 LED1000/WW 13W 100-240V Rec AL	Aluminum and white

Order Code	Full Product Name	Housing Color
911401755232	BCP210 LED1000/WW 13W 100-240V Rec AL	Aluminum and white
911401755272	BCP311 LED760/WW 15W 100-240V Cyl BK	Black and aluminum
911401755252	BCP212 LED1000/WW 13W 100-240V Rec AL	Aluminum and white

