



SunStay. All In One solar street light

SunStay

Integrated solar street light with Lithium Ferro Phosphate battery, solar panel and charger built into the luminaire. Pressure die cast aluminium for sturdiness and long life. Specially designed pole mounting bracket allows different tilt angles, lateral and pole top mounting.

Benefits

- Brings light to areas without access to electric grid
- Saves energy
- Preserves landscape as no trenching for cabling required
- Environment friendly
- Sturdy construction for long life

Features

- High luminous efficacy of 175 lm/Watt to maximize battery performance
- Replaceable Lithium Ferro Phosphate battery for long life and hassle free operations.
- MPPT charge controller for maximum efficiency
- Pressure die-cast aluminum housing for sturdiness and excellent heat dissipation.
- Specially designed pole mounting bracket with adjustable tilt angles of 0 to 15 degrees, which can also be used in post top & lateral mounting positions
- Factory set dimming profile along with PIR sensor for run time maximization.
- Self diagnostic feature along with battery charging, discharging & cut-off LED Indicators

Application

- Class A & B roads
- Rural areas
- Parks, pedestrian path lighting
- Industries, office, schools
- Shopping centers, corporate campuses, plazas



Versions



standard shot sunstay

SunStay 4500 Lumen

Dimensional drawing



PHILIPS

Light Technical	
Correlated Color Temperature (Nom)	5700 K
Color rendering index (CRI)	>70
Operating and Electrical	
Battery charging & discharging cycles	2000
Battery type	Lithium Ferro Phosphate
Battery voltage	12.8 V
Charge controller type	MPPT
Panel type	Mono crystalline
Panel voltage	17 Vmp, 21 Voc V
Temperature	
Ambient temperature range	0 to +35 °C
Controls and Dimming	
Dimmable	Yes
Configurability	Factory Configurable
Mechanical and Housing	
Housing Color	Gray
Approval and Application	
Ingress protection code	IP65
Application Conditions	
Battery location	Inside Luminaire
Grid connection type	Off grid
Solar dimming profile	30% Dusk to dawn, 100% on motion. (Sensor disabled for 5 Hrs, after 5 Hrs)

Operating and Electrical

Order Code	Full Product Name	Battery ampere hour	Panel peak wattage
919515812388	BRP710 LED30 CW MR S1 12V LFP AIO Solar	20 Ah	35 W
919515812390	BRP710 LED30 CW MR S1 12V LFP AIO Solar	20 Ah	35 W
919515813566	BRP710 LED45 CW MR S1 12V LFP Solar	30 Ah	60 W

Mechanical and Housing

Order Code	Full Product Name	Overall height	Overall length	Overall width
919515812388	BRP710 LED30 CW MR S1 12V LFP AIO Solar	156 mm	684 mm	369 mm
919515812390	BRP710 LED30 CW MR S1 12V LFP AIO Solar	156 mm	684 mm	369 mm

Order Code	Full Product Name	Overall height	Overall length	Overall width
919515813566	BRP710 LED45 CW MR S1 12V LFP Solar	188 mm	757 mm	511 mm

Application Conditions

Order Code	Full Product Name	Ambient temperature range for charging	Ambient temperature range for discharging (when light is on)
919515812388	BRP710 LED30 CW MR S1 12V LFP AIO Solar	0 °C to +45 °C	-20 °C to +35 °C

Order Code	Full Product Name	Ambient temperature	Ambient temperature
		range for charging	range for discharging (when light is on)
919515812390	BRP710 LED30 CW MR S1 12V LFP AIO Solar	0 °C to +45 °C °C	-20 °C to +35 °C °C
919515813566	BRP710 LED45 CW MR S1 12V LFP Solar	0 °C to +45 °C	-20 °C to +35 °C

