



New Smartbright Tri Color Waterproof Batten provides flexibility to the customer to choose from 3 CCT and 2 wattage options before installation, based on their specific need

Smartbright CCT/Wattage Tunable Waterproof batten

The new Philips tri-colour batten offers exceptional value. It is perfect for your everyday lighting installations. Available in 2 standard sizes, it has the option of 3 CCT selection and 2 Wattage selection to provide flexibility to customers.

Smartbright CCT/Wattage Tunable Waterproof batten

Benefits

- Tri-color, Dual wattage selectable
- 50K hours life
- Multi-purpose weatherproof design with IP65/IK08 rating

Features

- 3 colour temperatures and dual power settings – One device for many applications
- IP65/IK08 – Water and dustproof. For all weather
- Reliable with a long service life of 50 000 hours L70
- 5 years warranty

Application

- Parking Garages
- Offices

Versions

Smartbright tri color waterproof
Batten



Smartbright tri color waterproof
Batten



Smartbright CCT/Wattage Tunable Waterproof batten

-	
Driver failure rate at 5000 h	0.003 %
Application Conditions	
Ambient temperature range	-20 to +40 °C
Maximum dim level	Not applicable
Approval and Application	
Mech. impact protection code	IK08
Ingress protection code	IP65
Controls and Dimming	
Dimmable	No
Operating and Electrical	
Input Voltage	220 to 240 V
General Information	
Beam angle of light source	120 °
CE mark	-
Protection class IEC	Safety class I
Optical cover/lens type	Polycarbonate bowl/cover
Driver included	Yes
ENEC mark	-
Flammability mark	-
Glow-wire test	Temperature 650 °C, duration 30 s
Light source replaceable	No
Number of gear units	1 unit
Optic type	Beam angle 120°
Initial Performance (IEC Compliant)	
Initial chromaticity	0.38;0.38
Init. Corr. Color Temperature	- K
Init. Color Rendering Index	>80
Initial LED luminaire efficacy	100 lm/W
Luminous flux tolerance	+/-10%
Mechanical and Housing	
Color	Gray
Over Time Performance (IEC Compliant)	
Median useful life L80B50	44000 h
Median useful life L90B50	21000 h

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial luminous flux	Initial input power
911401821680	WT067C SWT SCCT LED L600 PSU AU	2000 lm	20 W
911401821780	WT067C SWT SCCT LED L1200 PSU AU	4000 lm	40 W

Smartbright CCT/Wattage Tunable Waterproof batten

